



DATA SHEET

# i15-MM0133 Lock

i15 Lock  
Safety locking devices

## SAFETY LOCKING DEVICES

## i15-MM0133 Lock

## ORDERING INFORMATION

Type	part no.
i15-MM0133 Lock	6034025

Further device versions and accessories at [www.sick.com/i15\\_Lock](http://www.sick.com/i15_Lock)



actuator not supplied with delivery

## DETAILED TECHNICAL DATA

## FEATURES

Sensor principle	Electro-mechanical
Locking principle	Power to release
Positive action N/C solenoid monitoring contacts	1
N/O solenoid monitoring contacts	0
Positive action N/C door monitoring contacts	1
N/O door monitoring contacts	1
N/C contact for door monitoring	0
Locking force $F_{max}$	2,000 N (EN ISO 14119) <sup>1)</sup>
Locking force $F_{zh}$	1,500 N (EN ISO 14119)
Actuation force	$\geq 35$ N
Retaining force	$\leq 30$ N
Actuation frequency	$\leq 7,000$ /h
Actuation directions	4
Approach speed	$\leq 20$ m/min

<sup>1)</sup> 1500 N with angled actuator.

## SAFETY-RELATED PARAMETERS

$B_{10d}$ parameter	$2 \times 10^6$ switching cycles (with small load)
Type	Type 2 (EN ISO 14119)
Actuator coding level	Low coding level (EN ISO 14119)

Safe state in the event of a fault	The switch has no internal fault detection and is unable to assume a safe state in the event of a fault. Fault detection is performed by the connected safety-related logic unit.
------------------------------------	-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

## FUNCTIONS

Safe series connection	None, only individual wiring (with diagnostics)
------------------------	-------------------------------------------------

## INTERFACES

Connection type	Cable gland, 1 x M20
Conductor cross section	0.34 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>

## ELECTRONICS

Contamination rating	3
Switching principle	Slow action switching element
Usage category	AC-15/DC-13 (IEC 60947-5-1)
Rated operating current (voltage)	4 A (230 V AC) 4 A (24 V DC)
Rated insulation voltage U <sub>i</sub>	250 V
Rated impulse withstand voltage U <sub>imp</sub>	2,500 V
Type of output	Electro-mechanical contacts
Power consumption	≤ 6 W
Short-circuit protection	4 A gG
Switching voltage	≥ 12 V DC
Switching current (switching voltage)	1 mA (24 V DC)
Solenoid operating voltage	20.4 V DC ... 26.4 V DC
Switch-on time of magnet	100 %
Locking principle	Power to release

## MECHANICS

Weight	0.48 kg
Housing material	Glass-fiber reinforced thermoplastic
Actuator head material	Metal
Mechanical life	2 x 10 <sup>6</sup> switching cycles


## AMBIENT DATA

Enclosure rating	IP67
Ambient operating temperature	-20 °C ... +55 °C
Storage temperature	-20 °C ... +55 °C

## CERTIFICATES


EU declaration of conformity	✓
UK declaration of conformity	✓
China RoHS	✓
cULus certificate	✓
EC-Type-Examination approval	✓
Third party certificate	✓

**DIMENSIONAL DRAWING**



Dimensions in mm (inch)

**SWITCHING ELEMENTS**



⌞ Positive action N/C locking monitoring contact  
 ⊕ Positive action N/C door monitoring contact

**UK: Locking monitoring contacts**  
**SK: Door monitoring contacts**

**Switching element 12:**  
 1 positive action N/C contact (Locking monitoring)  
 2 positive action N/C contacts (Door monitoring)

**Switching element 13:**  
 1 positive action N/C contact (Locking monitoring)  
 1 positive action N/C contact + 1 N/O contact (Door monitoring)

Further information as well as suitable accessories, example applications and downloads such as CAD dimensional models, operating instructions and software can be found at [www.sick.com/6034025](http://www.sick.com/6034025)



SICK AG  
WALDKIRCH  
GERMANY  
SICK.COM

# SICK AT A GLANCE

SICK is a leading global technology company for intelligent sensors and integrated solutions in industrial automation. Our technologies set benchmarks, making your industrial processes more efficient, safer and more sustainable – both in logistics and manufacturing operations.

SICK combines sensor intelligence with industry expertise and certified consulting services. We provide the ideal foundation for scalable as well as tailor-made automation solutions and create added value along the entire value chain. Our close partnerships with our customers are more than just a promise: Together, we optimize productivity, improve quality, protect health and safety, and help build a sustainable future. All with empathy and trust.

Since 1946, we have been developing innovative technologies with passion and a pioneering spirit. With a global network in around 40 countries, SICK has a global presence and is always close by. The company's headquarters are located in Waldkirch near Freiburg, Germany. Our customers benefit from our understanding of both local and global requirements, which enables us to deliver tailor-made solutions

**SICK**  
Sensor Intelligence