

T4000-2DRNAC

T4000 Compact

NON-CONTACT SAFETY SWITCHES





Ordering information

Туре	Part no.
T4000-2DRNAC	6022052

Other models and accessories → www.sick.com/T4000_Compact



Detailed technical data

Features

System part	Sensor
Sensor principle	RFID
Number of safe outputs	2
Safe switch on distance S _{ao}	18 mm ¹⁾ 18 mm ²⁾ 19 mm ³⁾
Safe switch off distance S _{ar}	40 mm ¹⁾ 58 mm ²⁾ 41 mm ³⁾
Active sensor surfaces	1
Actuation directions	5
Monitoring time minimum dwell time	≥ 0.5 s

 $^{^{1)}}$ With actuator T4000-1KBA.

Safety-related parameters

Category	Category 3 (EN ISO 13849)
Performance level	PL e (EN ISO 13849)
$\ensuremath{PFH_{D}}$ (mean probability of a dangerous failure per hour)	2.5 x 10 ⁻⁸
T _M (mission time)	20 years (EN ISO 13849)
Туре	Type 4 (EN ISO 14119)
Actuator coding level	High coding level (EN ISO 14119)
Classification in compliance with IEC/ EN 60947-5-3	PDF-M

Functions

Safe series connection	None, only individual wiring (with diagnostics)
------------------------	---

Interfaces

Connection type		

 $^{^{2)}}$ With actuator T4000-1KBQ.

³⁾ With actuator T4000-1KBR.

Long connecting cable	≤ 300 m
Coupling nut material	Brass
Display elements	
Out indication	✓
Error indication	✓
Status display	✓

Electrical data

Protection class	III
Contamination rating	2
Classification according to cULus	Class 2
Note on supply voltage U_S	Operation with UL-class 2 power supply only
External fuse	At supply voltage V_s 0.25 A 8 A
Switching voltage	24 V DC
Usage category	DC-13
Rated operating current (voltage)	0.4 A (24 V DC)
Rated insulation voltage U _i	75 V
Rated impulse withstand voltage \mathbf{U}_{imp}	1,500 V AC
Supply voltage V _s	(18 V DC 27 V DC)
Power consumption	80 mA
Type of output	Self-monitoring semiconductor outputs (OSSDs)
Switching current	≤ 0.4 A
Switch-on time	\leq 3 s $^{1)}$

¹⁾ After switching on the operating voltage, the semiconductor outputs are switched off during the ready delay and the alarm outputs are at LOW potential.

Mechanical data

Design	Rectangular
Dimensions (W x H x D)	40 mm x 118 mm x 40 mm
Weight	+ 0.4 kg
Housing material	Plastic PTB VO GF30

Ambient data


Enclosure rating	IP67
Ambient operating temperature	-20 °C +55 °C
Storage temperature	-25 °C +70 °C
Vibration resistance	10 Hz 55 Hz, 0.5 mm (IEC 60068-2-6)
Shock resistance	30 g, 11 ms (IEC 60068-2-27)

Classifications

ECLASS 5.0	27272403
ECLASS 5.1.4	27272403
ECLASS 6.0	27272403
ECLASS 6.2	27272403
ECLASS 7.0	27272403

ECLASS 8.0	27272403
ECLASS 8.1	27272403
ECLASS 9.0	27272403
ECLASS 10.0	27272403
ECLASS 11.0	27272403
ECLASS 12.0	27274601
ETIM 5.0	EC001829
ETIM 6.0	EC001829
ETIM 7.0	EC001829
ETIM 8.0	EC001829
UNSPSC 16.0901	39122205

Dimensional drawing (Dimensions in mm (inch))



SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

