



UE44-3SL3D330

UE44-3SL

SAFETY RELAYS

SICK
Sensor Intelligence.



Illustration may differ



Ordering information

Type	part no.
UE44-3SL3D330	6024910

Other models and accessories → www.sick.com/UE44-3SL

Detailed technical data

Safety-related parameters

Safety integrity level	1)
Category	Category 4 (EN ISO 13849) ²⁾ Category 3 (EN ISO 13849) ¹⁾
Performance level	PL e (EN ISO 13849) ²⁾ PL d (EN ISO 13849) ¹⁾
B_{10d} parameter	4 x 10 ⁵ switching cycles (with maximum load)
PFH_D (mean probability of a dangerous failure per hour)	3.0 x 10 ⁻⁸ (EN ISO 13849) ²⁾ 2.0 x 10 ⁻⁸ (EN ISO 13849) ¹⁾
T_M (mission time)	20 years (EN ISO 13849)
Stop category	0 (EN 60204-1)

¹⁾ For time contacts 37/38.

²⁾ For contacts 13/14, 23/24.

Electronics - Operating data

Voltage supply	A1, A2
Output circuit > 25 V AC / 60 V DC	PELV
Output circuit ≤ 25 V AC / 60 V DC	PELV or SELV
Supply voltage V_S	A1, A2
	24 V DC (20.4 V DC ... 26.4 V DC)
Residual ripple	(≤ 2.4 V _{pp}) ¹⁾
Power consumption	1.8 W
Overvoltage category	II
Rated insulation voltage U_i	300 V AC
Rated impulse withstand voltage U_{imp}	4 kV

¹⁾ In DC operation, within the limits of V_S.

Test voltage	2 kV (50 Hz) (EN 60439-1)
---------------------	---------------------------

¹⁾ In DC operation, within the limits of V_S .

Electronics - Control voltage: S11/S33, S21

Control voltage	22 V DC
Short-circuit current	≤ 2.2 A, between S33/S11 and S21
Short-circuit protection	PTC resistor

Electronics - Input circuits: S12, S31/S22

Input current	25 mA $\leq$ 100 mA
Reset time	
Manual	(≤ 30 ms)
Automatic	(≤ 750 ms)
Activation time of reset button	≥ 250 ms
Synchronous time monitoring	≤ 500 ms
Cable resistance	$\leq 85 \Omega$

Electronics - Output current paths: 13/14, 23/24, 37/38

Response time	(≤ 25 ms) ¹⁾
On-delay time	1.5 s ... 30 s
Number of enabling current paths (N/O)	2, category 4
Number of on-delayed N/O contacts	1, category 3
Contact type	Positively driven
Contact material	Silver alloy, gold flashed
Switching voltage	
Enabling current path	10 V AC ... 230 V AC 10 V DC ... 300 V DC
Current loading	
Enabling current path	10 mA ... 6 A
Total current	≤ 12 A
Usage category	AC-15/DC-13 (EN 60947-5-1)
Rated operating current (voltage)	4 A (230 V AC) 3600 switching cycles/h 5 A (24 V DC) 360 switching cycles/h 3 A (24 V DC) 3600 switching cycles/h 4 A (230 V AC) 360 switching cycles/h 3 A (230 V AC) 3600 switching cycles/h 4 A (24 V DC) 360 switching cycles/h 2.5 A (24 V DC) 3600 switching cycles/h
Switching frequency	≤ 3600 /h
Mechanical life (relay contacts)	5×10^6 switching cycles
Electrical life (relay contacts)	2×10^6 switching cycles

¹⁾ K1/K2.

Mechanics

Dimensions (W x H x D)	22.5 mm x 114 mm x 96.5 mm
Contamination rating	3 (EN 50178)

Weight	+ 0.2 kg
--------	----------


Certificates

EU declaration of conformity	✓
------------------------------	---

Classifications


ECLASS 5.0	27371990
ECLASS 5.1.4	27371990
ECLASS 6.0	27371819
ECLASS 6.2	27371819
ECLASS 7.0	27371819
ECLASS 8.0	27371819
ECLASS 8.1	27371819
ECLASS 9.0	27371819
ECLASS 10.0	27371819
ECLASS 11.0	27371819
ECLASS 12.0	27371819
ETIM 5.0	EC001449
ETIM 6.0	EC001449
ETIM 7.0	EC001449
ETIM 8.0	EC001449
UNSPSC 16.0901	41113704

Dimensional drawing



Dimensions in mm (inch)

Connection diagram



SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com