

# L21S-21MA1A L21

**SAFETY SINGLE-BEAM SENSORS** 





### Ordering information

Scanning range	Model	Housing material	System part	Туре	Part no.
16 m	M18 axial	Nickel-plat- ed brass	Sender	L21S-21MA1A	6034874

Other models and accessories → www.sick.com/L21



#### Detailed technical data

#### **Features**

Light source	LED
Type of light	Visible red light
Scanning range	16 m
Number of beams	1
Optical axis	Axial
Response time	0.2 ms
Response time	0.2 ms + Test device response time

#### Safety-related parameters

Туре	Type 2 (IEC 61496-1) 1)
Safety integrity level	SIL 1 (IEC 61508) 1)
Category	Category 2 (EN ISO 13849) 1)
Test rate (external test)	100 /s (EN ISO 13849) <sup>2)</sup>
Maximum demand rate	≤ 60 min <sup>-1</sup> (EN ISO 13849) <sup>3)</sup>
Performance level	PL c (EN ISO 13849) 1)
$\ensuremath{PFH_D}$ (mean probability of a dangerous failure per hour)	$1.0 \times 10^{-6} (EN ISO 13849)^{-1}$
$T_{\mathrm{M}}$ (mission time)	20 years (EN ISO 13849)

 $<sup>^{1)}\,\</sup>mathrm{Only}$  in combination with an appropriate test device, e.g., Flexi Classic or Flexi Soft.

#### Interfaces

Connection type	Male connector M12, 4-pin, straight
Electrical data	
Protection class	III (IEC 61140)
Sunnly voltage Vo	24 V DC (19 2 V DC 28 8 V DC)

 $<sup>^{2)}</sup>$  The test rate shall not be exceeded.

<sup>3)</sup> Between two requirements on a safety-related response of the device, at least 100 internal or external tests must be carried out.

Power consumption	≤ 20 mA
-------------------	---------

## Mechanical data

Design	Cylindrical
Dimensions (diameter x length)	M18 x 97.7 mm
Housing material	Nickel-plated brass
Lens material	Glass
Weight	67 g

#### Ambient data

Enclosure rating	IP67 (EN 60529)
Ambient operating temperature	-40 °C +55 °C
Storage temperature	-40 °C +75 °C
Air humidity	15 % 95 %, Non-condensing
Vibration resistance	5 g, 10 Hz 55 Hz (IEC 60068-2-6)
Shock resistance	10 g, 16 ms (IEC 60068-2-29)

#### Other information


Light source	LED
Type of light	Visible red light
Wave length	660 nm
Aperture angle/receiving angle	±5°/±5°

#### Classifications

ECLASS 5.0	27272701
ECLASS 5.1.4	27272701
ECLASS 6.0	27272701
ECLASS 6.2	27272701
ECLASS 7.0	27272701
ECLASS 8.0	27272701
ECLASS 8.1	27272701
ECLASS 9.0	27272701
ECLASS 10.0	27272701
ECLASS 11.0	27272701
ECLASS 12.0	27272701
ETIM 5.0	EC001831
ETIM 6.0	EC001831
ETIM 7.0	EC001831
ETIM 8.0	EC001831
UNSPSC 16.0901	46171620

## Dimensional drawing (Dimensions in mm (inch))

M18, axial, straight



#### Recommended accessories

Other models and accessories → www.sick.com/L21

	Brief description	Туре	Part no.	
		Турс	i ait iio.	
Plug connect	Plug connectors and cables			
	<ul> <li>Connection type head A: Female connector, M12, 4-pin, straight, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 5 m, 4-wire, PVC</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Zones with chemicals</li> </ul>	YF2A14-050VB3XLEAX	2096235	
5	<ul> <li>Connection type head A: Female connector, M12, 4-pin, angled, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 5 m, 4-wire, PVC</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Zones with chemicals</li> </ul>	YG2A14-050VB3XLEAX	2095897	
	<ul> <li>Connection type head A: Female connector, M12, 4-pin, straight</li> <li>Description: Unshielded, Head A: female connector, M12, 4-pin, straight, unshielded, for power supply, for cable diameter 4 mm 6 mm Head B: -</li> <li>Connection systems: Screw-type terminals</li> <li>Permitted cross-section: ≤ 0.75 mm²</li> </ul>	DOS-1204-G	6007302	
	<ul> <li>Connection type head A: Female connector, M12, 4-pin, angled</li> <li>Description: Unshielded, Head A: female connector, M12, 4-pin, angled, unshielded, for power supply, for cable diameter 3 mm 6.5 mm Head B: -</li> <li>Connection systems: Screw-type terminals</li> <li>Permitted cross-section: ≤ 0.75 mm²</li> </ul>	DOS-1204-W	6007303	

## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

# **WORLDWIDE PRESENCE:**

Contacts and other locations -www.sick.com

