

UM30-213112 UM30

ULTRASONIC SENSORS





Ordering information

Туре	Part no.
UM30-213112	6037666

Other models and accessories → www.sick.com/UM30



Detailed technical data

Mechanics/electronics

Supply voltage V _s	DC 9 V 30 V ¹⁾
Power consumption	$\leq 2.4 \text{ W}^{2)}$
Initialization time	< 300 ms
Design	Cylindrical
Housing material	Metal (nickel-plated brass, PBT, ultrasonic transducer: polyurethane foam, glass epoxy resin)
Thread size	M30 x 1.5
Connection type	Male connector, M12, 5-pin
Indication	LED display, 2 x LED
Weight	150 g
Sending axis	Straight
Dimensions (W x H x D)	30 mm x 30 mm x 84 mm
Enclosure rating	IP65 / IP67
Protection class	III

 $^{^{1)}}$ Limit values, reverse-polarity protected Operation in short-circuit protected network: max. 8 A, class 2.

Safety-related parameters

MTTF _D	101 years
DC _{avg}	0%

Performance

Operating range, limiting range	200 mm 1,300 mm, 2,000 mm
Target	Natural objects
Resolution	≥ 0.18 mm

 $^{^{1)}}$ In relation to the current measured value, minimum value \geq resolution.

²⁾ Without load.

²⁾ Referring to current measurement value.

 $^{^{3)}}$ Temperature compensation can be switched off, without temperature compensation: 0.17 $\%\,/$ K.

Repeatability	± 0.15 % ¹⁾
Accuracy	± 1 % ^{2) 3)}
Temperature compensation	√
Response time	92 ms
Switching frequency	8 Hz
Output time	23 ms
Ultrasonic frequency (typical)	200 kHz
Detection area (typical)	See diagrams
Additional function	Adjustable operating modes: Switching point (DtO) / Switching window/Background (ObSB) Teach-in of digital output Set levels of digital outputs Invertable digital output Set on delay digital output Synchronization of up to 50 sensors Multiplexing: no cross talk of up to 50 sensors Adjustable measurement filters: Measured value filters/Filter strength/Foreground suppression/Detection area/Sensitivity and sound beam Display (can be deactivated) Reset to factory default

 $^{^{1)}}$ In relation to the current measured value, minimum value \geq resolution.

Interfaces

Digital output	
Number	2 ¹⁾
Туре	PNP
Maximum output current I _A	≤ 200 mA
Multifunctional input (MF)	1 x MF
Hysteresis	20 mm

 $^{^{1)}}$ PNP: HIGH = V_S - (< 2 V) / LOW = 0 V.

Ambient data

Ambient temperature, operation	-25 °C +70 °C
Ambient temperature, storage	-40 °C +85 °C

Classifications

ECLASS 5.0	27270804
ECLASS 5.1.4	27270804
ECLASS 6.0	27270804
ECLASS 6.2	27270804
ECLASS 7.0	27270804
ECLASS 8.0	27270804
ECLASS 8.1	27270804
ECLASS 9.0	27270804
ECLASS 10.0	27270804
ECLASS 11.0	27270804

 $^{^{2)}}$ Referring to current measurement value.

 $^{^{3)}}$ Temperature compensation can be switched off, without temperature compensation: 0.17 % / K.


UM30-213112 | UM30

ULTRASONIC SENSORS

ECLASS 12.0	27272806
ETIM 5.0	EC001846
ETIM 6.0	EC001846
ETIM 7.0	EC001846
ETIM 8.0	EC001846
UNSPSC 16.0901	41111960

Dimensional drawing (Dimensions in mm (inch))

UM30-211, UM30-212, UM30-213



- ① Connection
- ② Display
- 3 Mounting nuts, SW 36 mm

Connection type




Connection diagram

UM30-21x112 UM30-21x115 Connector M12, 5-pin

 $\textcircled{1} \ \ \textbf{Synchronization and multiplex mode, Connect+ communication}$


Adjustment possible



- ② Display
- 4 Control elements
- ⑤ Status indicators

Detection area

Detection area in mm (inch)



- Detection area in mm (inch)
- ① Detection range dependent on reflection properties, size, and alignment of the object
- ② Limiting range
- ③ Operating range
- $\ \, \textcircled{4} \,$ Example object: aligned plate 500 mm x 500 mm
- ⑤ Example object: pipe with 27 mm diameter

Recommended accessories

Other models and accessories → www.sick.com/UM30

	Brief description	Туре	Part no.	
Cloning modu	Cloning modules			
	Tool for visualization, configuration and cloning, 3-digit LED display, supply voltage: DV 9 V 30 V $$	Connect+ adapter (CPA)	6037782	
Mounting brad	Mounting brackets and plates			
40	Mounting bracket for M30 sensors, steel, zinc coated, without mounting hardware	BEF-WN-M30	5308445	
Plug connectors and cables				
	 Connection type head A: Female connector, M12, 5-pin, straight, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 2 m, 5-wire, PVC Description: Sensor/actuator cable, unshielded Application: Zones with chemicals 	YF2A15- 020VB5XLEAX	2096239	

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

