




SSL-2J04-G25ME

Industrial Ethernet cables and fieldbus cables

CONNECTORS AND CABLES

SICK
Sensor Intelligence.



Ordering information

Type	part no.
SSL-2J04-G25ME	6033555

Other models and accessories → www.sick.com/Industrial_Ethernet_cables_and_fieldbus_cables



Detailed technical data

Technical specifications

Connection type head A	Male connector, M12, 4-pin, straight, D-coded
Connection type head B	Male connector, RJ45, 8-pin, straight
Connector material	RJ45: Marcromelt / M12: TPU
Connector color	Black
Locking nut material	CuZn, nickel-plated brass
Tightening torque	0.6 Nm
Cable	25 m, 4-wire, AWG22, PUR, halogen-free
Jacket material	PUR, halogen-free
Jacket color	Green
Cable diameter	6.5 mm
Conductor cross section	0.34 mm ²
Shielding	Shielded
Bending radius	
	Flexible use > 7 x cable diameter
	Stationary position > 3 x cable diameter
Bending cycles	≤ 3,000,000
Reference voltage	
	≤ 50 V
Current loading	1 A
Traversing speed	4 m/s
Acceleration	≤ 4 m/s ²
Signal type	PROFINET
Transmission characteristics	CAT5
Torsion force	± 180° / 1 m
Torsion cycles	30,000
Application	Robot
Enclosure rating	IP67 (M12), IP20 (RJ45) ¹⁾
Specialty	CAT 5e

¹⁾ M12.

Operating temperature		
	Flexible use	-20 °C ... +60 °C
	Stationary position	-40 °C ... +70 °C

1) M12.


Certificates

EU declaration of conformity	✓
China RoHS	✓

Classifications

ECLASS 5.0	19030312
ECLASS 5.1.4	19030312
ECLASS 6.0	27060304
ECLASS 6.2	27060304
ECLASS 7.0	27060304
ECLASS 8.0	27060304
ECLASS 8.1	27060304
ECLASS 9.0	27060304
ECLASS 10.0	27060304
ECLASS 11.0	27060304
ECLASS 12.0	27060304
ETIM 5.0	EC000830
ETIM 6.0	EC000830
ETIM 7.0	EC003249
ETIM 8.0	EC003249
UNSPSC 16.0901	26121604

Dimensional drawing



Dimensions in mm (inch)

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com