

VL180-2N42436 V180-2

CYLINDRICAL PHOTOELECTRIC SENSORS





Ordering information

Туре	Part no.
VL180-2N42436	6037494

Included in delivery: P250 (1)

Other models and accessories → www.sick.com/V180-2

Illustration may differ



Detailed technical data

Features

Functional principle	Photoelectric retro-reflective sensor
runctional principle	FITOLOGICATION TELECTIVE SETISOT
Functional principle detail	Dual lens
Dimensions (W x H x D)	18 mm x 18 mm x 70.2 mm
Housing design (light emission)	Cylindrical
Housing length	70.2 mm
Thread diameter (housing)	M18 x 1
Optical axis	Axial
Sensing range max.	0.05 m 7 m ¹⁾
Sensing range	0.05 m 6 m ¹⁾
Focus	Approx. 4.5°
Type of light	Visible red light
Light source	LED ²⁾
Light spot size (distance)	Ø 400 mm (6 m)
Angle of dispersion	Approx. 4.5°
Wave length	645 nm
Adjustment	Potentiometer, 270° (Sensitivity)

¹⁾ Reflector PL80A.

 $^{^{2)}}$ Average service life: 100,000 h at TU = +25 °C.

Mechanics/electronics

Supply voltage	10 V DC 30 V DC ¹⁾
Ripple	± 10 % ²⁾
Current consumption	30 mA ³⁾
Switching output	NPN ⁴⁾
Switching mode	Light/dark switching ⁴⁾
Switching mode selector	Selectable via L/D control cable
Signal voltage NPN HIGH/LOW	Approx. V_S / < 1.8 V
Output current I _{max} .	≤ 100 mA
Response time	\leq 0.5 ms $^{5)}$
Switching frequency	1,000 Hz ⁶⁾
Connection type	Male connector M12, 4-pin
Circuit protection	A ⁷⁾ B ⁸⁾ D ⁹⁾
Protection class	III
Weight	18 g
Polarisation filter	✓
Housing material	Plastic, PBT/PC
Optics material	Plastic, PMMA
Enclosure rating	IP67
Items supplied	Reflector P250, fastening nuts (2 x)
Ambient operating temperature	-25 °C +55 °C
Ambient temperature, storage	-40 °C +70 °C
UL File No.	NRKH2.E300503 & NRKH8.E300503

 $^{^{1)}\,\}mathrm{Limit}$ values when operated in short-circuit protected network: max. 8 A.

Safety-related parameters

MTTF _D	1,999 years
DC _{avg}	0 %

Classifications

eCl@ss 5.0	27270902
eCl@ss 5.1.4	27270902
eCl@ss 6.0	27270902
eCl@ss 6.2	27270902

 $^{^{2)}}$ May not exceed or fall below U_{V} tolerances.

³⁾ Without load.

⁴⁾ Control wire open: light switching L.ON.

⁵⁾ Signal transit time with resistive load.

⁶⁾ With light/dark ratio 1:1.

 $^{^{7)}}$ A = V_S connections reverse-polarity protected.

⁸⁾ B = inputs and output reverse-polarity protected.

⁹⁾ D = outputs overcurrent and short-circuit protected.

VL180-2N42436 | V180-2

CYLINDRICAL PHOTOELECTRIC SENSORS

	27270902
	27270902
	27270902
	27270902
	27270902
	27270902
	27270902
	EC002717
	EC002717
	EC002717
	EC002717
901	39121528

Connection type




Connection diagram

Cd-087

Characteristic curve


VL180-2, 7 m, axial



- ① Reflector PL80A
- 2 Reflector P250, PL40A, PL50A, C110A
- 3 Reflector PL30A, PL31A
- ④ Reflector PL20A
- ⑤ P45
- ® Reflective tape Diamond Grade


Light spot size

VL180-2




Sensing range diagram

VL180-2, 7 m, axial



- Sensing range
- Sensing range max.
- ① Reflector PL80A
- ② Reflector P250, PL40A, PL50A, C110A
- 3 Reflector PL30A, PL31A
- ④ Reflector PL20A
- ⑤ P45
- ® Reflective tape Diamond Grade


Adjustments




- 3 Sensitivity control 270°
- ④ LED indicator orange: switching output active
- ⑤ LED indicator green

Dimensional drawing (Dimensions in mm (inch))

VL180-2, plastic, axial





- ① M12 male device connector, 4-pin
- ② Connection cable 2 m
- 3 Sensitivity control (potentiometer, 270°)
- 4 LED indicator orange: switching output active
- ⑤ LED indicator green: strength indicator
- 6 Fastening nuts (2 x); A/F 22, PC

Recommended accessories

Other models and accessories → www.sick.com/V180-2

	Brief description	Туре	Part no.
Plug connecto	ors and cables		
	Head A: female connector, M12, 4-pin, straight, A-coded Head B: Flying leads Cable: Sensor/actuator cable, PVC, unshielded, 5 m	YF2A14- 050VB3XLEAX	2096235
Who were	Head A: male connector, M12, 4-pin, straight Cable: unshielded	STE-1204-G	6009932
Reflectors			
	Rectangular, screw connection, 51 mm x 61 mm, PMMA/ABS, Screw-on, 2 hole mounting	P250	5304812

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

