







ULTRASONIC LEVEL SENSOR

ULTRASONIC LEVEL SENSOR



Ordering information

Туре	Part no.
UP56-212112	6041662

Other models and accessories → www.sick.com/UP56



Detailed technical data

Features

Medium	Fluids, bulk solids
Measurement	Switch, Continuous
Measuring range in tank	85 mm 350 mm
Measuring range immersion tube	85 mm 1,500 mm
Process pressure	0 bar 6 bar Gauge pressure
Process temperature	-25 °C +70 °C

Performance

Accuracy of sensor element	≤ 2 % ¹)
Reproducibility	± 0.15 % ¹⁾
Resolution	≤ 0.18 mm
Response time	\leq 84 ms ²⁾
MTTF	> 100 years
Display	✓

 $^{\mbox{1})}$ From the full scale value.

 $^{\rm 2)}$ Recovery time 32 ms ... 180 ms according to EMC EN 60947-5-7.

Electronics

Supply voltage	9 V DC 30 V DC ¹⁾
Residual ripple	± 10 %
Power consumption	\leq 80 mA ²⁾
Protection class	III
Connection type	Round connector M12 x 1, 5-pin
Output signal	2 x PNP

¹⁾ Reverse-polarity protected.

²⁾ At 24 V DC without output load.

ULTRASONIC LEVEL SENSOR

Hysteresis	5 mm
Output current	200 mA
Time delay before availability	≤ 300 ms
Enclosure rating	IP67
Ultrasonic frequency	320 kHz
Ultrasonic transducer	PTFE coating, FFKM

¹⁾ Reverse-polarity protected.

 $^{2)}$ At 24 V DC without output load.

Mechanics

Process connection	G1A
Housing material	Stainless steel 1.4571, PBT, TPU, FKM
Housing design	Standard
Weight	+ 210 g
Ambient data	

Ambient operating temperature	-25 °C +70 °C ¹⁾
Ambient temperature, storage	-40 °C +85 °C

 $^{1)}$ Temperature compensation at –25 °C ... +50 °C, can be switched off.


Classifications

ECLASS 5.0	27200506
ECLASS 5.0	21200300
ECLASS 5.1.4	27200506
ECLASS 6.0	27200506
ECLASS 6.2	27200506
ECLASS 7.0	27200506
ECLASS 8.0	27200506
ECLASS 8.1	27200506
ECLASS 9.0	27200506
ECLASS 10.0	27200506
ECLASS 11.0	27200506
ECLASS 12.0	27200506
ETIM 5.0	EC001447
ETIM 6.0	EC001447
ETIM 7.0	EC001447
ETIM 8.0	EC001447
UNSPSC 16.0901	41111950


Type code

Coverage				
1	30 250 mm			
2	85 350 mm			
3	200 mm 1,300 mm			
4	350 mm 3,400 mm			
6	65 700 mm			

ULTRASONIC LEVEL SENSOR




UP56-211/ 212/ 213



Connection diagram

2 x transistor switching output




Connection type

Male connector M12, 5-pin



Scanning range

Detection range UP56-212118



If the points named above are located in the radiation cone, reliable detection is guaranteed

① Example object: aligned plate 500 mm x 500 mm

③ Pipe diameter 27 mm

Recommended accessories

Other models and accessories → www.sick.com/UP56

	Brief description	Туре	Part no.	
Cloning modu	les			
	Tool for visualization, configuration and cloning, 3-digit LED display, supply voltage: DV 9 V \dots 30 V	Connect+ adapter (CPA)	6037782	
Plug connectors and cables				
×.	 Connection type head A: Female connector, M12, 5-pin, straight, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 2 m, 5-wire, PUR, halogen-free Description: Sensor/actuator cable, unshielded Application: Zones with oils and lubricants, Drag chain operation, Robot 	YF2A15- 020UB5XLEAX	2095617	

ULTRASONIC LEVEL SENSOR

	Brief description	Туре	Part no.
•	 Connection type head A: Female connector, M12, 5-pin, straight, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 2 m, 5-wire, PVC Description: Sensor/actuator cable, unshielded Application: Zones with chemicals 	YF2A15- 020VB5XLEAX	2096239
	 Connection type head A: Female connector, M12, 5-pin, straight, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 5 m, 5-wire, PUR, halogen-free Description: Sensor/actuator cable, unshielded Application: Zones with oils and lubricants, Drag chain operation, Robot 	YF2A15- 050UB5XLEAX	2095618
N	 Connection type head A: Female connector, M12, 5-pin, straight, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 5 m, 5-wire, PVC Description: Sensor/actuator cable, unshielded Application: Zones with chemicals 	YF2A15- 050VB5XLEAX	2096240
	 Connection type head A: Female connector, M12, 5-pin, straight, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 10 m, 5-wire, PUR, halogen-free Description: Sensor/actuator cable, unshielded Application: Zones with oils and lubricants, Drag chain operation, Robot 	YF2A15- 100UB5XLEAX	2095619
\$ 6	 Connection type head A: Female connector, M12, 5-pin, straight, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 10 m, 5-wire, PVC Description: Sensor/actuator cable, unshielded Application: Zones with chemicals 	YF2A15- 100VB5XLEAX	2096241
>	 Connection type head A: Female connector, M12, 5-pin, angled, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 2 m, 5-wire, PUR, halogen-free Description: Sensor/actuator cable, unshielded Application: Zones with oils and lubricants, Drag chain operation, Robot 	YG2A15- O2OUB5XLEAX	2095772
*	 Connection type head A: Female connector, M12, 5-pin, angled, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 2 m, 5-wire, PVC Description: Sensor/actuator cable, unshielded Application: Zones with chemicals 	YG2A15- 020VB5XLEAX	2096215
>	 Connection type head A: Female connector, M12, 5-pin, angled, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 5 m, 5-wire, PUR, halogen-free Description: Sensor/actuator cable, unshielded Application: Zones with oils and lubricants, Drag chain operation, Robot 	YG2A15- 050UB5XLEAX	2095773
*	 Connection type head A: Female connector, M12, 5-pin, angled, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 5 m, 5-wire, PVC Description: Sensor/actuator cable, unshielded Application: Zones with chemicals 	YG2A15- 050VB5XLEAX	2096216
	 Connection type head A: Female connector, M12, 5-pin, angled, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 10 m, 5-wire, PUR, halogen-free Description: Sensor/actuator cable, unshielded Application: Zones with oils and lubricants, Drag chain operation, Robot 	YG2A15- 100UB5XLEAX	2095774

ULTRASONIC LEVEL SENSOR

	Brief description	Туре	Part no.
*	 Connection type head A: Female connector, M12, 5-pin, angled, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 10 m, 5-wire, PVC Description: Sensor/actuator cable, unshielded Application: Zones with chemicals 	YG2A15- 100VB5XLEAX	2096217

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com



Online data sheet

