HF transponder, cylinder

RFID transponder



RFID

HF transponder, cylinder | RFID transponder

RFID



Ordering information

Туре	Part no.
HF transponder, cylinder	6044368

Other models and accessories -> www.sick.com/RFID_transponder

Detailed technical data

Features	
Туре	Hardtag
Frequency band	HF (13.56 MHz)
Carrier frequency	13.56 MHz
RFID standard	ISO/IEC 15693, ISO/IEC 18000-3 "Mode 1"
Read range	
RFH505	1 cm ¹⁾
RFH510	1.8 cm ¹⁾
RFH515	2.3 cm ¹⁾
RFH620	2.5 cm ¹⁾
RFH630	4.5 cm ¹⁾
IC type	NXP ICODE SLIX
Memory capacity (UII / user memory)	896 Bit (28 x 4 Byte)
IC write cycle	≤ 100,000
IC data retention time	< 10 years

¹⁾ Typical value; actual value depends on environmental conditions.

Mechanics/electronics

Housing	Nylon
Housing color	Black
Enclosure rating	IP67
Weight	+ 2.2 g
Dimensions (L x W x H)	30 mm x 5 mm
Diameter	5 mm
Thickness	30 mm
Design	Cylinders
Mounting method	Recessed
Ambient data	
Ambient operating temperature	-40 °C +85 °C ¹⁾

 $^{1)}$ Max. temperature at which the RFID transponder can interact with the RFID read/write device.

HF transponder, cylinder | RFID transponder RFID

Storage temperature	-40 °C +85 °C

 $^{\rm (1)}$ Max. temperature at which the RFID transponder can interact with the RFID read/write device.

Classifications

ECLASS 5.0	27280402
ECLASS 5.1.4	27280402
ECLASS 6.0	27280402
ECLASS 6.2	27280402
ECLASS 7.0	27280402
ECLASS 8.0	27280402
ECLASS 8.1	27280402
ECLASS 9.0	27280402
ECLASS 10.0	27280402
ECLASS 11.0	27280402
ECLASS 12.0	27280402
ETIM 6.0	EC002998
ETIM 7.0	EC002998
ETIM 8.0	EC002998
UNSPSC 16.0901	52161523

Assembly note





Recommended services

Additional services -> www.sick.com/RFID_transponder

	Туре	Part no.
Commissioning		
 Product area: RFID Range of services: Inspection of connection, alignment, optimization of parameters of the RFU/RFH as well as tests, Setup of previously defined functions of reading configuration, data processing and network, interfaces and inputs and outputs Travel expenses: The prices do not include travel costs such as hotel, flight, travel time and expenses. Duration: Additional work will be invoiced separately 	Commissioning RFU/RFH	1610018
Maintenance		
 Product area: RFID Range of services: Inspection, analysis and restoring of defined functions, Checking and adjustment of reading configuration, data processing, network, interfaces and inputs and outputs as well as operating data Duration: Additional work will be invoiced separately Travel expenses: The prices do not include travel costs such as hotel, flight, travel time and expenses. 	Maintenance RFU/RFH	1611424

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com



Online data sheet

