



# TBT-1PBSE1006GZ

TBT

TEMPERATURE SENSORS

**SICK**  
Sensor Intelligence.



Illustration may differ

### Ordering information

| Type            | part no. |
|-----------------|----------|
| TBT-1PBSE1006GZ | 6043126  |

Other models and accessories → [www.sick.com/TBT](http://www.sick.com/TBT)

### Detailed technical data

#### Features

|                        |                    |
|------------------------|--------------------|
| <b>Measuring range</b> | -50 °C ... +250 °C |
| <b>Sensor element</b>  | Pt100              |
| <b>Output signal</b>   | Pt100, 4-wire      |

#### Mechanics/electronics

|                                           |                                                                             |
|-------------------------------------------|-----------------------------------------------------------------------------|
| <b>Communication interface</b>            | -                                                                           |
| <b>Process connection</b>                 | Compression fitting G ½ B, stainless steel ferrule                          |
| <b>Seal</b>                               | Without seal                                                                |
| <b>Insertion length/diameter of probe</b> | 100 mm / 6 mm                                                               |
| <b>Wetted parts</b>                       | Stainless steel 1.4571                                                      |
| <b>Maximum process pressure</b>           | ≤ 100 bar <sup>1)</sup>                                                     |
| <b>Pressure resistance</b>                | Max. 100 bar with supplied compression fitting with stainless steel ferrule |
| <b>Housing material</b>                   | Aluminum                                                                    |
| <b>Connection type</b>                    | Cable gland M16 x 1.5 <sup>2)</sup>                                         |
| <b>Enclosure rating</b>                   | IP65 <sup>3)</sup>                                                          |
| <b>Measuring current</b>                  | 0.3 mA ... 1 mA                                                             |
| <b>Electrical safety</b>                  | Protection class: III, dielectric strength: 500 V AC                        |
| <b>Protection class III</b>               | ✓                                                                           |
| <b>CE-conformity</b>                      | 2004/108/EC, EN 61326-2-3                                                   |
| <b>Weight</b>                             | Ca. 155 g (depending on configuration)                                      |
| <b>Initialization time</b>                | < 1 ms                                                                      |

<sup>1)</sup> Pressure resistance at room temperature.

<sup>2)</sup> The enclosure rating classes specified only apply while the thermometer is connected with female connectors that provide the corresponding enclosure rating.

<sup>3)</sup> IP enclosure rating as per IEC 60529.

#### Performance

|                                   |                                                                 |
|-----------------------------------|-----------------------------------------------------------------|
| <b>Accuracy of sensor element</b> | Class A according to IEC 60751                                  |
| <b>Response time</b>              | $t_{50} \leq 5.8 \text{ s}^1$<br>$t_{90} \leq 15.5 \text{ s}^1$ |

<sup>1)</sup> Depending on sensor configuration, according to IEC 60751.

Ambient data

|                                             |                    |
|---------------------------------------------|--------------------|
| Ambient temperature                         | -40 °C ... +125 °C |
| Storage and transport temperature           | -40 °C ... +60 °C  |
| Shock resistance                            | 500 g (IEC 60751)  |
| Vibration resistance according to IEC 60751 | 3 g                |


Certificates

|            |   |
|------------|---|
| China RoHS | ✓ |
|------------|---|

Classifications


|                |          |
|----------------|----------|
| ECLASS 5.0     | 27200208 |
| ECLASS 5.1.4   | 27200208 |
| ECLASS 6.0     | 27200208 |
| ECLASS 6.2     | 27200208 |
| ECLASS 7.0     | 27200208 |
| ECLASS 8.0     | 27200208 |
| ECLASS 8.1     | 27200208 |
| ECLASS 9.0     | 27200208 |
| ECLASS 10.0    | 27200208 |
| ECLASS 11.0    | 27200208 |
| ECLASS 12.0    | 27200208 |
| ETIM 5.0       | EC002994 |
| ETIM 6.0       | EC002994 |
| ETIM 7.0       | EC002994 |
| ETIM 8.0       | EC002994 |
| UNSPSC 16.0901 | 41112211 |

Dimensional drawing: cylindrical threads




Dimensions in mm (inch)

Dimensional drawing: conical threads




Dimensions in mm (inch)

Dimensional drawing: housing, without process connection



Dimensions in mm (inch)

Connection type Cable entry M16 x 1.5, cable cross-section up to 0.75 mm<sup>2</sup>, output signal Pt100



## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

## WORLDWIDE PRESENCE:

Contacts and other locations –[www.sick.com](http://www.sick.com)