



# VTE180-2N42489

V180

PHOTOELECTRIC SENSORS

**SICK**  
Sensor Intelligence.



Ordering information

| Type           | part no. |
|----------------|----------|
| VTE180-2N42489 | 6043825  |

Other models and accessories → [www.sick.com/V180](http://www.sick.com/V180)

Illustration may differ



Detailed technical data

Features

|                                 |                                     |
|---------------------------------|-------------------------------------|
| Functional principle            | Photoelectric proximity sensor      |
| Functional principle detail     | Energetic                           |
| Dimensions (W x H x D)          | 18 mm x 18 mm x 83.8 mm             |
| Housing design (light emission) | Cylindrical                         |
| Housing length                  | 83.8 mm                             |
| Optical axis                    | Radial                              |
| Sensing range max.              | 1 mm ... 900 mm <sup>1)</sup>       |
| Sensing range                   | 1 mm ... 650 mm <sup>1)</sup>       |
| Focus                           | Approx. 1.2°                        |
| Type of light                   | Visible red light                   |
| Light source                    | LED <sup>2)</sup>                   |
| Light spot size (distance)      | Ø 30 mm (800 mm)                    |
| Angle of dispersion             | Approx. 1.2°                        |
| Wave length                     | 645 nm                              |
| Adjustment                      | Potentiometer, 270° (Sensing range) |

<sup>1)</sup> Object with 90% remission (based on standard white, DIN 5033).

<sup>2)</sup> Average service life: 100,000 h at T<sub>U</sub> = +25 °C.

## Mechanics/electronics

|                                              |                                                               |
|----------------------------------------------|---------------------------------------------------------------|
| <b>Supply voltage <math>U_B</math></b>       | 10 V DC ... 30 V DC <sup>1)</sup>                             |
| <b>Ripple</b>                                | $\pm 10 \%$ <sup>2)</sup>                                     |
| <b>Current consumption</b>                   | 30 mA <sup>3)</sup>                                           |
| <b>Switching output</b>                      | NPN <sup>4)</sup>                                             |
| <b>Switching mode</b>                        | Light/dark switching <sup>4)</sup>                            |
| <b>Signal voltage NPN HIGH/LOW</b>           | Approx. $V_S / < 1.8 \text{ V}$                               |
| <b>Output current <math>I_{\max.}</math></b> | $\leq 100 \text{ mA}$                                         |
| <b>Response time</b>                         | $\leq 0.5 \text{ ms}$ <sup>5)</sup>                           |
| <b>Switching frequency</b>                   | 1,000 Hz <sup>6)</sup>                                        |
| <b>Connection type</b>                       | Male connector M12, 4-pin                                     |
| <b>Circuit protection</b>                    | A <sup>7)</sup><br>B <sup>8)</sup><br>D <sup>9)</sup>         |
| <b>Protection class</b>                      | III                                                           |
| <b>Weight</b>                                | 18 g                                                          |
| <b>Housing material</b>                      | Plastic, PBT/PC                                               |
| <b>Optics material</b>                       | Plastic, PMMA                                                 |
| <b>Enclosure rating</b>                      | IP67                                                          |
| <b>Ambient operating temperature</b>         | $-25 \text{ }^\circ\text{C} \dots +55 \text{ }^\circ\text{C}$ |
| <b>Ambient temperature, storage</b>          | $-40 \text{ }^\circ\text{C} \dots +70 \text{ }^\circ\text{C}$ |

<sup>1)</sup> Limit values when operated in short-circuit protected network: max. 8 A.

<sup>2)</sup> May not fall below or exceed  $U_y$  tolerances.

<sup>3)</sup> Without load.

<sup>4)</sup> Control wire open: light switching L.ON.

<sup>5)</sup> Signal transit time with resistive load.

<sup>6)</sup> With light/dark ratio 1:1.

<sup>7)</sup> A =  $V_S$  connections reverse-polarity protected.

<sup>8)</sup> B = inputs and output reverse-polarity protected.

<sup>9)</sup> D = outputs overcurrent and short-circuit protected.

## Safety-related parameters

|                         |             |
|-------------------------|-------------|
| <b>MTTF<sub>D</sub></b> | 1,999 years |
| <b>DC<sub>avg</sub></b> | 0 %         |


## Certificates

|                                                          |   |
|----------------------------------------------------------|---|
| <b>EU declaration of conformity</b>                      | ✓ |
| <b>UK declaration of conformity</b>                      | ✓ |
| <b>ACMA declaration of conformity</b>                    | ✓ |
| <b>Moroccan declaration of conformity</b>                | ✓ |
| <b>China RoHS</b>                                        | ✓ |
| <b>cULus certificate</b>                                 | ✓ |
| <b>Photobiological safety (DIN EN 62471) certificate</b> | ✓ |

Classifications

|                       |          |
|-----------------------|----------|
| <b>ECLASS 5.0</b>     | 27270903 |
| <b>ECLASS 5.1.4</b>   | 27270903 |
| <b>ECLASS 6.0</b>     | 27270903 |
| <b>ECLASS 6.2</b>     | 27270903 |
| <b>ECLASS 7.0</b>     | 27270903 |
| <b>ECLASS 8.0</b>     | 27270903 |
| <b>ECLASS 8.1</b>     | 27270903 |
| <b>ECLASS 9.0</b>     | 27270903 |
| <b>ECLASS 10.0</b>    | 27270904 |
| <b>ECLASS 11.0</b>    | 27270904 |
| <b>ECLASS 12.0</b>    | 27270903 |
| <b>ETIM 5.0</b>       | EC001821 |
| <b>ETIM 6.0</b>       | EC001821 |
| <b>ETIM 7.0</b>       | EC002719 |
| <b>ETIM 8.0</b>       | EC002719 |
| <b>UNSPSC 16.0901</b> | 39121528 |

Adjustments




- ③ sensitivity control 270°
- ④ LED indicator orange: switching output active
- ⑤ LED indicator green


Connection type




## Connection diagram Cd-087




## Characteristic curve VTE180-2, 900 mm, radial



## Light spot size VTE180-2, 900 mm, 1.100 mm




### Sensing range diagram VTE180-2, 900 mm, radial



■ Sensing range      ■ Sensing range max.

- ① Sensing range on white, 90% remission factor
- ② Sensing range on gray, 18% remission factor
- ③ Sensing range on black, 6% remission factor

### Dimensional drawing VTF180-2, VTE180-2, plastic, radial



Dimensions in mm (inch)

- ① Connector M12
- ② Connection cable 2 m
- ③ sensitivity control: potentiometer 270°
- ④ LED indicator orange: switching output active
- ⑤ LED indicator green, stability indicator: LED lights continuously = light reception < 0.9/> 1.1; LED off = light reception > 0.9 / < 1.1
- ⑥ fastening nuts (2 x); A/F 22, PC

## Recommended accessories

Other models and accessories → [www.sick.com/V180](http://www.sick.com/V180)

|                                                                                                                                                                                                                                                        | Brief description                                                                                                                                                                                                                                                                                                                                                                                                                                                            | Type               | part no. |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------|----------|
| Mounting systems                                                                                                                                                                                                                                       |                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |                    |          |
|                                                                                      | <ul style="list-style-type: none"> <li><b>Description:</b> Mounting bracket for M18 sensors</li> <li><b>Material:</b> Steel</li> <li><b>Details:</b> Steel, zinc coated</li> <li><b>Items supplied:</b> Without mounting hardware</li> <li><b>Suitable for:</b> GR18, V180-2, V18, W15, Z1, Z2</li> </ul>                                                                                                                                                                    | BEF-WN-M18         | 5308446  |
|                                                                                                                                                                                                                                                        | <ul style="list-style-type: none"> <li><b>Description:</b> Plate N11N for universal clamp bracket</li> <li><b>Material:</b> Stainless steel</li> <li><b>Details:</b> Stainless steel 1.4571 (sheet), Stainless steel 1.4408 (clamp)</li> <li><b>Items supplied:</b> Universal clamp (5322627), mounting hardware</li> <li><b>Usable for:</b> DeltaPac, Glare, WTD20E</li> </ul>                                                                                              | BEF-KHS-N11N       | 2071081  |
| connectors and cables                                                                                                                                                                                                                                  |                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |                    |          |
|    | <ul style="list-style-type: none"> <li><b>Connection type head A:</b> Female connector, M12, 4-pin, straight, A-coded</li> <li><b>Connection type head B:</b> Flying leads</li> <li><b>Signal type:</b> Sensor/actuator cable</li> <li><b>Cable:</b> 5 m, 4-wire, PVC</li> <li><b>Description:</b> Sensor/actuator cable, unshielded</li> <li><b>Application:</b> Zones with chemicals, Uncontaminated zones</li> </ul>                                                      | YF2A14-050VB3XLEAX | 2096235  |
|                                                                                                                                                                                                                                                        | <ul style="list-style-type: none"> <li><b>Connection type head A:</b> Male connector, M12, 4-pin, straight, A-coded</li> <li><b>Description:</b> Unshielded</li> <li><b>Connection systems:</b> Screw-type terminals</li> <li><b>Permitted cross-section:</b> ≤ 0.75 mm²</li> </ul>                                                                                                                                                                                          | STE-1204-G         | 6009932  |
|                                                                                                                                                                                                                                                        | <ul style="list-style-type: none"> <li><b>Connection type head A:</b> Female connector, M12, 4-pin, straight, A-coded</li> <li><b>Connection type head B:</b> Flying leads</li> <li><b>Signal type:</b> Sensor/actuator cable</li> <li><b>Cable:</b> 5 m, 4-wire, PUR, halogen-free</li> <li><b>Description:</b> Sensor/actuator cable, unshielded</li> <li><b>Application:</b> Uncontaminated zones, Zones with oils and lubricants, Robot, Drag chain operation</li> </ul> | YF2A14-050UB3XLEAX | 2095608  |

## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

## WORLDWIDE PRESENCE:

Contacts and other locations –[www.sick.com](http://www.sick.com)