





HF Transponder, rectangular, on-metal

HF transponders

RFID TRANSPONDERS

SICK
Sensor Intelligence.



Ordering information

Type	part no.
HF Transponder, rectangular, on-metal	6047938

Other models and accessories → www.sick.com/HF_transponders

Detailed technical data

Features

Product segment	RFID transponders, RFID
Product	HF transponders
Scope	Marking of metal parts
Frequency band	HF (13.56 MHz)
Design	Rectangular
Housing material	ABS
Ambient operating temperature	-25 °C ... +85 °C ¹⁾
Storage temperature	-40 °C ... +85 °C
Housing color	Blue
IC type	NXP ICODE SLIX
Storage capacity	896 Bit (28 x 4 Byte) (User Memory)
IC data retention time	< 10 years
Mounting method	Screws, Rivets
Dimensions (W x H x L)	90 mm x 7 mm x 37 mm
Weight	+ 2.5 g
Reading range	
	RFH505 2 cm ²⁾
	RFH510 2.5 cm ²⁾
	RFH515 4 cm ²⁾
	RFH620 6.5 cm ²⁾
	RFH630 12 cm ²⁾

¹⁾ Max. temperature at which the RFID transponder can interact with the RFID read/write device.



²⁾ Typical value; actual value depends on environmental conditions.

Classifications


ECLASS 5.0	27280401
ECLASS 5.1.4	27280401
ECLASS 6.0	27280401
ECLASS 6.2	27280401
ECLASS 7.0	27280401
ECLASS 8.0	27280401
ECLASS 8.1	27280402

ECLASS 9.0	27280402
ECLASS 10.0	27280402
ECLASS 11.0	27280402
ECLASS 12.0	27280402
ETIM 5.0	EC002593
ETIM 6.0	EC002998
ETIM 7.0	EC002998
ETIM 8.0	EC002998
UNSPSC 16.0901	52161523

Reading field diagram RFH63x



Reading field diagram RFH62x



SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com