



DOL-1205-G05MY

Industrial Ethernet cables and fieldbus cables

CONNECTORS AND CABLES

SICK
Sensor Intelligence.



Illustration may differ



Ordering information

Type	part no.
DOL-1205-G05MY	6053042

Other models and accessories → www.sick.com/Industrial_Ethernet_cables_and_fieldbus_cables

Detailed technical data

Technical specifications

Connection type head A	Female connector, M12, 5-pin, straight
Connection type head B	Flying leads
Connection type	Flying leads
Connector material	TPU
Connector color	Black
Locking nut material	Zinc die-cast, nickel-plated
Cable	5 m, 5-wire
Jacket color	Black
Cable diameter	6.7 mm
Conductor cross section	2 x 0,34 mm ² + 2 x 0,25 mm ² + 1 x 0,34 mm ²
Shielding	Shielded
Bending radius	
Flexible use	> 10 x cable diameter
Stationary position	> 10 x cable diameter
Reference voltage	≤ 60 V
Traversing speed	3 m/s
Travelling distance	4.5 m
Acceleration	≤ 3 m/s ²
Signal type	CANopen, DeviceNet™
Note	A-coded
Enclosure rating	IP65/ IP67/ IP69K
Specialty	Flame-resistant, self-extinguishing
Operating temperature	
Flexible use	−20 °C ... +70 °C
Stationary position	−40 °C ... +80 °C

Certificates


EU declaration of conformity	✓
------------------------------	---

UK declaration of conformity	✓
China RoHS	✓

Classifications

ECLASS 5.0	19030312
ECLASS 5.1.4	19030312
ECLASS 6.0	27060304
ECLASS 6.2	27060304
ECLASS 7.0	27060304
ECLASS 8.0	27060304
ECLASS 8.1	27060304
ECLASS 9.0	27060304
ECLASS 10.0	27060304
ECLASS 11.0	27060304
ECLASS 12.0	27060304
ETIM 5.0	EC000830
ETIM 6.0	EC000830
ETIM 7.0	EC003249
ETIM 8.0	EC003249
UNSPSC 16.0901	26121604

Dimensional drawing




plug connector M12 x1, straight, screened

Dimensions in mm (inch)

- ① Drain wire
- ② Red
- ③ Black
- ④ White
- ⑤ blue

PIN assignment



- ① Drain wire
- ② Red
- ③ Black
- ④ White
- ⑤ blue

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com