



WS/WE100-2N1439 W100-2

MINIATURE PHOTOELECTRIC SENSORS





Ordering information

Туре	Part no.
WS/WE100-2N1439	6052363

Included in delivery: BEF-W100-A (2)

Other models and accessories → www.sick.com/W100-2

Illustration may differ



Detailed technical data

Features

reduited	
Functional principle	Through-beam photoelectric sensor
Dimensions (W x H x D)	11 mm x 31 mm x 20 mm
Housing design (light emission)	Rectangular
Sensing range max.	0 m 33 m
Sensing range	0 m 20 m
Type of light	Visible red light
Light source	LED ¹⁾
Light spot size (distance)	Ø 850 mm (12 m)
Wave length	632 nm
Adjustment	Potentiometer, 270° (Sensitivity)

 $^{^{1)}}$ Average service life: 100,000 h at T_U = +25 °C.

Mechanics/electronics

Supply voltage \mathbf{U}_{B}	10 V DC 30 V DC ¹⁾
Ripple	± 10 % ²⁾
Power consumption, sender	\leq 15 mA $^{3)}$
Power consumption, receiver	≤ 20 mA ³⁾

¹⁾ Limit values.

 $^{^{2)}}$ May not exceed or fall below U_{V} tolerances.

³⁾ Without load.

 $^{^{4)}}$ Signal transit time with resistive load.

⁵⁾ With light/dark ratio 1:1.

⁶⁾ Do not bend below 0 °C.

 $^{^{7)}}$ A = V_S connections reverse-polarity protected.

⁸⁾ B = output reverse-polarity protected.

 $^{^{9)}}$ D = outputs overcurrent and short-circuit protected.

Switching output	NPN
Switching mode	Light/dark switching
Switching mode selector	Selectable via light/dark rotary switch
Signal voltage NPN HIGH/LOW	Approx. V_S / < 1.8 V
Output current I _{max.}	≤ 100 mA
Response time	\leq 0.5 ms $^{4)}$
Switching frequency	1,000 Hz ⁵⁾
Connection type	Cable, 3-wire, 2 m ⁶⁾
Cable material	PVC
Conductor cross section	0.18 mm ²
Circuit protection	A ⁷⁾ B ⁸⁾ D ⁹⁾
Protection class	III
Housing material	Plastic, ABS/PC/POM
Optics material	Plastic, PMMA
Enclosure rating	IP67
Items supplied	2 Stainless steel mounting brackets (1.4301/304) BEF-W100-A
Ambient operating temperature	-25 °C +55 °C
Ambient temperature, storage	-40 °C +70 °C

¹⁾ Limit values.

Safety-related parameters

MTF_D	782 years
DC _{avg}	0 %

Classifications

ECLASS 5.0	27270901
ECLASS 5.1.4	27270901
ECLASS 6.0	27270901
ECLASS 6.2	27270901
ECLASS 7.0	27270901
ECLASS 8.0	27270901
ECLASS 8.1	27270901
ECLASS 9.0	27270901
ECLASS 10.0	27270901
ECLASS 11.0	27270901

 $^{^{2)}}$ May not exceed or fall below U_{V} tolerances.

³⁾ Without load.

⁴⁾ Signal transit time with resistive load.

⁵⁾ With light/dark ratio 1:1.

⁶⁾ Do not bend below 0 °C.

 $^{^{7)}}$ A = V_S connections reverse-polarity protected.

⁸⁾ B = output reverse-polarity protected.


⁹⁾ D = outputs overcurrent and short-circuit protected.

WS/WE100-2N1439 | W100-2

MINIATURE PHOTOELECTRIC SENSORS

ECLASS 12.0	27270901
ETIM 5.0	EC002716
ETIM 6.0	EC002716
ETIM 7.0	EC002716
ETIM 8.0	EC002716
UNSPSC 16.0901	39121528


Dimensional drawing (Dimensions in mm (inch))



- ① Threaded mounting hole M3
- ② Center of optical axis, sender (WS), Center of optical axis, receiver (WE)
- 3 Connection
- ④ LED indicator orange: switching output active
- ⑤ LED indicator green: power on

Adjustments


W100-2



- ① LED indicator orange: switching output active
- ② LED indicator green: power on
- 3 Sensing range adjustment: potentiometer
- 4 Light/ dark rotary switch: L = light switching, D = dark switching

Connection diagram

Cd-049




- ① Sender
- ② Receiver

Characteristic curve

WS/WE100-2





MINIATURE PHOTOELECTRIC SENSORS


Light spot size

Light spot size

Sensing range diagram

Distance in m (feet)

WS/WE100-2



Recommended accessories

Other models and accessories → www.sick.com/W100-2

	Brief description	Туре	Part no.
Mounting bra	ackets and plates		
	Mounting bracket for wall mounting, stainless steel, mounting hardware included	BEF-W100-A	5311520
	Mounting bracket for floor mounting, steel, zinc coated, mounting hardware included	BEF-W100-B	5311521
Plug connect	ors and cables		
	 Connection type head A: Male connector, M8, 3-pin, straight Description: Unshielded Connection systems: Screw-type terminals Permitted cross-section: 0.14 mm² 0.5 mm² 	STE-0803-G	6037322

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

