



ES21-SA14F1

ES21

SAFETY COMMAND DEVICES

SICK
Sensor Intelligence.



Ordering information

| Type | part no. |
|-------------|----------|
| ES21-SA14F1 | 6053943 |

Other models and accessories → www.sick.com/ES21



Detailed technical data

Features

| | |
|-------------------------------------|----------------|
| Positive action N/C contacts | 2 |
| N/O contacts | 1 |
| Actuation directions | 1 |
| Obstruction protection | ✓ |
| Release type | Rotary release |
| Labeling "EMERGENCY STOP" | ✓ |

Safety-related parameters

| | |
|----------------------------------|--|
| B_{10d} parameter | 2.5 x 10 ⁵ switching cycles |
|----------------------------------|--|

Functions

| | |
|-------------------------------|---|
| Safe series connection | None, only individual wiring (with diagnostics) |
|-------------------------------|---|

Interfaces

| | |
|-------------------------|-----------------------|
| Connection type | Cable gland, 2 x M20 |
| Conductor cross section | ≤ 2.5 mm ² |
| Contact | Screw connection |

Electronics - Operating data

| | |
|---|---------------------------------|
| Protection class | II (EN 50178) |
| Switching principle | Slow action switching element |
| Positive action N/C contacts | 2 |
| N/O contacts | 1 |
| Usage category | AC-15/DC-13 (EN 60947-5-1) |
| Rated operating current (voltage) | 3 A (250 V AC) 2 A (24 V DC) |
| Rated insulation voltage U_i | 600 V |
| Switching voltage | ≥ 5 V DC |
| Switching current | ≥ 1 mA |

Mechanics

| | |
|-------------------------|-----------------------|
| Weight | 220 g |
| Housing material | Plastic |
| Mounting version | Surface mount version |

Ambient data

| | |
|--------------------------------------|-------------------|
| Enclosure rating | IP65 (IEC 60529) |
| Ambient operating temperature | -25 °C ... +60 °C |
| Storage temperature | -25 °C ... +85 °C |


Certificates

| | |
|-------------------------------------|---|
| EU declaration of conformity | ✓ |
| UK declaration of conformity | ✓ |
| China RoHS | ✓ |
| Third party certificate | ✓ |

Classifications

| | |
|-----------------------|----------|
| ECLASS 5.0 | 27371228 |
| ECLASS 5.1.4 | 27371228 |
| ECLASS 6.0 | 27371244 |
| ECLASS 6.2 | 27371244 |
| ECLASS 7.0 | 27371244 |
| ECLASS 8.0 | 27371244 |
| ECLASS 8.1 | 27371244 |
| ECLASS 9.0 | 27371244 |
| ECLASS 10.0 | 27371244 |
| ECLASS 11.0 | 27371244 |
| ECLASS 12.0 | 27371244 |
| ETIM 5.0 | EC002034 |
| ETIM 6.0 | EC002034 |
| ETIM 7.0 | EC002034 |
| ETIM 8.0 | EC002034 |
| UNSPSC 16.0901 | 39121545 |

Dimensional drawing Surface mount version



Dimensions in mm (inch)

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com