

SICK Sensor Intelligence.

FORK SENSORS

FORK SENSORS



Ordering information

Туре	Part no.
WF80-95B41CA00	6058613

Other models and accessories → www.sick.com/WF





Detailed technical data

Features

Functional principle	Fork sensor
Functional principle detail	Optical detection principle
Dimensions (W x H x D)	10 mm x 110 mm x 110 mm
Fork width	80 mm
Fork depth	95 mm
Minimum detectable object (MDO)	0.2 mm
Label detection	✓
Light source	LED, infrared
Wave length	850 nm
Adjustment	Teach-in button, cable (Teach-in, sensitivity, light/dark switching, key lock, Teach-in dynamic)
Teach-in mode	1-point teach-in 2-point teach-in Teach-in dynamic
Output function	Light/darkswitching, selectable via button

Mechanics/electronics

Current consumption	20 mA ¹⁾
Switching frequency	15 kHz ²⁾
Response time	46 µs ³⁾

¹⁾ Without load.

²⁾ With light/dark ratio 1:1.

³⁾ Signal transit time with resistive load.

⁴⁾ Reference voltage DC 50 V.

 $^{5)}$ Depending on fork width.

FORK SENSORS

Stability of response time	1 20 40
Stability of response time	± 20 µs
Jitter	17 µs
Switching output	Push-pull: PNP/NPN
Switching output (voltage)	Push-pull: PNP/NPN High = $U_V - \langle 2 V / Low \rangle \leq 2 V$
Switching mode	Light/dark switching
Output current I _{max.}	100 mA
Input, teach-in (ET)	Teach: U > 5 V < U _V Run: U < 4 V
Initialization time	40 ms
Time delay	Switch-off delay, 0 ms / 8 ms / 16 ms / 32 ms / 65 ms / 130 ms / 260 ms / 520 ms, adjustable via IO-Link (0 ms = default)
Connection type	Male connector M8, 4-pin
Protection class	III ⁴)
Circuit protection	U _V connections, reverse polarity protected Output Q short-circuit protected Interference pulse suppression
Enclosure rating	IP65
Weight	Approx. 36 g 160 g ⁵⁾
Housing material	Metal, Aluminum

¹⁾ Without load.

²⁾ With light/dark ratio 1:1.

³⁾ Signal transit time with resistive load.

⁴⁾ Reference voltage DC 50 V.

⁵⁾ Depending on fork width.

Safety-related parameters

MTTF _D	97 years
DCavg	0 %


Communication interface

IO-Link	✓
VendorID	26
DeviceID HEX	8000AE
DeviceID DEC	8388782
Cycle time	2.3 ms
Process data structure A	Bit 0 = switching signal Q_{L1} Bit 1 = switching signal Q_{L2} Bit 2 = not used Bit 3 = Teach busy Bit 4 15 = empty
Process data structure B	Bit 0 = switching signal Q_{L1} Bit 1 = Quality of Run Alarm Bit 2 = not used Bit 3 = Teach busy Bit 4 15 = empty
Process data structure C	Bit 0 = switching signal Q_{L1} Bit 1 = switching signal Q_{L2} Bit 2 = not used Bit 3 = Teach busy Bit 4 5 = empty

FORK SENSORS


Process data structure DBit 0 = switching signal QL1 Bit 1 = Quality of Run Alarm Bit 2 = not used Bit 3 = Teach busy Bit 4 5 = empty Bit 6 15 = measuring valueAmbient dataAmbient light immunity< 10,000 lx		
Bit 1 = Quilty of Run Alarm Bit 2 = nocity Bit 45 = empty Bit		Bit 6 15 = measuring value
Ambient light immunity≤ 10,000 kShock loadAccording to EN 60068-2.27UL File No.NRFH.E191603Smart TaskBase logicsSmart Task nameBase logicsClassifications27270909ECLASS 5.027270909ECLASS 6.027270909ECLASS 6.227270909ECLASS 6.227270909ECLASS 7.027270909ECLASS 8.127270909ECLASS 8.127270909ECLASS 8.127270909ECLASS 8.127270909ECLASS 8.127270909ECLASS 9.027270909ECLASS 1.027270909ECLASS 1.027270909ECLASS 1.027270909ECLASS 1.027270909ECLASS 1.027270909ETIM 5.0EC002720ETIM 5.0EC002720ETIM 5.0EC02720ETIM 5.0EC02720ETIM 5.0EC02720ETIM 5.0EC02720	Process data structure D	Bit 1 = Quality of Run Alarm Bit 2 = not used Bit 3 = Teach busy Bit 4 5 = empty
Shock loadAccording to EN 60068-2-27 NRKH.E191603UL File No.NRKH.E191603Smart TaskBase logicsSmart Task nameBase logicsClassifications27270909ECLASS 5.027270909ECLASS 6.027270909ECLASS 6.027270909ECLASS 6.227270909ECLASS 7.027270909ECLASS 8.127270909ECLASS 8.127270909ECLASS 9.027270909ECLASS 1.027270909ECLASS 1.027270909ECLASS 1.027270909ECLASS 9.027270909ECLASS 1.027270909ECLASS 1.027270909 <t< th=""><th>Ambient data</th><th></th></t<>	Ambient data	
UL File No.NRKH.E191603Smart TaskSmart Task nameBase logicsClassificationsECLASS 5.027270909ECLASS 6.027270909ECLASS 6.027270909ECLASS 6.227270909ECLASS 6.227270909ECLASS 7.027270909ECLASS 8.027270909ECLASS 8.127270909ECLASS 8.027270909ECLASS 8.127270909ECLASS 8.127270909ECLASS 9.027270909ECLASS 9.027270909ECLASS 11.027270909ECLASS 11.027270909ECLASS 11.027270909ETIM 5.0E0002720ETIM 5.0E0002720ETIM 5.0E0002720ETIM 5.0E0002720ETIM 5.0E0002720ETIM 5.0E0002720	Ambient light immunity	≤ 10,000 lx
Smart TaskSmart Task nameBase logicsClassificationsECLASS 5.027270909ECLASS 6.027270909ECLASS 6.227270909ECLASS 6.227270909ECLASS 7.027270909ECLASS 8.027270909ECLASS 8.127270909ECLASS 9.027270909ECLASS 1.027270909ECLASS 1.027270909ECLASS 1.027270909ECLASS 1.027270909ECLASS 1.027270909ECLASS 1.027270909ECLASS 1.027270909ECLASS 1.027270909ETIM 5.0E002720ETIM 5.0E002720ETIM 5.0E002720	Shock load	According to EN 60068-2-27
Smart Task name Base logics Classifications Classifications EcLASS 5.0 27270909 EcLASS 5.1.4 27270909 EcLASS 6.0 27270909 EcLASS 6.2 27270909 EcLASS 6.2 27270909 EcLASS 7.0 27270909 EcLASS 8.1 27270909 EcLASS 8.1 27270909 EcLASS 9.0 27270909 EcLASS 1.0 Eco002720 ETIM 6.0 Eco002720 ETIM 7.0 Eco02720 ETIM 8.0 Eco02720	UL File No.	NRKH.E191603
Classifications EcLass 5.0 27270909 EcLass 5.1.4 27270909 EcLass 6.0 27270909 EcLass 6.2 27270909 EcLass 6.2 27270909 EcLass 7.0 27270909 EcLass 8.1 27270909 EcLass 8.0 27270909 EcLass 8.1 27270909 EcLass 9.0 27270909 EcLass 9.0 27270909 EcLass 10.0 27270909 EcLass 11.0 Eco02720 Erim 5.0 Eco02720 Erim 5.0 Eco02720 Erim 6.0 Eco02720 Erim 8.0 Eco02720	Smart Task	
ECLASS 5.027270909ECLASS 5.1.427270909ECLASS 6.027270909ECLASS 6.227270909ECLASS 7.027270909ECLASS 8.027270909ECLASS 9.027270909ECLASS 9.027270909ECLASS 10.027270909ECLASS 11.027270909ECLASS 12.027270909ETIM 5.0E002720ETIM 5.0E002720ETIM 6.0E002720ETIM 6.0E002720	Smart Task name	Base logics
ECLASS 5.1.427270909ECLASS 6.027270909ECLASS 6.227270909ECLASS 7.027270909ECLASS 8.027270909ECLASS 9.027270909ECLASS 10.027270909ECLASS 11.027270909ECLASS 11.027270909ECLASS 11.027270909ECLASS 12.027270909ETIM 5.0E002720ETIM 6.0E002720ETIM 6.0E002720ETIM 6.0E002720	Classifications	
ECLASS 6.027270909ECLASS 6.227270909ECLASS 7.027270909ECLASS 8.027270909ECLASS 8.127270909ECLASS 9.027270909ECLASS 10.027270909ECLASS 11.027270909ECLASS 12.027270909ETIM 5.0EC02720ETIM 6.0EC02720ETIM 6.0EC02720ETIM 7.0EC02720ETIM 8.0EC02720	ECLASS 5.0	27270909
ECLASS 6.227270909ECLASS 7.027270909ECLASS 8.027270909ECLASS 8.127270909ECLASS 9.027270909ECLASS 10.027270909ECLASS 11.027270909ECLASS 12.027270909ETIM 5.0E002720ETIM 6.0E002720ETIM 7.0E002720ETIM 7.0E002720ETIM 8.0E002720	ECLASS 5.1.4	27270909
EcLASS 7.027270909EcLASS 8.027270909EcLASS 8.127270909EcLASS 9.027270909EcLASS 10.027270909EcLASS 11.027270909EcLASS 12.027270909EtIM 5.0E002720ETIM 6.0E002720ETIM 6.0E002720ETIM 7.0E002720ETIM 8.0E002720	ECLASS 6.0	27270909
EcLass 8.027270909EcLass 8.127270909EcLass 9.027270909EcLass 10.027270909EcLass 11.027270909EcLass 12.027270909EtIM 5.0Ec002720EtIM 6.0Ec002720EtIM 6.0Ec002720EtIM 7.0Ec002720EtIM 8.0Ec002720	ECLASS 6.2	27270909
ECLASS 8.127270909ECLASS 9.027270909ECLASS 10.027270909ECLASS 11.027270909ECLASS 12.027270909ETIM 5.0EC02720ETIM 6.0EC02720ETIM 6.0EC02720ETIM 7.0EC02720ETIM 8.0EC02720	ECLASS 7.0	27270909
ECLASS 9.0 27270909 ECLASS 10.0 27270909 ECLASS 11.0 27270909 ECLASS 12.0 27270909 ETIM 5.0 EC02720 ETIM 6.0 EC02720 ETIM 7.0 EC02720 ETIM 8.0 EC02720	ECLASS 8.0	27270909
ECLASS 10.027270909ECLASS 11.027270909ECLASS 12.027270909ETIM 5.0EC02720ETIM 6.0EC02720ETIM 7.0EC02720ETIM 8.0EC02720	ECLASS 8.1	27270909
ECLASS 11.0 27270909 ECLASS 12.0 27270909 ETIM 5.0 EC02720 ETIM 6.0 EC02720 ETIM 7.0 EC02720 ETIM 8.0 EC02720	ECLASS 9.0	27270909
ECLASS 12.0 27270909 ETIM 5.0 EC002720 ETIM 6.0 EC002720 ETIM 7.0 EC002720 ETIM 8.0 EC002720	ECLASS 10.0	27270909
ETIM 5.0 EC002720 ETIM 6.0 EC002720 ETIM 7.0 EC002720 ETIM 8.0 EC002720	ECLASS 11.0	27270909
ETIM 6.0 EC002720 ETIM 7.0 EC002720 ETIM 8.0 EC002720	ECLASS 12.0	27270909
ETIM 7.0 EC002720 ETIM 8.0 EC002720	ETIM 5.0	EC002720
ETIM 8.0 EC002720	ETIM 6.0	EC002720
	ETIM 7.0	EC002720
UNSPSC 16.0901 39121528	ETIM 8.0	EC002720
	UNSPSC 16.0901	39121528

Dimensional drawing (Dimensions in mm (inch))



Adjustments

Adjustment: teach-in via Teach-in button (WFxx-B41Cxx)



- 1 Function signal indicator (yellow), switching output
- ② Function signal indicator (green)
- ③ Teach-in button and function button

Connection diagram

Cd-273




FORK SENSORS

Concept of operation

Teach-in via Teach-in button (WFxx-B41Cxx)

1. Start teach-in: Position the background or object between the fork



Press the teach-in button for 3 - 20 s. With the pushbutton pressed down, move several objects with carrier material (label objects to be detected) through the sensor. The yellow LED flashes at 3 Hz during the teach-in procedure. Recommendation: Move at least 3 objects through the sensor.

Note

Fine adjustment

In order to obtain a higher operating reserve, a fine adjustment can be carried out after successful teach-in. For this purpose, the switching threshold is set close to the taught-in object. The teach-in button must be pressed and released within 10 s of successful teach-in. Successful setting is signaled by flashing twice at 1 Hz.

Light/dark switching

 \bigcirc

 \bigcirc

You can change between light switching and dark switching by pressing the teach-in button for 20 - 30 s.

Pushbutton lock


The device can be locked against unintended operation by pressing the teach-in button for > 30 s. The device can be unlocked by pressing the teach-in button again for > 30 s.

Recommended accessories

Other models and accessories -> www.sick.com/WF

	Brief description	Туре	Part no.
Cloning modu	les		
	IO-Link version V1.1, Port class 2, PIN 2, 4, 5 galvanically connected, Supply voltage 18 V DC 32 V DC (limit values, operation in short-circuit protected network max. 8 A)	IOLP2ZZ-M3201 (SICK Memory Stick)	1064290

2. End teach-in:



Release the teach-in button for < 20 s. If teach-in is suc-cessful, the function indicator (yellow LED) directly indicates the output state of the sensor. The switching threshold is now optimally set between background and object. The best possible operational safety is provided.

FORK SENSORS

	Brief description	Туре	Part no.
	IO-Link V1.1 Class A port, USB2.0 port, optional external power supply $24V / 1A$	IOLA2US-01101 (SiLink2 Master)	1061790
	EtherCAT IO-Link Master, IO-Link V1.1, Port Class A, power supply via 7/8" cable 24 V $/$ 8 A, fieldbus connection via M12 cable	IOLG2EC-03208R01 (IO-Link Master)	6053254
Plug connecto	rs and cables		
W.	 Connection type head A: Female connector, M8, 4-pin, straight, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 5 m, 4-wire, PVC Description: Sensor/actuator cable, unshielded Application: Zones with chemicals 	YF8U14- 050VA3XLEAX	2095889
N N	 Connection type head A: Female connector, M8, 4-pin, straight, A-coded Connection type head B: Male connector, M12, 4-pin, straight, A-coded Signal type: Sensor/actuator cable Cable: 5 m, 4-wire, PVC Description: Sensor/actuator cable, unshielded Application: Zones with chemicals 	YF8U14- 050VA3M2A14	2096609
	 Connection type head A: Male connector, M8, 4-pin, straight Description: Unshielded Connection systems: Screw-type terminals Permitted cross-section: 0.14 mm² 0.5 mm² 	STE-0804-G	6037323
Sensor Integra	ation Gateway		
	 Further functions: Web server integrated, USB connection for easy configuration of the SIG200 Sensor Integration Gateway with SOPAS ET, the engineering tool from SICK, logic editor is available for easy configuration of logic functions Connection CONFIG: 1 x M8, 4-pin female connector, USB 2.0 (USB-A) Logic editor: yes Communication interface: IO-Link, USB, Ethernet, PROFINET, REST API Product category: IO-Link Master 	SIG200-0A0412200	1089794
1	 Further functions: Web server integrated, USB connection for easy configuration of the SIG200 Sensor Integration Gateway with SOPAS ET, the engineering tool from SICK, logic editor is available for easy configuration of logic functions Connection CONFIG: 1 x M8, 4-pin female connector, USB 2.0 (USB-A) Logic editor: yes Communication interface: IO-Link, USB, Ethernet, REST API Product category: IO-Link Master 	SIG200-0A0G12200	1102605

Recommended services

Additional services -> www.sick.com/WF

	Туре	Part no.
Function Block Factory		
 Description: The Function Block Factory supports common programmable logic controllers (PLCs) from various manufacturers, such as Siemens, Beckhoff, Rockwell Automation and B&R. More information on the FBF can be found here. Note: You can configure your function block at Function Block Factory. As a login please use your SICK ID. 	Function Block Factory	On request

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com



Online data sheet

