



I2D302M-RCA11

picoCam

2D MACHINE VISION

SICK
Sensor Intelligence.



Ordering information

Type	part no.
I2D302M-RCA11	6060391

Other models and accessories → www.sick.com/picoCam



Detailed technical data

Features

Technology	2D snapshot
Product category	Streaming, flexible
Sensor	CMOS monochrome
Sensor used	e2V EV76C570ABT
Shutter technology	Global-Shutter Rolling-Shutter Global-Start-Shutter
Illumination	To be ordered separately as accessories
Further functions	Line mode, Scaler, Sequencer, log mode, Hot pixel correction on the sensor, Fine illumination grid, Multi area of interest, Binning
Lens	C-mount
Optical format	1/1.8"
Note	To be ordered separately as accessories

Mechanics/electronics

Connection type	Hirose 6-pin male connector (voltage supply, 1 digital input, 1 digital output)
Supply voltage	12 V ... 24 V ¹⁾
Power consumption	≤ 2.9 W
Enclosure rating	IP30
Weight	61 g
Dimensions (L x W x H)	40.5 mm x 29 mm x 29 mm

¹⁾ Or PoE.

Performance

Bit depth	12 bit
Sensor resolution	1,600 px x 1,200 px (1.92 Mpixel, 4:3, UXGA)
Sensor size	7.2 mm x 5.4 mm
Scan/frame rate	35.6 fps, in freerun mode 34.4 fps, in trigger mode
Memory	60 MB

Exposure time	0.02 ms ... 10,000 ms
Pixel size	4.5 µm

Interfaces

Ethernet	✓ , UDP/IP
Data transmission rate	1,000 Mbit/s
Configuration software	I2D Software Suite

Ambient data

Shock load	80 g, EN 60068-2-27 (1995-03), EN 60068-2-29 (1995-03)
Vibration load	10 g, 30 Hz ... 500 Hz, EN 60068-2-6 (1996-05)
Ambient operating temperature	0 °C ... +40 °C ¹⁾
Storage temperature	-20 °C ... +60 °C ¹⁾

¹⁾ Relative humidity: 20% ... 80%.

General notes

Note	Not free of paint wetting impairment substances.
-------------	--


Certificates

EU declaration of conformity	✓
ACMA declaration of conformity	✓
China RoHS	✓

Classifications

ECLASS 5.0	27310205
ECLASS 5.1.4	27310205
ECLASS 6.0	27310205
ECLASS 6.2	27310205
ECLASS 7.0	27310205
ECLASS 8.0	27310205
ECLASS 8.1	27310205
ECLASS 9.0	27310205
ECLASS 10.0	27310205
ECLASS 11.0	27310205
ECLASS 12.0	27310205
ETIM 5.0	EC001820
ETIM 6.0	EC001820
ETIM 7.0	EC001820
ETIM 8.0	EC001820
UNSPSC 16.0901	43211731


Dimensional drawing




Dimensions in mm (inch)

- ① blind hole thread M3, 5 mm deep (12 x), for mounting
- ② Fixing hole M3 (2 x), for mounting
- ③ LED for status display (2 x)
- ④ Gigabit Ethernet port, RJ45, 8-pin
- ⑤ Power I/O connection, male connector, M12, 6-pin, Hirose


Field of view



Field of view




Spectral range



Recommended accessories

Other models and accessories → www.sick.com/picoCam

	Brief description	Type	part no.
connectors and cables			
	<ul style="list-style-type: none">• Connection type head A: Male connector, RJ45• Connection type head B: Male connector, RJ45• Signal type: Ethernet• Cable: 3 m, CAT5, CAT5e• Description: Ethernet, Highly flexible, unshielded	SSL-080J-G03MACR	6037974
	<ul style="list-style-type: none">• Connection type head A: Female connector, HR10, 6-pin• Connection type head B: Flying leads• Signal type: Power, I/O• Cable: 5 m• Description: Power, I/O	Connecting cable (female connector – open)	6061064

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com