# UHF Transponder, rectangular, on-metal, ETSI RFID transponder



RFID

# UHF Transponder, rectangular, on-metal, ETSI | RFID transponder





#### **Ordering information**

Туре	Part no.
UHF Transponder, rectangular, on-metal, ETSI	6070746

Other models and accessories -> www.sick.com/RFID\_transponder

### Detailed technical data

### Features

Туре	Hardtag
Frequency band	UHF (860 MHz 960 MHz)
Carrier frequency	865 MHz 868 MHz
RFID standard	EPCglobal UHF Class 1 Generation 2, ISO/IEC 18000-6 C
Read range	
RFU61x	40 cm <sup>1)</sup>
RFU62x	100 cm <sup>1)</sup>
RFU63x/RFU65x	200 cm <sup>1)</sup>
Special features	On Metal, High Temperature <sup>2)</sup>
IC type	Alien Higgs 3
Memory capacity (UII / user memory)	96/512 Bit
IC write cycle	≤ 100,000
IC data retention time	< 50 years

<sup>1)</sup> Typical value; actual value depends on environmental conditions.

<sup>2)</sup> For optimal performance the transponder must be mounted directly onto metal. The metal surface must be of at least the same size as the transporter.

## Mechanics/electronics

Housing	Nylon
Housing color	Black
Enclosure rating	IP68
Weight	5 g
Dimensions (L x W x H)	12.8 mm x 31.7 mm x 4.97 mm
Design	Rectangular
Mounting method	Self-adhesive

### Ambient data

Ambient operating temperature	-30 °C +85 °C <sup>1)</sup>
Application temperature	+ 150 °C, 5 h, Unlimited <sup>2)</sup>
Storage temperature	-30 °C +85 °C

 $^{(1)}$  Max. temperature at which the RFID transponder can interact with the RFID read/write device.

<sup>2)</sup> Max. temperature the RFID transponder can withstand [maximum temperature; duration; cycles]. For optimal performance, the transponders should completely cool off before a new temperature cycle is started.

## Classifications

ECLASS 5.0         27280402           ECLASS 5.1.4         27280402           ECLASS 6.0         27280402           ECLASS 6.2         27280402           ECLASS 6.2         27280402           ECLASS 7.0         27280402           ECLASS 8.0         27280402           ECLASS 8.1         27280402           ECLASS 9.0         27280402 <th></th> <th></th>		
ECLASS 6.027280402ECLASS 6.227280402ECLASS 7.027280402ECLASS 8.027280402ECLASS 8.127280402ECLASS 9.027280402ECLASS 1.0.027280402ECLASS 1.1.027280402ECLASS 1.2.027280402ETIM 6.0E002988ETIM 7.0E002988ETIM 8.0E002988	ECLASS 5.0	27280402
ECLASS 6.227280402ECLASS 7.027280402ECLASS 8.027280402ECLASS 8.127280402ECLASS 9.027280402ECLASS 10.027280402ECLASS 11.027280402ECLASS 12.027280402ETIM 6.0EC02998ETIM 7.0EC02998ETIM 8.0EC02998	ECLASS 5.1.4	27280402
Eclass 7.027280402Eclass 8.027280402Eclass 8.127280402Eclass 9.027280402Eclass 10.027280402Eclass 11.027280402Eclass 12.027280402Etim 6.0Eco2988Etim 7.0Eco2988Etim 8.0Eco2988	ECLASS 6.0	27280402
ECLASS 8.027280402ECLASS 8.127280402ECLASS 9.027280402ECLASS 10.027280402ECLASS 11.027280402ECLASS 12.027280402ETIM 6.0EC02998ETIM 7.0EC02998ETIM 8.0EC02998	ECLASS 6.2	27280402
ECLASS 8.127280402ECLASS 9.027280402ECLASS 10.027280402ECLASS 11.027280402ECLASS 12.027280402ETIM 6.0E002998ETIM 7.0E002998ETIM 8.0E002998	ECLASS 7.0	27280402
ECLASS 9.0       27280402         ECLASS 10.0       27280402         ECLASS 11.0       27280402         ECLASS 12.0       27280402         ETIM 6.0       E002998         ETIM 8.0       E002998	ECLASS 8.0	27280402
ECLASS 10.0       27280402         ECLASS 11.0       27280402         ECLASS 12.0       27280402         ETIM 6.0       EC02998         ETIM 7.0       EC02998         ETIM 8.0       EC02998	ECLASS 8.1	27280402
ECLASS 11.0       27280402         ECLASS 12.0       27280402         ETIM 6.0       EC02998         ETIM 7.0       EC02998         ETIM 8.0       EC02998	ECLASS 9.0	27280402
ECLASS 12.0       27280402         ETIM 6.0       EC002998         ETIM 7.0       EC002998         ETIM 8.0       EC002998	ECLASS 10.0	27280402
ETIM 6.0     EC002998       ETIM 7.0     EC002998       ETIM 8.0     EC002998	ECLASS 11.0	27280402
ETIM 7.0         EC002998           ETIM 8.0         EC002998	ECLASS 12.0	27280402
ETIM 8.0 EC002998	ETIM 6.0	EC002998
	ETIM 7.0	EC002998
UNSPSC 16.0901 52161523	ETIM 8.0	EC002998
	UNSPSC 16.0901	52161523

#### **Recommended services**

Additional services -> www.sick.com/RFID\_transponder

	Туре	Part no.
Commissioning		
<ul> <li>Product area: RFID</li> <li>Range of services: Inspection of connection, alignment, optimization of parameters of the RFU/RFH as well as tests, Setup of previously defined functions of reading configuration, data processing and network, interfaces and inputs and outputs</li> <li>Travel expenses: The prices do not include travel costs such as hotel, flight, travel time and expenses.</li> <li>Duration: Additional work will be invoiced separately</li> </ul>	Commissioning RFU/RFH	1610018
Maintenance		
<ul> <li>Product area: RFID</li> <li>Range of services: Inspection, analysis and restoring of defined functions, Checking and adjustment of reading configuration, data processing, network, interfaces and inputs and outputs as well as operating data</li> <li>Duration: Additional work will be invoiced separately</li> <li>Travel expenses: The prices do not include travel costs such as hotel, flight, travel time and expenses.</li> </ul>	Maintenance RFU/RFH	1611424

# SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

# WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com



Online data sheet

