



# WI180C-IOA00

Interface modules

INTEGRATION MODULES AND ADAPTERS


**SICK**  
Sensor Intelligence.



### Ordering information

Type	part no.
WI180C-IOA00	6071650

Other models and accessories → [www.sick.com/Interface\\_modules](http://www.sick.com/Interface_modules)



### Detailed technical data

#### Features

<b>Product segment</b>	Integration modules and adapters
<b>Product</b>	Interface modules
<b>Description</b>	IO-Link Smart Sensor Gateway for WLL180T, KTL180 and AOD1; Features: IO-Link; COM3; M8 connection, 4-pin; full read/write functionality for the process and service data of the connected sensors. See operating instructions for additional information and technical details
<b>Enclosure rating</b>	IP50
<b>Dimensions (W x H x L)</b>	39 mm x 36.3 mm x 102.35 mm

#### Certificates

<b>EU declaration of conformity</b>	✓
<b>UK declaration of conformity</b>	✓
<b>ACMA declaration of conformity</b>	✓
<b>Moroccan declaration of conformity</b>	✓
<b>China RoHS</b>	✓
<b>cULus certificate</b>	✓
<b>Information according to Art. 3 of Data Act (Regulation EU 2023/2854)</b>	✓

#### Classifications

<b>ECLASS 5.0</b>	27242202
<b>ECLASS 5.1.4</b>	27242602
<b>ECLASS 6.0</b>	27242602
<b>ECLASS 6.2</b>	27242602
<b>ECLASS 7.0</b>	27242602
<b>ECLASS 8.0</b>	27242602
<b>ECLASS 8.1</b>	27242602
<b>ECLASS 9.0</b>	27242602

<b>ECLASS 10.0</b>	27242602
<b>ECLASS 11.0</b>	27242602
<b>ECLASS 12.0</b>	27242602
<b>ETIM 5.0</b>	EC001597
<b>ETIM 6.0</b>	EC001597
<b>ETIM 7.0</b>	EC001597
<b>ETIM 8.0</b>	EC001597
<b>UNSPSC 16.0901</b>	32151705

### Technical data

<b>Features</b>	Supported products	WLL180T fiber amplifiers KTL180 fiber contrast sensors OD1 displacement sensors (via AOD1 amplifier) QL1 displacement sensors (via AOD1 amplifier)	
	Further functions	IO-Link connection for easy configuration of the WI180C-IO Sensor Integration Gateway with SOPAS ET, the engineering tool from SICK	
<b>Mechanics/ Electronics</b>	Supply voltage	10.8 - 26.4 V (SIO), 18 - 26.4 V (IO-Link)	
	Power consumption (without connected devices)	40 mA	
	Switch-on delay	300 ms (connected to one WLL180T/KTL180)	
	Switch-on delay (overall system)	350 ms (connected to 16 WLL180T/KTL180) 2.5 s (connected to one AOD1 with OD1)	
	Optical indicators	1 Green (Power/C) 2 Orange (Q1, Q2)	
	Switching output	Push/Pull	
	Output: QL1 / C	Switching output or IO-Link mode	
	Output current I <sub>max</sub>	≤ 100 mA <sup>6</sup>	
	Pin 2 configuration	External input, Teach-in, switching signal	
	Connection type	Male connector M8, 4-pin	
<b>Safety-related parameters</b>	Circuit protection	A <sup>2</sup> B <sup>3</sup> C <sup>4</sup>	
	Protection class	III	
	Weight	20 g	
	Dimensions (W x H x D)	10.5 mm x 34.6 mm x 71.9 mm	
	Housing material	Plastic, ABS/PC	
	Enclosure rating	IP50 <sup>5</sup>	
	MTTFd	520.7 years	
	DCavg	0%	
	<b>Smart Task</b>	Smart Task name	Base logics (SLTI)
		Logic function	Direct AND OR Window Hysteresis
<b>IO-Link interface</b>	Timer function	Deactivated On delay Off delay ON and OFF delay Impulse (one shot)	
	Inverter	Yes	
	Protocol version	IO-Link V1.1	
	Communication interface detail	COM3 (230.4 kBaud)	
	Cycle time	2.0 ms	
	Process data length	16 bytes	
	Process data structure (5 analog outputs out of 16 modules)	Bit 0 - Bit 1 = QL1 - QL2 Bit 2 - Bit 33 = Module 1 Quint.1 - Module 16 Quint.2 Bit 34 - Bit 47 = Reserved Bit 48 - Bit 63 = Analog output 5 Bit 64 - Bit 79 = Analog output 4 Bit 80 - Bit 95 = Analog output 3 Bit 96 - Bit 111 = Analog output 2 Bit 112 - Bit 127 = Analog output 1	
	Process data structure (7 analog outputs out of 7 modules)	Bit 0 - Bit 1 = QL1 - QL2 Bit 2 - Bit 15 = Module 1 Quint.1 - Module 7 Quint.2 Bit 16 - Bit 31 = Analog output 7 Bit 32 - Bit 47 = Analog output 6 Bit 48 - Bit 63 = Analog output 5 Bit 64 - Bit 79 = Analog output 4 Bit 80 - Bit 95 = Analog output 3 Bit 96 - Bit 111 = Analog output 2 Bit 112 - Bit 127 = Analog output 1	
	Vendor ID	26	
	Device ID HEX	0x80022E	
Device ID DEC	8389166		
<b>Internal system bus</b>	Protocol version	V1	
	Maximum number of connected modules	16	
<b>Ambient data</b>	Electromagnetic compatibility (EMC)	EN 60947-5-2	
	Shock load	500m/s <sup>2</sup> (50G)	
	Ambient operating temperature	-25... +55°C <sup>6</sup>	
	Ambient storage temperature	-40... +70°C	

<sup>2</sup> A = VS connections reverse-polarity protected.

<sup>3</sup> B = inputs and output reverse-polarity protected.

<sup>4</sup> C = interference suppression.

<sup>5</sup> With correctly attached system bus module.

<sup>6</sup> Depending on number of connected sensor devices.



1-3 units: Ambient temperature -25...55°C; max. output current 100mA

4-8 units: Ambient temperature -25...50°C; max. output current 50mA

9-16 units: Ambient temperature -25...45°C; max. output current 20mA


### Dimensions in mm (inch)

**Dimensional drawing**



Dimensions in mm (inch)

**Anschlusschema Cd-447**



## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

## WORLDWIDE PRESENCE:

Contacts and other locations –[www.sick.com](http://www.sick.com)