



# LFC-XXSGTE

LFC

LEVEL SENSORS

**SICK**  
Sensor Intelligence.



## Ordering information

Type	part no.
LFC-XXSGTE	6086409

Other models and accessories → [www.sick.com/LFC](http://www.sick.com/LFC)



## Detailed technical data

### Features

<b>Medium</b>	Fluids
<b>Measurement</b>	Switch
<b>Process pressure</b>	-1 bar ... 64 bar
<b>Process temperature</b>	-20 °C ... +100 °C <sup>1)</sup>

<sup>1)</sup> +135 °C for max. 1 h.

### Performance

<b>Reproducibility</b>	± 1 mm
<b>Response time</b>	500 ms
<b>Dielectricity constant</b>	≥ 2
<b>MTBF</b>	7,3*10 <sup>6</sup> h

### Electronics

<b>Communication interface</b>	IO-Link
<b>Supply voltage</b>	12 V DC ... 35 V DC <sup>1)</sup>
<b>Residual ripple</b>	≤ 5 V <sub>pp</sub>
<b>Power consumption</b>	≤ 10 mA
<b>Protection class</b>	III
<b>Connection type</b>	M12 round connector x 1, 4-pin
<b>Output signal</b>	2 x PNP/NPN, IO-Link
<b>Power consumption</b>	≤ 0.1 W
<b>Contamination rating</b>	4

<sup>1)</sup> All connections are polarity protected. All outputs are overload and short-circuit protected.

<sup>2)</sup> NEMA type 6P.

<b>Inductive load</b>	≤ 0.5 H
<b>Capacitive load</b>	100 nF
<b>Enclosure rating</b>	IP66 IP67 IP69 <sup>2)</sup>
<b>Overvoltage category</b>	I
<b>Load current</b>	≤ 250 mA (Output permanently short-circuit proof)
<b>Voltage drop</b>	< 3 V
<b>Switching voltage</b>	< 34 V DC
<b>Reverse current</b>	< 10 µA
<b>EMC</b>	EN 61326-1

<sup>1)</sup> All connections are polarity protected. All outputs are overload and short-circuit protected.

<sup>2)</sup> NEMA type 6P.

## Mechanics

<b>Wetted parts</b>	PEEK <sup>1)</sup>
<b>Process connection</b>	G ½ A, ISO0228-1, for hygienic thread adapter / 316L (RA < 0.76 µm)
<b>Housing material</b>	Stainless steel 1.4404 / 316L
<b>Sealing material</b>	NBR (male connector)

<sup>1)</sup> Sensor tip PEEK, polished.

## Ambient data

<b>Ambient operating temperature</b>	-40 °C ... +70 °C
<b>Ambient temperature, storage</b>	-40 °C ... +80 °C

## Classifications


<b>ECLASS 5.0</b>	27273290
<b>ECLASS 5.1.4</b>	27273290
<b>ECLASS 6.0</b>	27273290
<b>ECLASS 6.2</b>	27273290
<b>ECLASS 7.0</b>	27273290
<b>ECLASS 8.0</b>	27273290
<b>ECLASS 8.1</b>	27273290
<b>ECLASS 9.0</b>	27273290
<b>ECLASS 10.0</b>	27273290
<b>ECLASS 11.0</b>	27273290
<b>ECLASS 12.0</b>	27200503
<b>ETIM 5.0</b>	EC002654
<b>ETIM 6.0</b>	EC002654
<b>ETIM 7.0</b>	EC002654
<b>ETIM 8.0</b>	EC002654
<b>UNSPSC 16.0901</b>	41111950

## Certificates

<b>EU declaration of conformity</b>	✓
-------------------------------------	---

<b>UK declaration of conformity</b>	✓
<b>ACMA declaration of conformity</b>	✓
<b>FDA certificate</b>	✓
<b>EHEDG approval</b>	✓
<b>cULus certificate</b>	✓
<b>cCSAus certificate</b>	✓
<b>IO-Link certificate</b>	✓
<b>Food contact material manufacturer declaration</b>	✓
<b>Information according to Art. 3 of Data Act (Regulation EU 2023/2854)</b>	✓

Process connection G 1/2, unit: mm (inch), decimal separator: period



Dimensions in mm (inch)

## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

## WORLDWIDE PRESENCE:

Contacts and other locations –[www.sick.com](http://www.sick.com)