



WI180C-IOB01

Interface modules

INTEGRATION MODULES AND ADAPTERS

SICK
Sensor Intelligence.



Ordering information

Type	part no.
WI180C-IOB01	6074861

Other models and accessories → www.sick.com/Interface_modules



Detailed technical data

Features

Product segment	Integration modules and adapters
Product	Interface modules
Description	IO-Link Smart Sensor Gateway for WLL180T, KTL180 and AOD1; Features: IO-Link; COM3; M8 connection, 4-pin; full read/write functionality for the process and service data of the connected sensors. See operating instructions for additional information and technical details
Enclosure rating	IP50
Dimensions (W x H x L)	39 mm x 36.3 mm x 102.35 mm

Certificates

EU declaration of conformity	✓
UK declaration of conformity	✓
ACMA declaration of conformity	✓
Moroccan declaration of conformity	✓
China RoHS	✓
cULus certificate	✓
Information according to Art. 3 of Data Act (Regulation EU 2023/2854)	✓

Classifications

ECLASS 5.0	27242202
ECLASS 5.1.4	27242602
ECLASS 6.0	27242602
ECLASS 6.2	27242602
ECLASS 7.0	27242602
ECLASS 8.0	27242602
ECLASS 8.1	27242602
ECLASS 9.0	27242602

ECLASS 10.0	27242602
ECLASS 11.0	27242602
ECLASS 12.0	27242602
ETIM 5.0	EC001597
ETIM 6.0	EC001597
ETIM 7.0	EC001597
ETIM 8.0	EC001597
UNSPSC 16.0901	32151705

Technical data

Features	Supported products	WLL180T fiber amplifiers KTL180 fiber contrast sensors OD1 displacement sensors (via AOD1 amplifier) OL1 displacement sensors (via AOD1 amplifier)	
	Further functions	IO-Link connection for easy configuration of the WI180C-IO Sensor Integration Gateway with SOPAS ET, the engineering tool from SICK	
Mechanics/ Electronics	Supply voltage	10.8 - 26.4 V (SIO), 18 - 26.4 V (IO-Link)	
	Power consumption (without connected devices)	40 mA	
	Switch-on delay	300 ms (connected to one WLL180T/KTL180)	
	Switch-on delay (overall system)	350 ms (connected to 16 WLL180T/KTL180) 2.5 s (connected to one AOD1 with OD1)	
	Optical indicators	1 Green (Power/C) 2 Orange (Q1, Q2)	
	Switching output	Push/Pull	
	Output: QL1 / C	Switching output or IO-Link mode	
	Output current I _{max}	≤ 100 mA ⁶	
	Pin 2 configuration	External input, Teach-in, switching signal	
	Connection type	Male connector M8, 4-pin	
	Circuit protection	A ² B ³ C ⁴	
	Protection class	III	
	Weight	20 g	
	Dimensions (W x H x D)	10.5 mm x 34.6 mm x 71.9 mm	
Housing material	Plastic, ABS/PC		
Enclosure rating	IP50 ⁵		
Safety-related parameters	MTTFd	520.7 years	
	DCavg	0%	
Smart Task	Smart Task name	Base logics (SLTI)	
	Logic function	Direct AND OR Window Hysteresis	
IO-Link interface	Timer function	Deactivated On delay Off delay ON and OFF delay Impulse (one shot)	
	Inverter	Yes	
	Protocol version	IO-Link V1.1	
	Communication interface detail	COM3 (230.4 kBaud)	
	Cycle time	2.5 ms	
	Process data length	32 bytes	
	Process data structure (3 structures selectable)	Structure 1: Binary switching outputs for 16 modules, analog values for 13 modules out of 16 modules, binary switching outputs QL1 / QL2 for gateway Structure 2: Binary switching outputs for 14 modules, analog values for 14 modules, binary switching outputs QL1 / QL2 for gateway Structure 3: Analog values for 16 modules For detailed process data structure see Quickstart manual 8025499	
	Vendor ID	26	
	Device ID HEX	0x80022E	
	Device ID DEC	8389166	
	Internal system bus	Protocol version	V1
		Maximum number of connected modules	16
	Ambient data	Electromagnetic compatibility (EMC)	EN 60947-5-2
		Shock load	500m/s ² (50G)
Ambient operating temperature		-25 ... +55°C ⁶	
	Ambient storage temperature	-40... +70°C	

² A = VS connections reverse-polarity protected.

³ B = inputs and output reverse-polarity protected.

⁴ C = interference suppression.

⁵ With correctly attached system bus module.

⁶ Depending on number of connected sensor devices.


1-3 units: Ambient temperature -25...55°C; max. output current 100mA

4-8 units: Ambient temperature -25...50°C; max. output current 50mA

9-16 units: Ambient temperature -25...45°C; max. output current 20mA


Dimensions in mm (inch)

Dimensional drawing



Dimensions in mm (inch)

Anschlussschema Cd-447



SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com