



TR110-SRUCAB0

TR110 Lock

SAFETY LOCKING DEVICES

SICK
Sensor Intelligence.



Ordering information

| Type | part no. |
|---------------|----------|
| TR110-SRUCAB0 | 6082950 |

Other models and accessories → www.sick.com/TR110_Lock



Detailed technical data

Features

| | |
|--|------------------------|
| Sensor principle | RFID |
| Locking principle | Power to release |
| Coding | Uniquely coded |
| Locking force F_{max} | |
| With straight actuator | 3,900 N (EN ISO 14119) |
| With angled actuator | 1,500 N (EN ISO 14119) |
| With hinged actuator | 2,600 N (EN ISO 14119) |
| Locking force F_{Zh} | |
| With straight actuator | 3,000 N (EN ISO 14119) |
| With angled actuator | 1,100 N (EN ISO 14119) |
| With hinged actuator | 2,000 N (EN ISO 14119) |
| Actuation force | ≥ 10 N |
| Retaining force | 20 N |
| Force against which unlocking is possible | ≤ 20 N |
| Actuation frequency | ≤ 0.5 Hz |
| Approach speed | ≤ 20 m/min |

Safety-related parameters

| | |
|---|---|
| Safety integrity level | SIL 3 (IEC 61508) |
| Category | Category 4 (EN ISO 13849) ¹⁾ |
| Performance level | PL e (EN ISO 13849) ¹⁾ |
| PFH_D (mean probability of a dangerous failure per hour) | 5.38×10^{-9} ¹⁾ |

¹⁾ Applies for monitoring of the door position (interlocking monitoring) and locking monitoring.

| | |
|---|--|
| T_M (mission time) | 20 years (EN ISO 13849) |
| Type | Type 4 (EN ISO 14119) |
| Actuator coding level | High coding level (EN ISO 14119) |
| Safe state in the event of a fault | At least one safety-related semiconductor output (OSSD) is in the OFF state. |

¹⁾ Applies for monitoring of the door position (interlocking monitoring) and locking monitoring.

Functions

| | |
|--|--|
| Switching behavior of the OSSDs | Locking monitoring |
| Safe series connection | With T-connector (without diagnostics) |

Interfaces

| | |
|-------------------------|---|
| Connection type | Plug connector, M12, 8-pin and plug connector, M12, 5-pin |
| Coupling nut material | Brass |
| Display elements | LEDs |
| Diagnostics indicator | ✓ |
| Status display | ✓ |

Electronics

| | |
|--|---|
| Protection class | III (IEC 61140) |
| Contamination rating | 3 (EN 60947-1) |
| Classification according to cULus | Class 2 |
| Usage category | DC-13 (IEC 60947-5-1) |
| Rated operating current (voltage) | 150 mA (24 V DC) ¹⁾ |
| Rated insulation voltage U_i | 50 V |
| Rated impulse withstand voltage U_{imp} | 500 V |
| Supply voltage V_s | |
| Sensor | 24 V DC (20.4 V DC ... 28.8 V DC) |
| Magnet | 24 V DC (20.4 V DC ... 28.8 V DC) |
| Power consumption | |
| Sensor | 40 mA |
| Magnet | 400 mA |
| Type of output | Self-monitoring semiconductor outputs (OSSDs) |
| Safety outputs | 2 semiconductor outputs (OSSDs), p-switching, short-circuit protected |
| Application diagnostic outputs | P-switching, short-circuit protected |
| Output current | |
| Safety outputs | 1 mA ... 150 mA |
| Application diagnostic outputs | 1 mA ... 50 mA |
| Power consumption of magnet | 6 W |
| Switch-on time of magnet | 100 % |
| Response time | ≤ 260 ms ²⁾ |
| Release time | 150 ms |

¹⁾ In the case of inductive loads, outputs must be protected with a freewheeling diode.

²⁾ 5 ms for each additional switch.

| | |
|--------------------------|--------------------------|
| Switch-on time | 5 s |
| Discrepancy time | 10 ms (EN IEC 60947-5-3) |
| Locking principle | Power to release |

¹⁾ In the case of inductive loads, outputs must be protected with a freewheeling diode.

²⁾ 5 ms for each additional switch.

Mechanics

| | |
|------------------------|--------------------------------------|
| Weight | 0.42 kg |
| Material | |
| Switch head | Zinc diecast |
| Housing | Glass-fiber reinforced thermoplastic |
| Plug connectors | Nickel-plated brass |
| Mechanical life | 1 x 10 ⁶ switching cycles |

Ambient data

| | |
|--------------------------------------|---------------------------------|
| Enclosure rating | IP67 (EN 60529) IP69K |
| Ambient operating temperature | -20 °C ... +55 °C |
| Vibration resistance | 10 Hz ... 55 Hz (IEC 60068-2-6) |
| Shock resistance | 30 g, 11 ms (EN 60068-2-27) |
| EMC | EN IEC 60947-5-3 |

Certificates

| | |
|---------------------------------------|---|
| EU declaration of conformity | ✓ |
| UK declaration of conformity | ✓ |
| ACMA declaration of conformity | ✓ |
| China RoHS | ✓ |
| cULus certificate | ✓ |


Classifications

| | |
|---------------------|----------|
| ECLASS 5.0 | 27272603 |
| ECLASS 5.1.4 | 27272603 |
| ECLASS 6.0 | 27272603 |
| ECLASS 6.2 | 27272603 |
| ECLASS 7.0 | 27272603 |
| ECLASS 8.0 | 27272603 |
| ECLASS 8.1 | 27272603 |
| ECLASS 9.0 | 27272603 |
| ECLASS 10.0 | 27272603 |
| ECLASS 11.0 | 27272603 |
| ECLASS 12.0 | 27272603 |
| ETIM 5.0 | EC002593 |
| ETIM 6.0 | EC002593 |
| ETIM 7.0 | EC002593 |
| ETIM 8.0 | EC002593 |

UNSPSC 16.0901


39122205

Dimensional drawing




Dimensions in mm (inch)

Series connection with T-piece (without diagnostics)



- ① TR110 Lock safety locking device
- ② Connection cable with 8-pin, M12 male connector and 8-pin, M12 female connector (e.g., YF2A18-xxxUA5M2A18)
- ③ T-piece
- ④ Connection cable with 5-pin, M12 male connector and 5-pin, M12 female connector (e.g., YF2A15-xxxUB5M2A15)
- ⑤ connecting cable with M12 female connector, 5-pin and flying leads (e.g., YF2A15-xxxVB5XLEAX)
- ⑥ connecting cable with M12 female connector, 5-pin and flying leads (e.g., YF2A15-xxxVB5XLEAX)
- ⑦ Safe evaluation unit
- ⑧ End plug


Pin assignment



| Pin | Designation | Description |
|-----|-------------|-------------------------------------|
| 1 | Magnet - | Magnet control 0 V DC |
| 2 | AUX DOOR | Door application diagnostic output |
| 3 | AUX DIAG | Error application diagnostic output |
| 4 | Magnet + | Magnet control 24 V DC |
| 5 | n.c. | Not connected |

For details see operating instructions

Pin assignment



| Pin | Designation | Description |
|-----|-------------|---------------------------------------|
| 1 | AUX LOCK | Locking application diagnostic output |
| 2 | +24 V DC | Safety switch voltage supply |
| 3 | Reset | Reset input |
| 4 | In 2 | Enable input for OSSD 2 |
| 5 | OSSD 1 | OSSD 1 output |
| 6 | OSSD 2 | OSSD 2 output |
| 7 | 0 V | 0 V DC voltage supply |
| 8 | In 1 | Enable input for OSSD 1 |

For details see operating instructions

Recommended accessories

Other models and accessories → www.sick.com/TR110_Lock

| | Brief description | Type | part no. |
|---|---|------------|----------|
| actuators and bolts | | | |
|  | <ul style="list-style-type: none"> Product: Actuators for RFID safety switches Description: Actuator angled Items supplied: Including two safety screws M4 | TR110-XABT | 5334663 |
|  | <ul style="list-style-type: none"> Product: Actuators for RFID safety switches Description: Hinged actuators for doors with hinges on left Items supplied: Including two safety screws M5 | TR110-XAFL | 5338331 |
|  | <ul style="list-style-type: none"> Product: Actuators for RFID safety switches Description: Hinged actuators for doors with hinges on right Items supplied: Including two safety screws M5 | TR110-XAFR | 5338332 |
|  | <ul style="list-style-type: none"> Product: Actuators for RFID safety switches Description: Hinged actuators for doors with hinges on top Items supplied: Including two safety screws M5 | TR110-XAFT | 5338336 |
|  | <ul style="list-style-type: none"> Product: Actuators for RFID safety switches Description: Actuator straight Items supplied: Including two safety screws M4 | TR110-XAS | 5321176 |
|  | <ul style="list-style-type: none"> Product: Actuators for RFID safety switches Description: Hinged actuators for doors with hinges on bottom Items supplied: Including two safety screws M5 | TR110-XAFB | 5338338 |

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com