

# SPL-F440PPS1W04

SLG

AUTOMATION LIGHT GRIDS

**SICK**  
Sensor Intelligence.



Illustration may differ



Ordering information

| Type            | part no. |
|-----------------|----------|
| SPL-F440PPS1W04 | 1046314  |

Other models and accessories → [www.sick.com/SLG](http://www.sick.com/SLG)

Detailed technical data

Features

|                                        |                                            |
|----------------------------------------|--------------------------------------------|
| <b>Sensor principle</b>                | Sender/receiver                            |
| <b>Minimum detectable object (MDO)</b> | Parallel beam, 45 mm                       |
| <b>Beam separation</b>                 | 40 mm                                      |
| <b>Optical light exit</b>              | Flat                                       |
| <b>Number of beams</b>                 | 12                                         |
| <b>Detection height</b>                | 440 mm                                     |
| <b>Parameterization</b>                | None                                       |
| <b>Cross beam/parallel beam</b>        | Parallel beam active                       |
| <b>Output 1</b>                        | Output 1 active, if light beam interrupted |
| <b>Muting function</b>                 | Muting function deactivated                |
| <b>Automatic teach</b>                 | Automatic teach active                     |
| <b>Alignment aid</b>                   | Without alignment aid                      |

Mechanics/electronics

|                                             |                      |
|---------------------------------------------|----------------------|
| <b>Light source</b>                         | Infrared light       |
| <b>Wave length</b>                          | 950 nm               |
| <b>Supply voltage <math>V_s</math></b>      | DC24 V, $\pm 20\%$   |
| <b>Power consumption receiver</b>           | $\leq 50\text{ mA}$  |
| <b>Ripple</b>                               | $< 5\text{ V}_{pp}$  |
| <b>Output current <math>I_{max.}</math></b> | $\leq 100\text{ mA}$ |
| <b>Output load, capacitive</b>              | 100 nF               |
| <b>Output load, Inductive</b>               | 1 H                  |
| <b>Initialization time</b>                  | 1 s                  |
| <b>Switching output</b>                     | PNP                  |

|                               |                                                                                                                              |
|-------------------------------|------------------------------------------------------------------------------------------------------------------------------|
| <b>Inputs</b>                 | Job LED                                                                                                                      |
| <b>Dimensions (W x H x D)</b> | 25 mm x 512.4 mm x 8.2 mm                                                                                                    |
| <b>Connection type</b>        | Cable with M8 male connector, 4-pin                                                                                          |
| <b>Housing material</b>       | PMMA                                                                                                                         |
| <b>Display</b>                | LED                                                                                                                          |
| <b>Synchronization</b>        | Optical                                                                                                                      |
| <b>Enclosure rating</b>       | IP65                                                                                                                         |
| <b>Circuit protection</b>     | U <sub>V</sub> connections, reverse polarity protected<br>Output Q short-circuit protected<br>Interference pulse suppression |
| <b>Protection class</b>       | III                                                                                                                          |
| <b>Weight</b>                 | 60 g                                                                                                                         |
| <b>Pulse frequency</b>        | 500 kHz                                                                                                                      |
| <b>Aluminum stabilizer</b>    | Without stabilizer                                                                                                           |

## Performance

|                        |                                    |
|------------------------|------------------------------------|
| <b>Maximum range</b>   | 3 m <sup>1)</sup>                  |
| <b>Minimum range</b>   | Parallel beam: ≥ 0 m <sup>2)</sup> |
| <b>Operating range</b> | 1.5 m                              |
| <b>Response time</b>   | Parallel beam, 19 ms               |

<sup>1)</sup> No reserve for environmental issue and deterioration of the diode.

<sup>2)</sup> Aperture ± 10°.

## Ambient data

|                                      |                                                          |
|--------------------------------------|----------------------------------------------------------|
| <b>Shock resistance</b>              | 10 g / DIN EN 60068-2-29 / 16 ms                         |
| <b>Vibration resistance</b>          | 5 g, 10 Hz ... 55 Hz (IEC 68-2-6)                        |
| <b>EMC</b>                           | EN 60947-5-2                                             |
| <b>Ambient light immunity</b>        | Direct: 100,000 lx <sup>1)</sup><br>Indirect: 150,000 lx |
| <b>Ambient operating temperature</b> | -25 °C ... +55 °C                                        |
| <b>Ambient temperature, storage</b>  | -25 °C ... +70 °C                                        |

<sup>1)</sup> Sunlight.

## Certificates

|                                                                              |   |
|------------------------------------------------------------------------------|---|
| <b>EU declaration of conformity</b>                                          | ✓ |
| <b>UK declaration of conformity</b>                                          | ✓ |
| <b>ACMA declaration of conformity</b>                                        | ✓ |
| <b>Moroccan declaration of conformity</b>                                    | ✓ |
| <b>China RoHS</b>                                                            | ✓ |
| <b>Information according to Art. 3 of Data Act (Regulation EU 2023/2854)</b> | ✓ |


## Classifications

|                     |          |
|---------------------|----------|
| <b>ECLASS 5.0</b>   | 27270910 |
| <b>ECLASS 5.1.4</b> | 27270910 |

|                |          |
|----------------|----------|
| ECLASS 6.0     | 27270910 |
| ECLASS 6.2     | 27270910 |
| ECLASS 7.0     | 27270910 |
| ECLASS 8.0     | 27270910 |
| ECLASS 8.1     | 27270910 |
| ECLASS 9.0     | 27270910 |
| ECLASS 10.0    | 27270910 |
| ECLASS 11.0    | 27270910 |
| ECLASS 12.0    | 27270910 |
| ETIM 5.0       | EC002549 |
| ETIM 6.0       | EC002549 |
| ETIM 7.0       | EC002549 |
| ETIM 8.0       | EC002549 |
| UNSPSC 16.0901 | 39121528 |


Dimensional drawing Sxx-Fxxxxxx1xxx

Flat, without stabilizer




- ① First beam
- ② last beam
- ③ beam separation (RM)
- ④ number of beams (n)
- ⑤ detection height (DH)
- ⑥ Connection

Connection type and diagram



Slim & Flat



Recommended accessories

Other models and accessories → [www.sick.com/SLG](http://www.sick.com/SLG)

|                  | Brief description                                                                                                                                                                                                                                                                                                  | Type         | part no. |
|------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------|----------|
| Mounting systems |                                                                                                                                                                                                                                                                                                                    |              |          |
|                  | <ul style="list-style-type: none"><li>• <b>Description:</b> Mounting bracket for light grids from a detection height of 600 mm (with slot, recommended for compensation of material extension caused by temperature), mounting position: front</li><li>• <b>Items supplied:</b> 2x BEF-SLG1, 2x BEF-SLG2</li></ul> | BEF-SLG-SET1 | 2055427  |

|                                                                                   | Brief description                                                                                                                                                                                                                                                                                                                                                                                                           | Type               | part no. |
|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------|----------|
| connectors and cables                                                             |                                                                                                                                                                                                                                                                                                                                                                                                                             |                    |          |
|  | <ul style="list-style-type: none"><li>• <b>Connection type head A:</b> Female connector, M8, 4-pin, straight, A-coded</li><li>• <b>Connection type head B:</b> Flying leads</li><li>• <b>Signal type:</b> Sensor/actuator cable</li><li>• <b>Cable:</b> 2 m, 4-wire, PVC</li><li>• <b>Description:</b> Sensor/actuator cable, unshielded</li><li>• <b>Application:</b> Untamminated zones, Zones with chemicals</li></ul>   | YF8U14-020VA3XLEAX | 2095888  |
|  | <ul style="list-style-type: none"><li>• <b>Connection type head A:</b> Female connector, M8, 4-pin, straight, A-coded</li><li>• <b>Connection type head B:</b> Flying leads</li><li>• <b>Signal type:</b> Sensor/actuator cable</li><li>• <b>Cable:</b> 0.6 m, 4-wire, PVC</li><li>• <b>Description:</b> Sensor/actuator cable, unshielded</li><li>• <b>Application:</b> Untamminated zones, Zones with chemicals</li></ul> | YF8U14-C60VA3XLEAX | 2145852  |
|  | <ul style="list-style-type: none"><li>• <b>Connection type head A:</b> Female connector, M8, 4-pin, straight, A-coded</li><li>• <b>Connection type head B:</b> Flying leads</li><li>• <b>Signal type:</b> Sensor/actuator cable</li><li>• <b>Cable:</b> 1 m, 4-wire, PVC</li><li>• <b>Description:</b> Sensor/actuator cable, unshielded</li><li>• <b>Application:</b> Untamminated zones, Zones with chemicals</li></ul>   | YF8U14-010VA3XLEAX | 2145853  |

## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

## WORLDWIDE PRESENCE:

Contacts and other locations –[www.sick.com](http://www.sick.com)