



UE410-EN4


Flexi Classic

SAFETY CONTROLLERS

SICK
Sensor Intelligence.



Illustration may differ



Ordering information

| Type | part no. |
|-----------|----------|
| UE410-EN4 | 1044078 |

Other models and accessories → www.sick.com/Flexi_Classic

Detailed technical data

Features

| | |
|-------------------------------------|----------|
| Module | Gateway |
| Fieldbus, industrial network | PROFINET |

Interfaces

| | |
|--|---|
| Connection type | 2 x female connector, RJ-45 |
| Integrated Ethernet switch | 3-port layer-2 managed switch with Auto-MDI-X for automatic detection of crossed Ethernet cable |
| Data transmission rate | (10Base-T) (100Base-T) autosensing |
| Application diagnostic outputs | 4 (X1 - X4) |
| Application diagnostic output connection type | Plug-in screw-type terminals |
| Display elements | LEDs |
| Fieldbus, industrial network | PROFINET |

Electronics

| | |
|-----------------------------------|----------------|
| Protection class | III (EN 61140) |
| Voltage supply | Via FLEXBUS |
| Power consumption | ≤ 2.4 W (DC) |
| Internal power consumption | ≤ 2.4 W (DC) |

Mechanics

| | |
|-------------------------------|------------------------------|
| Dimensions (W x H x D) | 22.5 mm x 96.5 mm x 120.8 mm |
| Weight | + 160 g |

Ambient data

| | |
|-------------------------|--|
| Enclosure rating | |
|-------------------------|--|

| | | |
|--|-----------|---|
| | Housing | IP40 (EN 60529) |
| | Terminals | IP20 (EN 60529) |
| Ambient operating temperature | | -25 °C ... +55 °C |
| Storage temperature | | -25 °C ... +70 °C |
| Air humidity | | ≤ 95 %, Non-condensing |
| Climate conditions according to | | EN 61131-2 (55 °C ambient operating temperature, 95% rel. humidity) |
| Electromagnetic compatibility (EMC) | | Class A (EN 61000-6-2, EN 55011) |
| Vibration resistance | | 5 g RMS, 5 Hz ... 500 Hz (EN 60068-2-64) |


Certificates

| | |
|--|---|
| EU declaration of conformity | ✓ |
| UK declaration of conformity | ✓ |
| ACMA declaration of conformity | ✓ |
| China RoHS | ✓ |
| CCC certificate | ✓ |
| cULus certificate | ✓ |
| Information according to Art. 3 of Data Act (Regulation EU 2023/2854) | ✓ |

Classifications


| | |
|-----------------------|----------|
| ECLASS 5.0 | 27243001 |
| ECLASS 5.1.4 | 27243101 |
| ECLASS 6.0 | 27243101 |
| ECLASS 6.2 | 27243101 |
| ECLASS 7.0 | 27243101 |
| ECLASS 8.0 | 27243101 |
| ECLASS 8.1 | 27243101 |
| ECLASS 9.0 | 27243101 |
| ECLASS 10.0 | 27243101 |
| ECLASS 11.0 | 27243101 |
| ECLASS 12.0 | 27243101 |
| ETIM 5.0 | EC001449 |
| ETIM 6.0 | EC001449 |
| ETIM 7.0 | EC001449 |
| ETIM 8.0 | EC001449 |
| UNSPSC 16.0901 | 32151705 |

Dimensional drawing



Dimensions in mm (inch)

Connection diagram



SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com