



WTD20E-V2414

DeltaPac

PHOTOELECTRIC SENSORS

SICK
Sensor Intelligence.



Illustration may differ

Ordering information

Type	part no.
WTD20E-V2414	1064778

Other models and accessories → www.sick.com/DeltaPac

Detailed technical data

Features

Functional principle	Photoelectric proximity sensor
Dimensions (W x H x D)	42 mm x 42 mm x 45 mm
Housing design (light emission)	Rectangular
Sensing range max.	30 mm ... 35 mm ¹⁾
Sensing range	30 mm ... 35 mm
Type of light	Visible red light
Light source	PinPoint LED ²⁾
Light spot size (distance)	Ø 1 mm (30 mm) ³⁾
Wave length	635 nm
Adjustment	None
Special applications	Zero gap detection
Background suppression	≥ 80 mm
Key feature of the object	Smoothed edges, rounded out body and prism shaped

¹⁾ The sensing range max. refers to the object leading edge. The individual object leading edges must be within the operating range.

²⁾ Average service life: 100,000 h at T_J = +25 °C.

³⁾ 4 x.

Mechanics/electronics

Supply voltage	10 V DC ... 30 V DC ¹⁾
Ripple	< 5 V _{pp} ²⁾
Current consumption	160 mA
Switching output	PNP
Output current I_{max.}	≤ 100 mA ³⁾

¹⁾ Limit values, reverse-polarity protected, operation in short-circuit protected network: max. 8 A.

²⁾ May not exceed or fall below U_v tolerances.

³⁾ 2 switching outputs with I_{max} = 100 mA.

⁴⁾ A = V_S connections reverse-polarity protected.

⁵⁾ B = inputs and output reverse-polarity protected.

⁶⁾ C = interference suppression.

Connection type	Male connector M12, 4-pin
Circuit protection	A ⁴⁾ B ⁵⁾ C ⁶⁾
Protection class	III
Weight	130 g
Housing material	Plastic, Novodur
Enclosure rating	IP67
Ambient operating temperature	-40 °C ... +55 °C
Ambient temperature, storage	-40 °C ... +75 °C
Productivity max.	≤ 54,000 pcs./h
Object speed max.	≤ 1.2 m/s
Radius of the object contour	2 mm ... 5 mm
Switching accuracy	≤ 2 x radius
Repeatability (T_a not constant)	typ. < 1 mm
Switch on delay Q₁ & Q₂	≤ 60 ms
Time delay off Q₁	≤ 60 ms
Object width min.	≥ 20 mm
Object height min.	≥ 50 mm

¹⁾ Limit values, reverse-polarity protected, operation in short-circuit protected network: max. 8 A.

²⁾ May not exceed or fall below U_v tolerances.

³⁾ 2 switching outputs with I_{max} = 100 mA.

⁴⁾ A = V_S connections reverse-polarity protected.


⁵⁾ B = inputs and output reverse-polarity protected.

⁶⁾ C = interference suppression.



Classifications

ECLASS 5.0	27270904
ECLASS 5.1.4	27270904
ECLASS 6.0	27270904
ECLASS 6.2	27270904
ECLASS 7.0	27270904
ECLASS 8.0	27270904
ECLASS 8.1	27270904
ECLASS 9.0	27270904
ECLASS 10.0	27270904
ECLASS 11.0	27270904
ECLASS 12.0	27270903
ETIM 5.0	EC002719
ETIM 6.0	EC002719
ETIM 7.0	EC002719
ETIM 8.0	EC002719
UNSPSC 16.0901	39121528

Connection diagram Cd-243





Characteristic curve, rounded out body and prism shaped, rounded edges, speed



Parameter example, dimensions in mm (inch)

Object width	Object radii	Object speed min.	Object speed max.
200 (7.87)	5 (0.20)	0.25 m/s	3.0 m/s
250 (9.84)	20 (0.79)	0.75 m/s	3.0 m/s

Characteristic curve, productivity





Parameter example, dimensions in mm (inch)

Object width	Object radii	Productivity min.	Productivity max.
200 (7.87)	5 (0.20)	4,500 pc/h	53,500 pc/h
250 (9.84)	20 (0.79)	11,000 pc/h	43,000 pc/h

- = R5, Radii of 5 mm
- = R20, Radii of 20 mm
- = Working range
- = Maximal working range

Characteristic curve, rounded edges, object speed





Parameter example, dimensions in mm (inch)

Object width	Object radii	Object speed min.	Object speed max.
75 (2.95)	2 (0.08)	0.15 m/s	1.1 m/s
125 (4.92)	5 (0.20)	0.25 m/s	1.2 m/s

- = R2, Radii of 2 mm
- = R5, Radii of 5 mm
- = Working range
- = Maximal working range

Characteristic curve, productivity




Parameter example, dimensions in mm (inch)


Object width	Object radii	Productivity min.	Productivity max.
75 (2.95)	2 (0.08)	7,000 pc/h	53,000 pc/h
125 (4.92)	5 (0.20)	7,000 pc/h	34,500 pc/h

- = R2, Radii of 2 mm
- = R5, Radii of 5 mm
- = Working range
- = Maximal working range

Sensing range in detail



Dimensional drawing WTD20E-V/W24xx, connector



Dimensions in mm (inch)

- ① Standard direction
- ② Center of optical axis, sender
- ③ Center of optical axis, receiver (first energy scale)
- ④ Center of optical axis, receiver (second energy scale)
- ⑤ Optical axis, receiver
- ⑥ LED indicator orange: status of received light beam, presence signal Q1
- ⑦ LED indicator green: Supply voltage active
- ⑧ fixing hole
- ⑨ Connection (rotatable)

Recommended accessories

Other models and accessories → www.sick.com/DeltaPac

	Brief description	Type	part no.
Mounting systems			
	<ul style="list-style-type: none"> • Description: Plate N11N for universal clamp bracket • Material: Stainless steel • Details: Stainless steel 1.4571 (sheet), Stainless steel 1.4408 (clamp) • Items supplied: Universal clamp (5322627), mounting hardware • Usable for: DeltaPac, Glare, WTD20E 	BEF-KHS-N11N	2071081

	Brief description	Type	part no.
connectors and cables			
	<ul style="list-style-type: none"> • Connection type head A: Female connector, M12, 4-pin, straight, A-coded • Connection type head B: Flying leads • Signal type: Sensor/actuator cable • Cable: 5 m, 4-wire, PVC • Description: Sensor/actuator cable, unshielded • Application: Uncontaminated zones, Zones with chemicals 	YF2A14-050VB3XLEAX	2096235
	<ul style="list-style-type: none"> • Connection type head A: Male connector, M12, 4-pin, straight, A-coded • Description: Unshielded • Connection systems: Screw-type terminals • Permitted cross-section: ≤ 0.75 mm² 	STE-1204-G	6009932
	<ul style="list-style-type: none"> • Connection type head A: Female connector, M12, 4-pin, straight, A-coded • Connection type head B: Flying leads • Signal type: Sensor/actuator cable • Cable: 5 m, 4-wire, PUR, halogen-free • Description: Sensor/actuator cable, unshielded • Application: Drag chain operation, Zones with oils and lubricants, Robot, Drag chain operation 	YF2A14-050UB3XLEAX	2095608

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com