



WL12-2B560

LICHTSCHRANKEN UND TASTER

SICK
Sensor Intelligence.



Illustration may differ

Ordering information

| Type | part no. |
|------------|----------|
| WL12-2B560 | 1016080 |

Other models and accessories → www.sick.com/

Detailed technical data

Features

| | |
|--|---------------------------------------|
| Functional principle | Photoelectric retro-reflective sensor |
| Dimensions (W x H x D) | 15 mm x 49 mm x 41.5 mm |
| Housing design (light emission) | Rectangular |
| Sensing range max. | 0 m ... 4 m ¹⁾ |
| Sensing range | 0 m ... 3.5 m ¹⁾ |
| Type of light | Visible red light |
| Light source | LED |
| Adjustment | Potentiometer |

¹⁾ Reflector PL80A.

Mechanics/electronics


| | |
|--------------------------------------|------------------------------------|
| Supply voltage | 10 V DC ... 30 V DC |
| Ripple | < 5 V _{pp} |
| Current consumption | 30 mA ¹⁾ |
| Switching mode | Light/dark switching ²⁾ |
| Response time | ≤ 330 μs ³⁾ |
| Connection type | Male connector M12, 5-pin |
| Housing material | Metal, zinc diecast |
| Optics material | Plastic, PMMA |
| Enclosure rating | IP67 |
| Ambient operating temperature | -40 °C ... +60 °C |
| Ambient temperature, storage | -40 °C ... +75 °C |
| UL File No. | NRKH.E181493 & NRKH7.E181493 |

¹⁾ Without load.


²⁾ Control cable 0 V or open-circuited = light switching. Control cable Vs = dark switching.

³⁾ Signal transit time with resistive load.


Connection type




Connection diagram



Characteristic curve




Sensing range diagram




| Reflector type | Operating range |
|-------------------|-----------------|
| 1 PL 80 A | 0 ... 3.5 m |
| 2 C 110 | 0 ... 1.8 m |
| 3 PL 50 A | 0 ... 2.0 m |
| 4 PL 40 A | 0 ... 1.8 m |
| 5 PL 30 A | 0 ... 1.6 m |
| 6 PL 20 A | 0 ... 1.0 m |
| 7 Reflective tape | 0 ... 0.5 m |

Adjustments



- ① Receive indicator
- ⑤ sensitivity control

Dimensional drawing



Dimensions in mm (inch)

- ① LED signal strength indicator
- ② Center of optical axis
- ③ M4 threaded mounting hole – 4 mm depth
- ④ Mounting hole, Ø 4.2 mm
- ⑤ Function selector

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com