



PLB-5370100

PLB

ROBOT GUIDANCE SYSTEMS

SICK
Sensor Intelligence.



Ordering information

Type	part no.
PLB-5370100	1127781

Other models and accessories → www.sick.com/PLB

Detailed technical data

Features

Product version	PLB-530
Field of view	Large
Classification	Prime
Tasks	Position determination
Applications	Robot guidance
Camera type	3D snapshot
Example volume of view (L x W x H)	1200 mm x 800 mm x 800 mm
Image resolution	0.7 mm ... 1 mm, depending on the distance to the camera
Light source	LED, white
LED class	Risk group 2
Localization principle	Geometrical shape and edge localization
Technology	3D snapshot, image analysis

Mechanics/electronics

Connection type	Plug connector, M12, 5-pin
Supply voltage	24 V DC, ± 20 %
Current consumption	5 A
Dimensions (L x W x H)	226 mm x 165 mm x 86 mm
Weight	2 kg
Enclosure rating	IP65

Performance

Part localization time	3 s ... 10 s, typical
Part size	(approx.) > 50 mm x 50 mm x 50 mm
Part characteristics	Simple and complex part shapes

Interfaces

Ethernet	Function	Data output
	Data transmission rate	10/100 MBit/s
	Protocol	TCP/IP (camera)
	Electrical connection	RJ45
USB		

Type	USB 3.0 Typ B
Function	Data transmission

Ambient data

Ambient temperature, operation	0 °C ... +40 °C, Non-condensing
Shock load	15 g / 11 ms ¹⁾
Vibration load	10-150 Hz / 5 g ²⁾

¹⁾ IEC 60068-2-27.

²⁾ IEC 60068-2-6.

General notes

Items supplied	ZOne+ camera PLB Application Software
Factory calibrated	✓

Classifications

ECLASS 5.0	27381501
ECLASS 5.1.4	27381501
ECLASS 6.0	27381590
ECLASS 6.2	27381590
ECLASS 7.0	27381590
ECLASS 8.0	27381590
ECLASS 8.1	27381590
ECLASS 9.0	27381590
ECLASS 10.0	27381590
ECLASS 11.0	27381591
ECLASS 12.0	27381591

Recommended accessories

Other models and accessories → www.sick.com/PLB

	Brief description	Type	part no.
Power supply units and power supply cables			
	Input voltage: ≤ 230 V AC Output voltage: 24 V DC Output current: 10 A Description: Power supply unit	Power supply unit	6032863

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com