




DATA SHEET

CM30-16BNP-EWDS03

CM
Capacitive proximity sensors

SICK

Sensor Intelligence



Illustration may differ

CAPACITIVE PROXIMITY SENSORS

CM30-16BNP-EWDS03

ORDERING INFORMATION

Type	part no.
CM30-16BNP-EWDS03	6080314

Further device versions and accessories at www.sick.com/CM



DETAILED TECHNICAL DATA

FEATURES

Housing	Metric
Thread size	M30 x 1.5
Diameter	Ø 30 mm
Sensing range S_n	3 mm ... 16 mm
Safe sensing range S_a	12.24 mm ¹⁾
Installation type	Flush
Switching frequency	50 Hz
Connection type	Cable with AMP male connector, 3-pin, 0.3 m ²⁾
Switching output	NPN
Switching output detail	NPN
Output function	Complementary
Output characteristic	Wire configurable
Electrical wiring	DC 4-wire
Adjustment	
Potentiometer	Sensitivity (11 turns)
Enclosure rating	IP68 ³⁾ IP69K
Items supplied	Mounting nut, PA12 plastic (2x) Screwdriver for potentiometer adjustment (1 x)

¹⁾ For flush mounting in electrically conductive materials $S_a = 0.8 \times S_r$ at temperatures <0 °C and >60 °C.

²⁾ Do not bend below 0 °C.

³⁾ 1 m water depth / 60 min.

MECHANICS/ELECTRONICS

Supply voltage	10 V DC ... 36 V DC
Ripple	$\leq 10\%$ ¹⁾
Voltage drop	$\leq 2\text{ V DC}$ ²⁾
Current consumption	12 mA ³⁾
Time delay before availability	$\leq 200\text{ ms}$
Hysteresis	3 % ... 20 %
Reproducibility	$\leq 5\%$ ⁴⁾ ⁵⁾
Temperature drift (of S _r)	$\pm 10\%$
EMC	According to EN 60947-5-2
Continuous current I _a	$\leq 200\text{ mA}$
Cable material	PVC
Conductor size	0.34 mm ²
Cable diameter	Ø 5.2 mm
Short-circuit protection	✓
Power-up pulse protection	✓
Shock and vibration resistance	According to EN 60068
Ambient operating temperature	-30 °C ... +85 °C ⁶⁾
Ambient temperature, storage	-40 °C ... +85 °C
Housing material	Plastic, PBT
Housing length	81 mm
Thread length	59.5 mm
Tightening torque, max.	$\leq 7.5\text{ Nm}$
UL File No.	NRKH.E191603

¹⁾ Of U_b.²⁾ At I_a max.³⁾ Without load.⁴⁾ Of S_r.⁵⁾ Supply voltage U_s and constant ambient temperature T_a.⁶⁾ +120 °C short time, at the front of the sensor.**SAFETY-RELATED PARAMETERS**

MTTF ₀	919 years
DC _{avg}	0 %
T _M (mission time)	20 years

REDUCTION FACTORS



Note	The values are reference values which may vary
Metal	1
Water	1
PVC	Approx. 0.4
Oil	Approx. 0.25
Glass	0.6
Ceramics	0.5
Alcohol	0.7
Wood	0.2 ... 0.7

INSTALLATION NOTE

Remark	Associated graphic see "Installation"
B	30 mm
C	30 mm
D	48 mm
F	64 mm

CERTIFICATES




EU declaration of conformity	✓
UK declaration of conformity	✓
Moroccan declaration of conformity	✓
China RoHS	✓
China Compulsory Product Certification (CCC) exempt	✓
cULus certificate	✓

INSTALLATION NOTE FLUSH INSTALLATION**SHOCK AND VIBRATION RESISTANCE**

Shock (IEC 60068-2-27):	30 G / 11ms, 3 pos, 3 neg per axis
Rough handling shocks (IEC 60068-2-31):	2 times from 1m, 100 times from 0,5m
Vibration (IEC 60068-2-6):	10 to 150 Hz, 1 mm / 15 G

ELECTROMAGNETIC COMPATIBILITY (EMC)

Electrostatic discharge (EN61000-4-2):	Contact discharge > 40 kV Air discharge > 40 kV
Electrical fast transients/burst (EN 61000-4-4):	+/- 4 kV
Surge (EN 61000-4-5):	Power supply > 2 kV (with 500 Ohm) Sensor output > 2 kV (with 500 Ohm)
Wire conducted disturbances (EN 61000-4-6):	> 20 Vrms
Power-frequency magnetic fields (EN 61000-4-8):	Continuous > 60 A/m, 75.9 μ tesla Short-time > 600 A/m, 759 μ tesla
Radiated RF electromagnetic fields (EN 61000-4-3):	> 20 V/m

CONNECTION DIAGRAM CD-007**RESPONSE DIAGRAM CM30, FLUSH INSTALLATION****DIMENSIONAL DRAWING CM30, FLUSH, CABLE WITH MALE CONNECTOR**

Dimensions in mm (inch)

- ① fastening nuts (2 x); 36 mm hex, plastic
- ② Cable 4 x 0.34 mm² PVC; Ø 5.2 mm
- ③ Heat-shrink tubing, 25 mm
- ④ Male connector: 1 x housing: AMP no.: 282105-1; 3 x tab contact AMP no.: 282404-1, tin plated pins AWG 20-22; 3 x green seal AMP no.: 0-0281934-4
- ⑤ Potentiometer for sensitivity adjustment
- ⑥ LED yellow: output active
- ⑦ LED green: operating indicator

Further information as well as suitable accessories, example applications and downloads such as CAD dimensional models, operating instructions and software can be found at www.sick.com/6080314



SICK AG
WALDKIRCH
GERMANY
SICK.COM

SICK AT A GLANCE

SICK is a leading global technology company for intelligent sensors and integrated solutions in industrial automation. Our technologies set benchmarks, making your industrial processes more efficient, safer and more sustainable – both in logistics and manufacturing operations.

SICK combines sensor intelligence with industry expertise and certified consulting services. We provide the ideal foundation for scalable as well as tailor-made automation solutions and create added value along the entire value chain. Our close partnerships with our customers are more than just a promise: Together, we optimize productivity, improve quality, protect health and safety, and help build a sustainable future. All with empathy and trust.

Since 1946, we have been developing innovative technologies with passion and a pioneering spirit. With a global network in around 40 countries, SICK has a global presence and is always close by. The company's headquarters are located in Waldkirch near Freiburg, Germany. Our customers benefit from our understanding of both local and global requirements, which enables us to deliver tailor-made solutions

SICK
Sensor Intelligence