



DATA SHEET

UM12-1192271

UM12
Ultrasonic distance sensors

SICK Sensor Intelligence



ULTRASONIC DISTANCE SENSORS

UM12-1192271

ORDERING INFORMATION

Type	part no.
UM12-1192271	6053549

Further device versions and accessories at www.sick.com/UM12



DETAILED TECHNICAL DATA

FEATURES

Operating range, limiting range	40 mm ... 240 mm, 350 mm
Resolution	≥ 0.069 mm
Repeatability	± 0.15 % ¹⁾
Measurement accuracy	± 1 % ²⁾
Temperature compensation	✓
Response time	30 ms ³⁾
Output time	10 ms
Ultrasonic frequency (typical)	500 kHz
Additional function	Teach-in of analog output, Invertable analog output, reset to factory default ⁴⁾
Safety-related parameters	MTTF _D 101 years DC _{avg} 0%

¹⁾ In relation to the current measured value, minimum value ≥ resolution.
²⁾ Referring to current measurement value.
³⁾ Subsequent smoothing of the analog output, depending on the application, may increase the response time by up to 200 %.
⁴⁾ Functions may vary depending on sensor type.

INTERFACES

Analog output	Number 1 Type Voltage output Voltage 0 V ... 10 V, ≥ 100,000 Ω Resolution 12 bit
---------------	---

ELECTRONICS

Supply voltage U_B	DC 15 V ... 30 V ¹⁾
Power consumption	$\leq 1.2 \text{ W}$ ²⁾
Initialization time	< 300 ms
Display	2 x LED
Enclosure rating	IP65 / IP67
Protection class	III

¹⁾ Limit values, reverse-polarity protected Operation in short-circuit protected network: max. 8 A, class 2.

²⁾ Without load.

MECHANICS

Dimensions (W x H x D)	12 mm x 12 mm x 60.1 mm
Design	Cylindrical
Sending axis	Straight
Housing material	Metal (nickel-plated brass, PBT, ultrasonic transducer: polyurethane foam, glass epoxy resin)
Weight	15 g
Thread size	M12 x 1
Connection type	Male connector, M12, 4-pin


AMBIENT DATA

Ambient temperature, operation	-25 °C ... +70 °C
Ambient temperature, storage	-40 °C ... +85 °C

CERTIFICATES

EU declaration of conformity	✓
UK declaration of conformity	✓
ACMA declaration of conformity	✓
Moroccan declaration of conformity	✓
China RoHS	✓
China Compulsory Product Certification (CCC) exempt	✓
cULus certificate	✓

DIMENSIONAL DRAWING UM12-11X2261, UM12-11X2271




Dimensions in mm (inch)

① Connection


② Mounting nuts, SW 17 mm

③ Status indicator supply voltage active (green), switching and analog output (orange)

CONNECTION TYPE




CONNECTION DIAGRAM UM12-11X2261, UM12-11X2271



DETECTION AREA UM12-119

Detection area in mm (inch)



- ① Detection range dependent on reflection properties, size, and alignment of the object
- ② Limiting range
- ③ operating range
- ④ example object: aligned plate 500 mm x 500 mm
- ⑤ Example object: cylindrical bar with a diameter of 10 mm

Further information as well as suitable accessories, example applications and downloads such as CAD dimensional models, operating instructions and software can be found at www.sick.com/6053549



SICK AG
WALDKIRCH
GERMANY
SICK.COM

SICK AT A GLANCE

SICK is a leading global technology company for intelligent sensors and integrated solutions in industrial automation. Our technologies set benchmarks, making your industrial processes more efficient, safer and more sustainable – both in logistics and manufacturing operations.

SICK combines sensor intelligence with industry expertise and certified consulting services. We provide the ideal foundation for scalable as well as tailor-made automation solutions and create added value along the entire value chain. Our close partnerships with our customers are more than just a promise: Together, we optimize productivity, improve quality, protect health and safety, and help build a sustainable future. All with empathy and trust.

Since 1946, we have been developing innovative technologies with passion and a pioneering spirit. With a global network in around 40 countries, SICK has a global presence and is always close by. The company's headquarters are located in Waldkirch near Freiburg, Germany. Our customers benefit from our understanding of both local and global requirements, which enables us to deliver tailor-made solutions

SICK
Sensor Intelligence