


Twinhead CLV690 OSCM

CLV Identification System

TRACK AND TRACE SYSTEMS

SICK
Sensor Intelligence.



Ordering information

Type	part no.
Twinhead CLV690 OSCM	1061480

Other models and accessories → www.sick.com/CLV_Identification_System



Detailed technical data

Features

Products by tasks	Identifying - 1D code
Covered conveyor width	800 mm
Focus	Auto focus
MTBF	100,000 h
MTTR	5 min
Conveyor type	Belt conveyor Tilt-tray sorter Roller conveyor Cross-belt sorter Pallet
Object infeed and outfeed	Automatic
Covered side of object	Single side reading

Mechanics/electronics

Dimensions, system (L x W x H)	1,100 mm x 1,280 mm x 1,745 mm
Connection modules	CDM420-0007
Mirror module	✓

Performance

Code types	1D
Transport speed	0 m/s ... 0.5 m/s, Depending on code height
Minimum object distance	50 mm
Number of codes per reading interval	1 ... 50
Module width	0.3 mm ... 0.5 mm
1D code resolution	0.3 mm ... 0.5 mm

Interfaces

Type	RS-232, RS-422/-485, PROFIBUS, PROFINET
Function	Data interface (read result output) Service interface
Data transmission rate	SICK CAN sensor network (CAN controller/CAN device) Host: 300 baud ... 500 kBaud, AUX: 57.6 kBaud fixed 10/100 MBit/s 20 kbit/s ... 1 Mbit/s

	Protocol	TCP/IP CSN (SICK CAN Sensor Network)
Number		1, 1, 2, 1
Remark		Depending on the cloning plug used, Optional over external fieldbus module (CDF)
Optical indicators		6, LEDs, Ready, Result, laser, Data, CAN, LNK TX, bar graph display of percentage read rates (10 LEDs)

Ambient data

Ambient operating temperature	0 °C ... +40 °C
Ambient temperature, storage	-20 °C ... +70 °C

General notes

Items supplied	Barcode scanner CLV690 with oscillating mirror (2x) Cloning plug for barcode scanner CLV690 (2x) Bracket for bar code scanner (2x) Photoelectric sensor (2x) Connection module CDM420-0007 (1x) Connection cable for barcode scanner to connection module (2 x)
Laser class	2 (IEC 60825-1:2014) 1 (IEC 60825-1:2014)


Certificates

EU declaration of conformity	✓
UK declaration of conformity	✓
China RoHS	✓
Information according to Art. 3 of Data Act (Regulation EU 2023/2854)	✓

Classifications

ECLASS 5.0	27280102
ECLASS 5.1.4	27280102
ECLASS 6.0	27280102
ECLASS 6.2	27280102
ECLASS 7.0	27280102
ECLASS 8.0	27280102
ECLASS 8.1	27280102
ECLASS 9.0	27280102
ECLASS 10.0	27280102
ECLASS 11.0	27280102
ECLASS 12.0	27280102
ETIM 5.0	EC002550
ETIM 6.0	EC002550
ETIM 7.0	EC002550
ETIM 8.0	EC002550
UNSPSC 16.0901	43211701

Dimensional drawing Twinhead CLV65x and Twinhead CLV69x



SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com