



DATA SHEET

IMP14-03BPSVC0S

IMP
Inductive proximity sensors

SICK

Sensor Intelligence



Illustration may differ

INDUCTIVE PROXIMITY SENSORS

IMP14-03BPSVC0S

ORDERING INFORMATION

Type	part no.
IMP14-03BPSVC0S	6050137

Further device versions and accessories at www.sick.com/IMP



DETAILED TECHNICAL DATA

FEATURES

Housing	Metric
Thread size	M14 x 1.5
Diameter	Ø 14 mm
Pressure resistance	≤ 500 bar
Sensing range S _n	3 mm
Safe sensing range S _a	2.4 mm
Installation type	Flush
Switching frequency	500 Hz
Connection type	Male connector M12, 4-pin
Switching output	PNP
Switching output detail	PNP
Output function	NO
Electrical wiring	DC 3-wire
Enclosure rating	IP68 ¹⁾
Special features	High pressure resistant
Special applications	Hydraulic application

¹⁾ Sensing face.

MECHANICS/ELECTRONICS

Supply voltage	10 V DC ... 30 V DC
Ripple	$\leq 20\%$ ¹⁾
Voltage drop	$\leq 2\text{ V}$ ²⁾
Time delay before availability	$\leq 50\text{ ms}$
Hysteresis	1 % ... 15 % ³⁾
Reproducibility	$\leq 4\%$ ⁴⁾ ⁵⁾
Temperature drift (of S _p)	15 %
EMC	According to EN 60947-5-2 ⁶⁾
Continuous current I _a	$\leq 200\text{ mA}$
Vacuum resistance	10 ⁻⁸ Torr ⁷⁾
Large sealing ring	11.5 mm x 2.0 mm
Short-circuit protection	✓
Shock and vibration resistance	30 g, 11 ms / 10 ... 55 Hz, 1 mm
Ambient operating temperature	-25 °C ... +80 °C
Housing material	Stainless steel V4A, DIN 1.4404 / AISI 316L
Sensing face material	Ceramics, ZrO ₂
Sealing ring material	NBR
Housing length	65 mm
Thread length	11 mm
Tightening torque, max.	$\leq 70\text{ Nm}$

¹⁾ Of V_s.²⁾ With I_a = 200 mA.³⁾ Typ. 8%.⁴⁾ U_b = 20 ... 30 VDC.⁵⁾ T_a = 23 °C ± 5 °C.⁶⁾ IEC61000-4-4; 1kV.⁷⁾ Front.**SAFETY-RELATED PARAMETERS**

MTTF _D	156 years
DC _{avg}	0 %
T _M (mission time)	20 years

REDUCTION FACTORS

Note	The values are reference values which may vary
St37 steel (Fe)	1
Stainless steel (V2A, 304)	Approx. 0.85
Aluminum (Al)	Approx. 0
Copper (Cu)	Approx. 0
Brass (Br)	Approx. 0.15

INSTALLATION NOTE


Remark	Associated graphic see "Installation"
B	12 mm

C	14 mm
D	9 mm
F	20 mm


CERTIFICATES



EU declaration of conformity	✓
UK declaration of conformity	✓
Moroccan declaration of conformity	✓
China RoHS	✓
China Compulsory Product Certification (CCC) exempt	✓

INSTALLATION NOTE



INSTALLATION NOTE FLUSH INSTALLATION



CONNECTION DIAGRAM CD-007**DIMENSIONAL DRAWING**

Dimensions in mm (inch)

① male connector M12, 4-pin

② width across 19

Further information as well as suitable accessories, example applications and downloads such as CAD dimensional models, operating instructions and software can be found at www.sick.com/6050137



SICK AG
WALDKIRCH
GERMANY
SICK.COM

SICK AT A GLANCE

SICK is a leading global technology company for intelligent sensors and integrated solutions in industrial automation. Our technologies set benchmarks, making your industrial processes more efficient, safer and more sustainable – both in logistics and manufacturing operations.

SICK combines sensor intelligence with industry expertise and certified consulting services. We provide the ideal foundation for scalable as well as tailor-made automation solutions and create added value along the entire value chain. Our close partnerships with our customers are more than just a promise: Together, we optimize productivity, improve quality, protect health and safety, and help build a sustainable future. All with empathy and trust.

Since 1946, we have been developing innovative technologies with passion and a pioneering spirit. With a global network in around 40 countries, SICK has a global presence and is always close by. The company's headquarters are located in Waldkirch near Freiburg, Germany. Our customers benefit from our understanding of both local and global requirements, which enables us to deliver tailor-made solutions

SICK
Sensor Intelligence