
SICK.COM




DATA SHEET

# BCV08-N1BM03N200

VarioLine
Wire draw encoders

SICK Sensor Intelligence



## WIRE DRAW ENCODERS

# BCV08-N1BM03N200

### ORDERING INFORMATION

| Type | part no. |
|---|---|
| BCV08-N1BM03N200 | 1133460 |

Further device versions and accessories at www.sick.com/VarioLine

## DETAILED TECHNICAL DATA

### SAFETY-RELATED PARAMETERS

| | |
|---|---|
| $MTTF_D$ (mean time to dangerous failure) | 80 years (EN ISO 13849-1) [1] |

[1] This product is a standard product and does not constitute a safety component as defined in the Machinery Directive. Calculation based on nominal load of components, average ambient temperature 40°C, frequency of use 8760 h/a. All electronic failures are considered hazardous. For more information, see document no. 8015532.

### PERFORMANCE

| | |
|---|---|
| Measurement range | 0 m ... 3 m |
| Encoder | Absolute encoders |
| Resolution (wire draw + encoder) | 0.0009 mm [1] [2] |
| Repeatability | ≤ 0.3 mm [3] |
| Linearity | ≤ ± 2 mm [3] |
| Hysteresis | ≤ 1.2 mm [3] |

[1] The values shown have been rounded.

[2] Example calculation based on the BCV08 with PROFINET: 230 mm (wire draw length per revolution - see Mechanical data): 262,144 (number of steps per revolution) = 0.001 mm (resolution of wire draw + encoder combination).

[3] Value applies to wire draw mechanism.

### INTERFACES

| | |
|---|---|
| Communication interface | PROFINET |
| Programmable/configurable | ✓ |

## ELECTRONICS

| | |
|---|---|
| Connection type | Male connector, 1x, M12, 4-pin, axial [1]<br>Female connector, 2x, M12, 4-pin, axial [2] |
| Supply voltage | 10 V DC ... 30 V DC |
| Power consumption | ≤ 3 W (without load) |

[1] A-coded.

[2] D-coded.

## MECHANICS

| | |
|---|---|
| Weight | 0.8 kg |
| Measuring wire material | Stainless steel 1.4401 |
| Measuring wire diameter | 0.81 mm |
| Housing material, wire draw mechanism | Stainless steel 1.4301 |
| Spring return force | 8 N ... 10 N [1] |
| Length of wire pulled out per revolution | 230 mm |
| Life of wire draw mechanism | Typ. 1,000,000 cycles [2] [3] |
| Actual wire draw length | 3.2 m |
| Operating speed | 4 m/s |
| Mounted encoder | AFM60 PROFINET, AFM60A-S1NB018X12, 1059040 |
| Mounted mechanic | MRA-V080-103D3, 5347779 |

[1] These values were measred at an ambient temperature of 25 °C. There may be variations at other temperatures.

[2] Average values, which depend on the application.

[3] The service life depends on the type of load. This is influenced by environmental conditions, the installation location, the measuring range in use, the traversing speed, and acceleration.

## AMBIENT DATA


| | |
|---|---|
| EMC | According to EN 61000-6-2 and EN 61000-6-3 |
| Enclosure rating | IP60, mounted mechanic<br>IP67, Encoder (IEC 60529) [1] |
| Operating temperature range | –30 °C ... +70 °C |

[1] With mating connector fitted.

## CERTIFICATES


| | |
|---|---|
| EU declaration of conformity | ✓ |
| UK declaration of conformity | ✓ |
| ACMA declaration of conformity | ✓ |
| Moroccan declaration of conformity | ✓ |
| China RoHS | ✓ |

**DIMENSIONAL DRAWING**




Dimensions in mm (inch)


**ANSCHLUSSBELEGUNG FEMALE CONNECTOR**




Port 1, Port 2

| PIN | Wire color | Signal |
|---|---|---|
| 1 | Yellow | T x D+ |
| 2 | White | R x D+ |
| 3 | Orange | T x D- |
| 4 | Blue | R x D- |


**ANSCHLUSSBELEGUNG MALE CONNECTOR**




Supply voltage

| PIN | Wire color | Signal |
|---|---|---|
| 1 | Brown | $U_s$ 10 V ... 30 V |
| 2 | White | Not assigned |
| 3 | Blue | GND |
| 4 | Black | Not assigned |

**CONNECTION DIAGRAM**




Further information as well as suitable accessories, example applications and downloads such as CAD dimensional models, operating instructions and software can be found at www.sick.com/1133460

SICK AG
WALDKIRCH
GERMANY
SICK.COM

# SICK AT A GLANCE

SICK is a leading global technology company for intelligent sensors and integrated solutions in industrial automation. Our technologies set benchmarks, making your industrial processes more efficient, safer and more sustainable – both in logistics and manufacturing operations.

SICK combines sensor intelligence with industry expertise and certified consulting services. We provide the ideal foundation for scalable as well as tailor-made automation solutions and create added value along the entire value chain. Our close partnerships with our customers are more than just a promise: Together, we optimize productivity, improve quality, protect health and safety, and help build a sustainable future. All with empathy and trust.

Since 1946, we have been developing innovative technologies with passion and a pioneering spirit. With a global network in around 40 countries, SICK has a global presence and is always close by. The company's headquarters are located in Waldkirch near Freiburg, Germany. Our customers benefit from our understanding of both local and global requirements, which enables us to deliver tailor-made solutions

SICK

Sensor Intelligence