SICK.COM



DATA SHEET

ZLD18-BFZCG8

Z18 Simple Sense
Photoelectric sensors

SICK Sensor Intelligence

Illustration may differ

PHOTOELECTRIC SENSORS

ZLD18-BFZCG8

ORDERING INFORMATION

Type	part no.
ZLD18-BFZCG8	1100594

Further device versions and accessories at www.sick.com/Z18_Simple_Sense

DETAILED TECHNICAL DATA

FEATURES

Functional principle	Photoelectric retro-reflective sensor
Functional principle detail	With minimum distance to reflector (dual lens system)
Dimensions (W x H x D)	13.6 mm x 34.8 mm x 21.9 mm
Housing design (light emission)	Hybrid
Thread diameter (housing)	M18
Mounting system type	M18, head/side (24.1 ... 25.4 mm)
Housing color	Transparent
Sensing range max.	0 m ... 5 m [1]
Sensing range	0 m ... 4.2 m [1]
Type of light	Visible red light
Light source	LED
Light spot size (distance)	Ø 125 mm (1,000 mm)
Wave length	625 nm

[1] Reflector PL80A.

MECHANICS/ELECTRONICS

Supply voltage U_B	10 V DC ... 30 V DC
Ripple	< 10 %

[1] Without load.

[2] Signal transit time with resistive load.

[3] With light/dark ratio 1:1.

[4] A = V_S connections reverse-polarity protected.

[5] B = inputs and output reverse-polarity protected.

[6] D = outputs overcurrent and short-circuit protected.

Current consumption	≤ 15 mA [1]
Switching output	PNP
Switching mode	Dark switching
Switching output detail	
Switching output Q1	PNP, Dark switching
Switching output Q2	Not connected
Output current $I_{max.}$	100 mA
Response time	≤ 500 µs [2]
Switching frequency	1,000 Hz [3]
Connection type	Terminal connection Wago 733-103, 3-pin, 2,000 mm
Cable material	Plastic, PVC
Conductor cross section	0.13 mm²
Circuit protection	A [4] B [5] D [6]
Protection class	III
Weight	4.54 g
Polarizing filter	✓
Housing material	Plastic, ABS
Optics material	Plastic, PMMA
Enclosure rating	IP67
Ambient operating temperature	–40 °C ... +55 °C
Ambient temperature, storage	–40 °C ... +70 °C
UL File No.	E189383

[1] Without load.

[2] Signal transit time with resistive load.

[3] With light/dark ratio 1:1.

[4] A = V_S connections reverse-polarity protected.

[5] B = inputs and output reverse-polarity protected.

[6] D = outputs overcurrent and short-circuit protected.

CONNECTION TYPE/PINOUTS

Connection type	
	Terminal connection Wago 733-103, 3-pin, 2,000 mm
Connection type Detail	
Cable material	Plastic
Conductor cross section	0.13 mm²
Pinouts	
BN 1	+ (L+)
BK 2	Q_L
BU 3	- (M)

CERTIFICATES

EU declaration of conformity	✓
UK declaration of conformity	✓
ACMA declaration of conformity	✓
Moroccan declaration of conformity	✓
China RoHS	✓

China Compulsory Product Certification (CCC) exempt	✓

DIMENSIONAL DRAWING



Dimensions in mm (inch)
① optical axis, sender
② optical axis, receiver
③ LED status indicator
④ Connection

PINOUTS, SEE TABLE TECHNICAL DATA: CONNECTION TYPE/PINOUTS



CHARACTERISTIC CURVE



① Reflector PL23 FT
② Reflector PL20A
③ Reflector PL250
④ Reflector PL40A
⑤ Reflector PL80A

SENSING RANGE DIAGRAM



Sensing range Sensing range max.

① Reflector PL23 FT
② Reflector PL20A
③ Reflector PL250
④ Reflector PL40A
⑤ Reflector PL80A

Further information as well as suitable accessories, example applications and downloads such as CAD dimensional models, operating instructions and software can be found at www.sick.com/1100594

SICK AG
WALDKIRCH
GERMANY
SICK.COM

SICK AT A GLANCE

SICK is a leading global technology company for intelligent sensors and integrated solutions in industrial automation. Our technologies set benchmarks, making your industrial processes more efficient, safer and more sustainable – both in logistics and manufacturing operations.

SICK combines sensor intelligence with industry expertise and certified consulting services. We provide the ideal foundation for scalable as well as tailor-made automation solutions and create added value along the entire value chain. Our close partnerships with our customers are more than just a promise: Together, we optimize productivity, improve quality, protect health and safety, and help build a sustainable future. All with empathy and trust.

Since 1946, we have been developing innovative technologies with passion and a pioneering spirit. With a global network in around 40 countries, SICK has a global presence and is always close by. The company's headquarters are located in Waldkirch near Freiburg, Germany. Our customers benefit from our understanding of both local and global requirements, which enables us to deliver tailor-made solutions

SICK

Sensor Intelligence