SICK.COM



DATA SHEET

BCV08-L1KM03P200

VarioLine
Wire draw encoders

SICK Sensor Intelligence



WIRE DRAW ENCODERS

BCV08-L1KM03P200

ORDERING INFORMATION

Type	part no.
BCV08-L1KM03P200	6084943

Further device versions and accessories at www.sick.com/VarioLine

DETAILED TECHNICAL DATA

SAFETY-RELATED PARAMETERS

$MTTF_D$ (mean time to dangerous failure)	850 years (EN ISO 13849-1) [1]

[1] This product is a standard product and does not constitute a safety component as defined in the Machinery Directive. Calculation based on nominal load of components, average ambient temperature 40°C, frequency of use 8760 h/a. All electronic failures are considered hazardous. For more information, see document no. 8015532.

PERFORMANCE

Measurement range	0 m ... 3 m
Encoder	Absolute encoders
Resolution (wire draw + encoder)	0.06 mm [1] [2]
Repeatability	≤ 0.3 mm [3]
Linearity	≤ ± 2 mm [3]
Hysteresis	≤ 1.2 mm [3]

[1] The values shown have been rounded.

[2] Example calculation based on the BCV08 with PROFINET: 230 mm (wire draw length per revolution - see Mechanical data): 262,144 (number of steps per revolution) = 0.001 mm (resolution of wire draw + encoder combination).

[3] Value applies to wire draw mechanism.

INTERFACES

Communication interface	- / Voltage
Signal type	Analog (voltage)

ELECTRONICS

Connection type	Cable, radial, 1.5 m
Supply voltage	19 V DC ... 33 V DC

Operating current	≤ 80 mA (without load)

MECHANICS

Weight	0.7 kg
Measuring wire material	Stainless steel 1.4401
Measuring wire diameter	0.81 mm
Housing material, wire draw mechanism	Stainless steel 1.4301
Spring return force	8 N ... 10 N [1]
Length of wire pulled out per revolution	230 mm
Life of wire draw mechanism	Typ. 1,000,000 cycles [2] [3]
Actual wire draw length	3.2 m
Operating speed	4 m/s
Mounted encoder	ACM36, ACM36-L1K0-K01, 6039752
Mounted mechanic	MRA-V080-103D3, 5347779

[1] These values were measred at an ambient temperature of 25 °C. There may be variations at other temperatures.


[2] Average values, which depend on the application.

[3] The service life depends on the type of load. This is influenced by environmental conditions, the installation location, the measuring range in use, the traversing speed, and acceleration.

AMBIENT DATA


EMC	According to EN 61000-6-2 and EN 61000-6-4
Enclosure rating	IP60, mounted mechanic IP65, Encoder
Operating temperature range	–30 °C ... +70 °C

DIMENSIONAL DRAWING




Dimensions in mm (inch)

ANSCHLUSSBELEGUNG



Color	Signal
Green	+ 24 V
White	Output
Brown	0 V

DIAGRAMS MULTITURN, VOLTAGE OUTPUT



Configured range (α) must be at least 10°

Further information as well as suitable accessories, example applications and downloads such as CAD dimensional models, operating instructions and software can be found at www.sick.com/6084943

SICK AG
WALDKIRCH
GERMANY
SICK.COM

SICK AT A GLANCE

SICK is a leading global technology company for intelligent sensors and integrated solutions in industrial automation. Our technologies set benchmarks, making your industrial processes more efficient, safer and more sustainable – both in logistics and manufacturing operations.

SICK combines sensor intelligence with industry expertise and certified consulting services. We provide the ideal foundation for scalable as well as tailor-made automation solutions and create added value along the entire value chain. Our close partnerships with our customers are more than just a promise: Together, we optimize productivity, improve quality, protect health and safety, and help build a sustainable future. All with empathy and trust.

Since 1946, we have been developing innovative technologies with passion and a pioneering spirit. With a global network in around 40 countries, SICK has a global presence and is always close by. The company's headquarters are located in Waldkirch near Freiburg, Germany. Our customers benefit from our understanding of both local and global requirements, which enables us to deliver tailor-made solutions

SICK

Sensor Intelligence