

SICK.COM



DATA SHEET

IHP03-0B8NSVU2K

IMM
Inductive proximity sensors

SICK

Sensor Intelligence



Illustration may differ

INDUCTIVE PROXIMITY SENSORS

IHP03-0B8NSVU2K

ORDERING INFORMATION

Type	part no.
IHP03-0B8NSVU2K	6058032

Further device versions and accessories at www.sick.com/IMM



DETAILED TECHNICAL DATA

FEATURES

Housing	Cylindrical
Housing	Short-body
Diameter	Ø 3 mm
Pressure resistance	≤ 150 bar ¹⁾
Sensing range S _n	0.8 mm
Safe sensing range S _s	0.648 mm
Installation type	Flush
Switching frequency	8,000 Hz
Connection type	Cable, 3-wire, 2 m ²⁾
Switching output	NPN
Switching output detail	NPN
Output function	NO
Electrical wiring	DC 3-wire
Enclosure rating	IP68 IP69K

¹⁾ Only sensing face.
²⁾ Do not bend below 0 °C.

MECHANICS/ELECTRONICS

Supply voltage	10 V DC ... 30 V DC
Ripple	≤ 20 % ¹⁾

¹⁾ Of V_s.
²⁾ With I_a = 100 mA.
³⁾ Supply voltage U_s and constant ambient temperature T_a.

Voltage drop	$\leq 2 \text{ V}^{2)}$
Time delay before availability	$\leq 10 \text{ ms}$
Hysteresis	1 % ... 10 %
Reproducibility	$\leq 2 \text{ \%}^{3)}$
Temperature drift (of S_r)	$\pm 10 \text{ \%}$
EMC	EN 60947-5-2 IEC 61000-4-2: (Testlevel 2) IEC 61000-4-4: (Testlevel 2)
Continuous current I_a	$\leq 100 \text{ mA}$
Cable material	PUR
Conductor size	0.055 mm ²
Cable diameter	Ø 2.6 mm
Short-circuit protection	✓
Shock and vibration resistance	30 g, 11 ms / 10 ... 55 Hz, 1 mm
Ambient operating temperature	-25 °C ... +70 °C
Housing material	Stainless steel V2A, DIN 1.4305 / AISI 303
Sensing face material	Ceramics, ZrO ₂
Housing length	12 mm
UL File No.	NRKH.E191603

¹⁾ Or V_s .

²⁾ With $I_a = 100 \text{ mA}$.

³⁾ Supply voltage U_a and constant ambient temperature T_a .

SAFETY-RELATED PARAMETERS

MTTF _D	186 years
DC _{avg}	0%
T _M (mission time)	20 years

REDUCTION FACTORS

Note	The values are reference values which may vary
Stainless steel (V2A, 304)	Approx. 0.8
Aluminum (Al)	Approx. 0.5
Copper (Cu)	Approx. 0.45
Brass (Br)	Approx. 0.6

INSTALLATION NOTE


Remark	Associated graphic see "Installation note"
A	1 mm
B	2 mm
C	3 mm
D	3 mm
E	0 mm
F	7 mm

CERTIFICATES


EU declaration of conformity	✓
UK declaration of conformity	✓

ACMA declaration of conformity	✓
Moroccan declaration of conformity	✓
China RoHS	✓


INSTALLATION NOTE QUASI-FLUSH INSTALLATION



CONNECTION DIAGRAM CD-001



DIMENSIONAL DRAWING ULTRASHORT, FLUSH, CABLE, IHP03



Dimensions in mm (inch)
① Connection

Further information as well as suitable accessories, example applications and downloads such as CAD dimensional models, operating instructions and software can be found at www.sick.com/6058032



SICK AG
WALDKIRCH
GERMANY
SICK.COM

SICK AT A GLANCE

SICK is a leading global technology company for intelligent sensors and integrated solutions in industrial automation. Our technologies set benchmarks, making your industrial processes more efficient, safer and more sustainable – both in logistics and manufacturing operations.

SICK combines sensor intelligence with industry expertise and certified consulting services. We provide the ideal foundation for scalable as well as tailor-made automation solutions and create added value along the entire value chain. Our close partnerships with our customers are more than just a promise: Together, we optimize productivity, improve quality, protect health and safety, and help build a sustainable future. All with empathy and trust.

Since 1946, we have been developing innovative technologies with passion and a pioneering spirit. With a global network in around 40 countries, SICK has a global presence and is always close by. The company's headquarters are located in Waldkirch near Freiburg, Germany. Our customers benefit from our understanding of both local and global requirements, which enables us to deliver tailor-made solutions

SICK
Sensor Intelligence