



MLG05W-0300E12503

MLG-2 WebChecker

AUTOMATION LIGHT GRIDS

SICK
Sensor Intelligence.



Illustration may differ



Ordering information

Type	part no.
MLG05W-0300E12503	1129587

Other models and accessories → www.sick.com/MLG-2_WebChecker

Detailed technical data

Features

Device version	Web guiding
Sensor principle	Sender/receiver
Minimum object length	4 mm ¹⁾
Beam separation	5 mm
Resolution	0.1 mm
Cycle time	32 µs per beam
Repeatability	6 µm ²⁾
Accuracy	± 0.3 mm ³⁾
Type of synchronization	Cable
Number of beams	90
Total measuring field width	445 mm
Measuring field width detailed	
Measuring field width (connection side)	445 mm
Blind zone (medium range)	0 mm
Measuring field width (head side)	0 mm
Software features (default)	
Q ₁	Alarm, general
Application	High resolution mode
Included with delivery	1 × sender

¹⁾ See graphic: product definition.
²⁾ 1 sigma, 0% object transmission (sensor internal value).
³⁾ Typical 0.1 mm. For opaque objects and exact alignment of sender/receiver.

1 × receiver
1 x Fieldbus module
4/6 x QuickFix brackets (6 x QuickFix brackets for monitoring heights above 2 m)
1 × Quick Start Guide

¹⁾ See graphic: product definition.

²⁾ 1 sigma, 0% object transmission (sensor internal value).

³⁾ Typical 0.1 mm. For opaque objects and exact alignment of sender/receiver.

Mechanics/electronics

Light source	LED, Infrared light
Wave length	850 nm
Supply voltage V_s	DC 19.2 V ... 28.8 V ¹⁾
Power consumption sender	59.5 mA ²⁾
Power consumption receiver	138 mA ²⁾
Fieldbus module current consumption	115 mA
Ripple	< 5 V _{pp}
Output current I_{max}	100 mA
Output load, capacitive	100 nF
Output load, Inductive	1 H
Initialization time	< 1 s
Switching output	Push-pull: PNP/NPN
Dimensions (W x H x D)	34 mm x 529.4 mm x 30.6 mm
Connection type	Plug, M12, 5-pin, 0.22 m Connector M12, 12-pin, 0.27 m
Housing material	Aluminum
Display	LED
Enclosure rating	IP65, IP67 ³⁾
Circuit protection	U _V connections, reverse polarity protected Output Q short-circuit protected Interference pulse suppression
Protection class	III
Weight	1.159 kg
Front screen	PMMA
Option	None
UL File No.	NRKH.E181493

¹⁾ Without load.

²⁾ Without load with 24 V.

³⁾ Operating in outdoor condition only with a external protection housing.

Performance

Maximum range	3.5 m ¹⁾
Minimum range	≥ 0.2 m
Operating range	2.5 m

¹⁾ No reserve for environmental issue and deterioration of the diode.

²⁾ With resistive load.

Response time	19 ms ²⁾
----------------------	---------------------

¹⁾ No reserve for environmental issue and deterioration of the diode.

²⁾ With resistive load.

Interfaces

EtherCAT®	✓
Digital output	Q ₁
Number	1

Ambient data

Shock resistance	Continuous shocks 10 g, 16 ms, 1000 shocks Single shocks 15 g, 11 ms 3 per axle
Vibration resistance	Sinusoidal oscillation 10-150 Hz 5 g
Ambient light immunity	100,000 lx
Ambient operating temperature	-30 °C ... +55 °C
Ambient temperature, storage	-40 °C ... +70 °C

Certificates

EU declaration of conformity	✓
UK declaration of conformity	✓
ACMA declaration of conformity	✓
Moroccan declaration of conformity	✓
China RoHS	✓
cULus certificate	✓
Profinet certificate	✓
Photobiological safety (IEC EN 62471)	✓
Information according to Art. 3 of Data Act (Regulation EU 2023/2854)	✓

Classifications

ECLASS 5.0	27270910
ECLASS 5.1.4	27270910
ECLASS 6.0	27270910
ECLASS 6.2	27270910
ECLASS 7.0	27270910
ECLASS 8.0	27270910
ECLASS 8.1	27270910
ECLASS 9.0	27270910
ECLASS 10.0	27270910
ECLASS 11.0	27270910
ECLASS 12.0	27270910
ETIM 5.0	EC002549
ETIM 6.0	EC002549
ETIM 7.0	EC002549
ETIM 8.0	EC002549

39121528

Figure 1 provides detailed dimensions for the front and rear views of the 10-pin D-sub connector. The front view (left) shows a rectangular connector with a total width of 38.5 (1.52) and a total height of 40.6 (1.6). The rear view (right) shows the internal components and pin locations, with a total width of 34 (1.34) and a total height of 133 (5.26).

Front View Dimensions:

- Total width: 38.5 (1.52)
- Top width: 36.3 (1.43)
- Bottom width: 30.6 (1.2)
- Bottom width (inner): 36.3 (1.43)
- Bottom width (outer): 38.5 (1.52)
- Bottom width (inner, bottom): 40.6 (1.6)
- Internal width: 38.1 (1.5)


Rear View Dimensions:

- Total width: 34 (1.34)
- Top width: 17 (0.67)
- Top width (inner): 17 (0.67)
- Top width (outer): 17.7 (0.7)
- Pin 1 diameter: 15.6 (0.61)
- Pin 2 diameter: 23.2 (0.91)
- Pin 3 diameter: 24 (0.94)
- Pin 4 diameter: 24 (0.94)
- Pin 5 diameter: 24 (0.94)
- Pin 6 diameter: 24 (0.94)
- Pin 7 diameter: 24 (0.94)
- Pin 8 diameter: 24 (0.94)
- Pin 9 diameter: 24 (0.94)
- Pin 10 diameter: 24 (0.94)
- Pin 11 diameter: 24 (0.94)
- Pin 12 diameter: 24 (0.94)
- Pin 13 diameter: 24 (0.94)
- Pin 14 diameter: 24 (0.94)
- Pin 15 diameter: 24 (0.94)
- Pin 16 diameter: 24 (0.94)
- Pin 17 diameter: 24 (0.94)
- Pin 18 diameter: 24 (0.94)
- Pin 19 diameter: 24 (0.94)
- Pin 20 diameter: 24 (0.94)
- Pin 21 diameter: 24 (0.94)
- Pin 22 diameter: 24 (0.94)
- Pin 23 diameter: 24 (0.94)
- Pin 24 diameter: 24 (0.94)
- Pin 25 diameter: 24 (0.94)
- Pin 26 diameter: 24 (0.94)
- Pin 27 diameter: 24 (0.94)
- Pin 28 diameter: 24 (0.94)
- Pin 29 diameter: 24 (0.94)
- Pin 30 diameter: 24 (0.94)
- Pin 31 diameter: 24 (0.94)
- Pin 32 diameter: 24 (0.94)
- Pin 33 diameter: 24 (0.94)
- Pin 34 diameter: 24 (0.94)
- Pin 35 diameter: 24 (0.94)
- Pin 36 diameter: 24 (0.94)
- Pin 37 diameter: 24 (0.94)
- Pin 38 diameter: 24 (0.94)
- Pin 39 diameter: 24 (0.94)
- Pin 40 diameter: 24 (0.94)
- Pin 41 diameter: 24 (0.94)
- Pin 42 diameter: 24 (0.94)
- Pin 43 diameter: 24 (0.94)
- Pin 44 diameter: 24 (0.94)
- Pin 45 diameter: 24 (0.94)
- Pin 46 diameter: 24 (0.94)
- Pin 47 diameter: 24 (0.94)
- Pin 48 diameter: 24 (0.94)
- Pin 49 diameter: 24 (0.94)
- Pin 50 diameter: 24 (0.94)
- Pin 51 diameter: 24 (0.94)
- Pin 52 diameter: 24 (0.94)
- Pin 53 diameter: 24 (0.94)
- Pin 54 diameter: 24 (0.94)
- Pin 55 diameter: 24 (0.94)
- Pin 56 diameter: 24 (0.94)
- Pin 57 diameter: 24 (0.94)
- Pin 58 diameter: 24 (0.94)
- Pin 59 diameter: 24 (0.94)
- Pin 60 diameter: 24 (0.94)
- Pin 61 diameter: 24 (0.94)
- Pin 62 diameter: 24 (0.94)
- Pin 63 diameter: 24 (0.94)
- Pin 64 diameter: 24 (0.94)
- Pin 65 diameter: 24 (0.94)
- Pin 66 diameter: 24 (0.94)
- Pin 67 diameter: 24 (0.94)
- Pin 68 diameter: 24 (0.94)
- Pin 69 diameter: 24 (0.94)
- Pin 70 diameter: 24 (0.94)
- Pin 71 diameter: 24 (0.94)
- Pin 72 diameter: 24 (0.94)
- Pin 73 diameter: 24 (0.94)
- Pin 74 diameter: 24 (0.94)
- Pin 75 diameter: 24 (0.94)
- Pin 76 diameter: 24 (0.94)
- Pin 77 diameter: 24 (0.94)
- Pin 78 diameter: 24 (0.94)
- Pin 79 diameter: 24 (0.94)
- Pin 80 diameter: 24 (0.94)
- Pin 81 diameter: 24 (0.94)
- Pin 82 diameter: 24 (0.94)
- Pin 83 diameter: 24 (0.94)
- Pin 84 diameter: 24 (0.94)
- Pin 85 diameter: 24 (0.94)
- Pin 86 diameter: 24 (0.94)
- Pin 87 diameter: 24 (0.94)
- Pin 88 diameter: 24 (0.94)
- Pin 89 diameter: 24 (0.94)
- Pin 90 diameter: 24 (0.94)
- Pin 91 diameter: 24 (0.94)
- Pin 92 diameter: 24 (0.94)
- Pin 93 diameter: 24 (0.94)
- Pin 94 diameter: 24 (0.94)
- Pin 95 diameter: 24 (0.94)
- Pin 96 diameter: 24 (0.94)
- Pin 97 diameter: 24 (0.94)
- Pin 98 diameter: 24 (0.94)
- Pin 99 diameter: 24 (0.94)
- Pin 100 diameter: 24 (0.94)
- Pin 101 diameter: 24 (0.94)
- Pin 102 diameter: 24 (0.94)
- Pin 103 diameter: 24 (0.94)
- Pin 104 diameter: 24 (0.94)
- Pin 105 diameter: 24 (0.94)
- Pin 106 diameter: 24 (0.94)
- Pin 107 diameter: 24 (0.94)
- Pin 108 diameter: 24 (0.94)
- Pin 109 diameter: 24 (0.94)
- Pin 110 diameter: 24 (0.94)
- Pin 111 diameter: 24 (0.94)
- Pin 112 diameter: 24 (0.94)
- Pin 113 diameter: 24 (0.94)
- Pin 114 diameter: 24 (0.94)
- Pin 115 diameter: 24 (0.94)
- Pin 116 diameter: 24 (0.94)
- Pin 117 diameter: 24 (0.94)
- Pin 118 diameter: 24 (0.94)
- Pin 119 diameter: 24 (0.94)
- Pin 120 diameter: 24 (0.94)
- Pin 121 diameter: 24 (0.94)
- Pin 122 diameter: 24 (0.94)
- Pin 123 diameter: 24 (0.94)
- Pin 124 diameter: 24 (0.94)
- Pin 125 diameter: 24 (0.94)
- Pin 126 diameter: 24 (0.94)
- Pin 127 diameter: 24 (0.94)
- Pin 128 diameter: 24 (0.94)
- Pin 129 diameter: 24 (0.94)
- Pin 130 diameter: 24 (0.94)
- Pin 131 diameter: 24 (0.94)
- Pin 132 diameter: 24 (0.94)
- Pin 133 diameter: 24 (0.94)
- Pin 134 diameter: 24 (0.94)
- Pin 135 diameter: 24 (0.94)
- Pin 136 diameter: 24 (0.94)
- Pin 137 diameter: 24 (0.94)
- Pin 138 diameter: 24 (0.94)
- Pin 139 diameter: 24 (0.94)
- Pin 140 diameter: 24 (0.94)
- Pin 141 diameter: 24 (0.94)
- Pin 142 diameter: 24 (0.94)
- Pin 143 diameter: 24 (0.94)
- Pin 144 diameter: 24 (0.94)
- Pin 145 diameter: 24 (0.94)
- Pin 146 diameter: 24 (0.94)
- Pin 147 diameter: 24 (0.94)
- Pin 148 diameter: 24 (0.94)
- Pin 149 diameter: 24 (0.94)
- Pin 150 diameter: 24 (0.94)
- Pin 151 diameter: 24 (0.94)
- Pin 152 diameter: 24 (0.94)
- Pin 153 diameter: 24 (0.94)
- Pin 154 diameter: 24 (0.94)
- Pin 155 diameter: 24 (0.94)
- Pin 156 diameter: 24 (0.94)
- Pin 157 diameter: 24 (0.94)
- Pin 158 diameter: 24 (0.94)
- Pin 159 diameter: 24 (0.94)
- Pin 160 diameter: 24 (0.94)
- Pin 161 diameter: 24 (0.94)
- Pin 162 diameter: 24 (0.94)
- Pin 163 diameter: 24 (0.94)
- Pin 164 diameter: 24 (0.94)
- Pin 165 diameter: 24 (0.94)
- Pin 166 diameter: 24 (0.94)
- Pin 167 diameter: 24 (0.94)
- Pin 168 diameter: 24 (0.94)
- Pin 169 diameter: 24 (0.94)
- Pin 170 diameter: 24 (0.94)
- Pin 171 diameter: 24 (0.94)
- Pin 172 diameter: 24 (0.94)
- Pin 173 diameter: 24 (0.94)
- Pin 174 diameter: 24 (0.94)
- Pin 175 diameter: 24 (0.94)
- Pin 176 diameter: 24 (0.94)
- Pin 177 diameter: 24 (0.94)
- Pin 178 diameter: 24 (0.94

② for thread bold M4; turning moment 0,5 Nm

Data sheet | 2026-02-26 01:28:13
Subject to change without notice

Pinouts Ethernet



Adjustments



① status indicator: green, yellow, red LEDs

Connection diagram T-piece



Product definition



- ① operating range
- ② total measuring field width
- ③ measuring field width (head side)
- ④ Blind zone (medium range)
- ⑤ measuring field width (connection side)
- ⑥ sender
- ⑦ receiver
- ⑧ Beam separation
- ⑨ minimum object length

Recommended accessories

Other models and accessories → www.sick.com/MLG-2_WebChecker

	Brief description	Type	part no.
connectors and cables			
	• Connection type head A: Female connector, M12, 5-pin, A-coded • Connection type head B: Female connector, M12, 5-pin, A-coded • Connection type head C: Male connector, M12, 4-pin, A-coded • Description: Unshielded	SB0-02G12-SM	6029305
	• Connection type head A: Male connector, M12, 4-pin, D-coded • Connection type head B: Male connector, M12, 4-pin, D-coded • Signal type: Ethernet • Cable: 5 m, 4-wire, PUR, halogen-free • Description: Ethernet, twisted pair, shielded • Permitted cross-section: ≥ 0.25 mm² • Application: Zones with oils and lubricants	YM2D24-050EA2M2D24	6034422
	• Connection type head A: Female connector, M12, 5-pin, straight, A-coded • Connection type head B: Flying leads • Signal type: Sensor/actuator cable • Cable: 5 m, 5-wire, PVC • Description: Sensor/actuator cable, unshielded • Application: Uncontaminated zones, Zones with chemicals	YF2A15-050VB5XLEAX	2096240
	• Connection type head A: Female connector, M12, 5-pin, straight, A-coded • Connection type head B: Male connector, M12, 5-pin, straight, A-coded • Signal type: Sensor/actuator cable • Cable: 5 m, 5-wire, PUR, halogen-free • Description: Sensor/actuator cable, unshielded • Application: Drag chain operation, Zones with oils and lubricants, Robot, Drag chain operation	YF2A15-050UB5M2A15	2096010
	• Connection type head A: Male connector, M12, 4-pin, straight, D-coded • Connection type head B: Male connector, RJ45, 4-pin, straight • Signal type: Ethernet, PROFINET • Cable: 5 m, 4-wire, PUR, halogen-free • Description: Ethernet, shielded, PROFINET • Application: Drag chain operation, Zones with oils and lubricants	YM2D24-050P-N1MRJA4	2106184
Mounting systems			
	• Description: Mounting bracket for external mounting of the fieldbus module, 1 × mounting bracket and 1 × M5 × 6 screw • Material: Stainless steel • Details: Stainless steel V2A (1.4301)	BEF-WN-FBM-SET1	2082322

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com