



DATA SHEET

IQ40-20BPPKK0S

IQG
Inductive proximity sensors

SICK

Sensor Intelligence



INDUCTIVE PROXIMITY SENSORS

IQ40-20BPPKK0S

ORDERING INFORMATION

Type	part no.
IQ40-20BPPKK0S	1071860

Further device versions and accessories at www.sick.com/IQG



DETAILED TECHNICAL DATA

FEATURES

Housing	Rectangular
Housing	Standard design
Dimensions (W x H x D)	40 mm x 40 mm x 118 mm
Sensing range S_n	20 mm
Safe sensing range S_a	16.2 mm
Installation type	Flush
Switching frequency	150 Hz
Connection type	Cable gland
Switching output	PNP
Switching output detail	PNP
Output function	Complementary
Electrical wiring	DC 4-wire
Enclosure rating	IP67, IP68, IP69K
Special applications	Difficult application conditions

MECHANICS/ELECTRONICS

Supply voltage	10 V DC ... 30 V DC
Ripple	$\leq 10 \text{ V}_{pp}$ ¹⁾

¹⁾ Or U_b .

²⁾ Or S_r .

³⁾ Reference voltage: 50 V DC.

Voltage drop	$\leq 2 \text{ V}$
Time delay before availability	$\leq 50 \text{ ms}$
Hysteresis	3 % ... 15 % ²⁾
Reproducibility	$\leq 2 \text{ %}$
Temperature drift (of S_r)	$\pm 10 \text{ %}$
Continuous current I_a	$\leq 200 \text{ mA}$
No load current	12.5 mA
Cable gland clamping area	M20 1.5
Wire size	$\leq 2.5 \text{ mm}^2$
Short-circuit protection	✓
Power-up pulse protection	✓
Shock and vibration resistance	30 g, 11 ms / 10 ... 55 Hz, 1 mm
Ambient operating temperature	-25 °C ... +85 °C
Ambient temperature, storage	-40 °C ... +85 °C
Housing material	Plastic, PA 66
Sensing face material	Plastic, PA 66
Tightening torque, max.	1.8 Nm
Protection class	II ³⁾
UL File No.	E348498

¹⁾ Of U_b .²⁾ Of S_r .³⁾ Reference voltage: 50 V DC.

SAFETY-RELATED PARAMETERS

MTTF _D	1,125 years
DC _{avg}	0 %
T _M (mission time)	20 years

REDUCTION FACTORS

Note	The values are reference values which may vary
Stainless steel (V2A, 304)	Approx. 0.71
Aluminum (Al)	Approx. 0.3
Copper (Cu)	Approx. 0.25
Brass (Br)	Approx. 0.36

INSTALLATION NOTE


Remark	Associated graphic see "Installation"
A	0 mm
B	40 mm
C	40 mm
D	60 mm
E	0 mm
F	70 mm

CERTIFICATES


EU declaration of conformity	✓
------------------------------	---

UK declaration of conformity	✓
ACMA declaration of conformity	✓
Moroccan declaration of conformity	✓
China RoHS	✓
China Compulsory Product Certification (CCC) exempt	✓
cULus certificate	✓


INSTALLATION NOTE




CONNECTION DIAGRAM CD-030



RESPONSE DIAGRAM



DIMENSIONAL DRAWING IQG STANDARD, CABLE GLAND



Dimensions in mm (inch)

- ① LED output state, yellow
- ② Sensing face
- ③ operational status LED, green

Further information as well as suitable accessories, example applications and downloads such as CAD dimensional models, operating instructions and software can be found at www.sick.com/1071860



SICK AG
WALDKIRCH
GERMANY
SICK.COM

SICK AT A GLANCE

SICK is a leading global technology company for intelligent sensors and integrated solutions in industrial automation. Our technologies set benchmarks, making your industrial processes more efficient, safer and more sustainable – both in logistics and manufacturing operations.

SICK combines sensor intelligence with industry expertise and certified consulting services. We provide the ideal foundation for scalable as well as tailor-made automation solutions and create added value along the entire value chain. Our close partnerships with our customers are more than just a promise: Together, we optimize productivity, improve quality, protect health and safety, and help build a sustainable future. All with empathy and trust.

Since 1946, we have been developing innovative technologies with passion and a pioneering spirit. With a global network in around 40 countries, SICK has a global presence and is always close by. The company's headquarters are located in Waldkirch near Freiburg, Germany. Our customers benefit from our understanding of both local and global requirements, which enables us to deliver tailor-made solutions

SICK
Sensor Intelligence