



# WTB9L-3P3261S03


W9

PHOTOELECTRIC SENSORS

**SICK**  
Sensor Intelligence.



Illustration may differ



### Ordering information

| Type            | part no. |
|-----------------|----------|
| WTB9L-3P3261S03 | 1073333  |

Other models and accessories → [www.sick.com/W9](http://www.sick.com/W9)

### Detailed technical data

#### Features

|                                        |                                                               |
|----------------------------------------|---------------------------------------------------------------|
| <b>Functional principle</b>            | Photoelectric proximity sensor                                |
| <b>Functional principle detail</b>     | Background suppression                                        |
| <b>Dimensions (W x H x D)</b>          | 12.2 mm x 50 mm x 23.6 mm                                     |
| <b>Housing design (light emission)</b> | Rectangular                                                   |
| <b>Mounting hole</b>                   | M3                                                            |
| <b>Sensing range max.</b>              | 25 mm ... 300 mm <sup>1)</sup>                                |
| <b>Sensing range</b>                   | 25 mm ... 300 mm <sup>1)</sup>                                |
| <b>Type of light</b>                   | Visible red light                                             |
| <b>Light source</b>                    | Laser <sup>2)</sup>                                           |
| <b>Light spot size (distance)</b>      | Ø 1 mm (170 mm)                                               |
| <b>Wave length</b>                     | 650 nm                                                        |
| <b>Laser class</b>                     | 1 (IEC 60825-1 / CDRH 21 CFR 1040.10 & 1040.11) <sup>3)</sup> |
| <b>Adjustment</b>                      | Potentiometer, 5 turns                                        |
| <b>Special applications</b>            | Detecting small objects                                       |

<sup>1)</sup> Object with 90% remission (based on standard white, DIN 5033).

<sup>2)</sup> Average service life: 50,000 h at T<sub>U</sub> = +25 °C.

<sup>3)</sup> Do not intentionally look into the laser beam. Never point the laser beam at people's eyes.

## Mechanics/electronics

|                                               |                                                           |
|-----------------------------------------------|-----------------------------------------------------------|
| <b>Supply voltage <math>U_B</math></b>        | 10 V DC ... 30 V DC <sup>1)</sup>                         |
| <b>Ripple</b>                                 | < 5 V <sub>pp</sub> <sup>2)</sup>                         |
| <b>Current consumption</b>                    | 30 mA <sup>3)</sup>                                       |
| <b>Switching output</b>                       | PNP <sup>4)</sup>                                         |
| <b>Output function</b>                        | Complementary                                             |
| <b>Switching mode</b>                         | Light/dark switching <sup>4)</sup>                        |
| <b>Output current <math>I_{max.}</math></b>   | ≤ 100 mA                                                  |
| <b>Response time</b>                          | ≤ 0.5 ms <sup>5)</sup>                                    |
| <b>Switching frequency</b>                    | 1,000 Hz <sup>6)</sup>                                    |
| <b>Connection type</b>                        | Cable with M8 male connector, 4-pin, 120 mm <sup>7)</sup> |
| <b>Cable material</b>                         | Plastic, PVC                                              |
| <b>Conductor cross section</b>                | 0.14 mm <sup>2</sup>                                      |
| <b>Circuit protection</b>                     | A <sup>8)</sup><br>B <sup>9)</sup><br>C <sup>10)</sup>    |
| <b>Protection class</b>                       | III                                                       |
| <b>Weight</b>                                 | 80 g                                                      |
| <b>Housing material</b>                       | Plastic, VISTAL®                                          |
| <b>Optics material</b>                        | Plastic, PMMA                                             |
| <b>Enclosure rating</b>                       | IP66<br>IP67<br>IP69K                                     |
| <b>Ambient operating temperature</b>          | -10 °C ... +50 °C                                         |
| <b>Ambient operating temperature extended</b> | -30 °C ... +55 °C <sup>11)</sup> <sup>12)</sup>           |
| <b>Ambient temperature, storage</b>           | -30 °C ... +70 °C                                         |
| <b>UL File No.</b>                            | NRKH.E181493                                              |

<sup>1)</sup> Limit values when operated in short-circuit protected network: max. 8 A.

<sup>2)</sup> May not fall below or exceed  $U_y$  tolerances.

<sup>3)</sup> Without load.

<sup>4)</sup> Q = light switching.

<sup>5)</sup> Signal transit time with resistive load.

<sup>6)</sup> With light/dark ratio 1:1.

<sup>7)</sup> Do not bend below 0 °C.

<sup>8)</sup> A =  $V_S$  connections reverse-polarity protected.

<sup>9)</sup> B = inputs and output reverse-polarity protected.

<sup>10)</sup> C = interference suppression.

<sup>11)</sup> As of  $T_a = 50$  °C, a max. supply voltage  $V_{max.} = 24$  V and a max. load current  $I_{max.} = 50$  mA is permitted.

<sup>12)</sup> Operation below  $T_u -10$  °C is possible if the sensor is already switched on at  $T_u > -10$  °C, then cools down, and the supply voltage is subsequently not switched off. Switching on below  $T_u -10$  °C is not permissible.

## Safety-related parameters

|                         |                                          |
|-------------------------|------------------------------------------|
| <b>MTTF<sub>D</sub></b> | 424 years (EN ISO 13849-1) <sup>1)</sup> |
| <b>DC<sub>avg</sub></b> | 0 %                                      |

<sup>1)</sup> Mode of calculation: Parts-Count-calculation.


## Certificates

|                                               |   |
|-----------------------------------------------|---|
| <b>EU declaration of conformity</b>           | ✓ |
| <b>UK declaration of conformity</b>           | ✓ |
| <b>ACMA declaration of conformity</b>         | ✓ |
| <b>Moroccan declaration of conformity</b>     | ✓ |
| <b>China RoHS</b>                             | ✓ |
| <b>ECOLAB certificate</b>                     | ✓ |
| <b>cULus certificate</b>                      | ✓ |
| <b>Laser safety (IEC 60825-1) certificate</b> | ✓ |

## Classifications


|                       |          |
|-----------------------|----------|
| <b>ECLASS 5.0</b>     | 27270904 |
| <b>ECLASS 5.1.4</b>   | 27270904 |
| <b>ECLASS 6.0</b>     | 27270904 |
| <b>ECLASS 6.2</b>     | 27270904 |
| <b>ECLASS 7.0</b>     | 27270904 |
| <b>ECLASS 8.0</b>     | 27270904 |
| <b>ECLASS 8.1</b>     | 27270904 |
| <b>ECLASS 9.0</b>     | 27270904 |
| <b>ECLASS 10.0</b>    | 27270904 |
| <b>ECLASS 11.0</b>    | 27270904 |
| <b>ECLASS 12.0</b>    | 27270903 |
| <b>ETIM 5.0</b>       | EC002719 |
| <b>ETIM 6.0</b>       | EC002719 |
| <b>ETIM 7.0</b>       | EC002719 |
| <b>ETIM 8.0</b>       | EC002719 |
| <b>UNSPSC 16.0901</b> | 39121528 |

## Adjustments possible Potentiometer




- ④ LED indicator yellow: Status of received light beam
- ⑤ LED indicator green: power on
- ⑨ Adjustment of sensing range

Connection diagram Cd-083




Characteristic curve



- ① Sensing range on black, 6% remission factor
- ② Sensing range on gray, 18% remission factor
- ③ Sensing range on white, 90% remission factor

Light spot size




Dimensions in mm (inch)

| Sensing range     | Vertical      | Horizontal    |
|-------------------|---------------|---------------|
| 50 mm<br>(1.97)   | 1.2<br>(0.05) | 1.0<br>(0.04) |
| 100 mm<br>(3.94)  | 1.1<br>(0.04) | 1.0<br>(0.04) |
| 200 mm<br>(7.87)  | 0.9<br>(0.04) | 0.9<br>(0.04) |
| 300 mm<br>(11.81) | 0.8<br>(0.03) | 0.8<br>(0.03) |

— Vertical  
— Horizontal


Sensing range diagram



■ Sensing range typ. max.

- ① Sensing range on black, 6% remission factor
- ② Sensing range on gray, 18% remission factor
- ③ Sensing range on white, 90% remission factor

Dimensional drawing WTB9L-3



Dimensions in mm (inch)

- ① Center of optical axis, receiver
- ② Center of optical axis, sender
- ③ Mounting hole M3 (Ø 3.1 mm)
- ④ LED indicator yellow: Status of received light beam
- ⑤ LED indicator green: power on
- ⑥ Connecting cable or connecting cable with connector
- ⑦ male connector M8, 4-pin
- ⑧ male connector M12, 4-pin

## Recommended accessories

Other models and accessories → [www.sick.com/W9](http://www.sick.com/W9)

|                                                                                                                                                                            | Brief description                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              | Type               | part no. |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------|----------|
| connectors and cables                                                                                                                                                      |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |                    |          |
| <br>     | <ul style="list-style-type: none"> <li><b>Connection type head A:</b> Female connector, M8, 4-pin, straight, A-coded</li> <li><b>Connection type head B:</b> Flying leads</li> <li><b>Signal type:</b> Sensor/actuator cable</li> <li><b>Cable:</b> 5 m, 4-wire, PVC</li> <li><b>Description:</b> Sensor/actuator cable, unshielded</li> <li><b>Application:</b> Uncontaminated zones, Zones with chemicals</li> </ul>                                                                                                                         | YF8U14-050VA3XLEAX | 2095889  |
|                                                                                                                                                                            | <ul style="list-style-type: none"> <li><b>Connection type head A:</b> Male connector, M8, 4-pin, straight, A-coded</li> <li><b>Description:</b> Unshielded</li> <li><b>Connection systems:</b> Screw-type terminals</li> <li><b>Permitted cross-section:</b> 0.14 mm² ... 0.5 mm²</li> </ul>                                                                                                                                                                                                                                                   | STE-0804-G         | 6037323  |
| Mounting systems                                                                                                                                                           |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |                    |          |
| <br> | <ul style="list-style-type: none"> <li><b>Description:</b> Plate N08 for universal clamp bracket</li> <li><b>Material:</b> Steel, zinc diecast</li> <li><b>Details:</b> Zinc plated steel (sheet), Zinc die cast (clamping bracket)</li> <li><b>Items supplied:</b> Universal clamp (5322626), mounting hardware</li> <li><b>Usable for:</b> W100, W150, W4S, W4F, W8, W9-3, W8G, W8 Laser, W8 Inox, G6, W100 Laser, W100-2, W10, G6 Inox, RAY10, W4SLG-3, W9, GR18, MultiPulse, Reflex Array, MultiLine, LUT3, KT5, KT8, KT10, CS8</li> </ul> | BEF-KHS-N08        | 2051607  |
|                                                                                                                                                                            | <ul style="list-style-type: none"> <li><b>Description:</b> Mounting bracket</li> <li><b>Material:</b> Steel</li> <li><b>Details:</b> Steel, zinc coated</li> <li><b>Items supplied:</b> Mounting hardware included</li> <li><b>Suitable for:</b> W9-3</li> </ul>                                                                                                                                                                                                                                                                               | BEF-WN-W9-2        | 2022855  |

## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

## WORLDWIDE PRESENCE:

Contacts and other locations –[www.sick.com](http://www.sick.com)