



RZN-03ZWS-KW0

RZN

CYLINDER SENSORS

SICK
Sensor Intelligence.



Ordering information

Type	part no.
RZN-03ZWS-KW0	1117647

Other models and accessories → www.sick.com/RZN



Detailed technical data

Features

Cylinder type	IMI Norgren slot
Cylinder types with adapter	Round body cylinder
Housing length	29.5 mm
Switching output	Reed
Switching frequency	400 Hz
Output function	NO
Electrical wiring	AC/DC 2-wire
Enclosure rating	IP67 ¹⁾

¹⁾ According to EN 60529.

Mechanics/electronics

Supply voltage	5 V AC/DC ... 240 V AC/DC ¹⁾
Rated insulation voltage U_i	240 V
Rated impulse withstand voltage U_{imp}	4 kV
Voltage drop	≤ 3.5 V
Continuous current I_a	≤ 100 mA ²⁾
Switching capacity	≤ 10 W
Protection class	II
Response sensitivity, typ.	3 mT
Overrun distance, typ.	10 mm ³⁾
Reproducibility	≤ 0.1 mT ⁴⁾
Status indicator LED	Yes
Teach-in	No

¹⁾ Mains fuse F < 0.5 A IEC60127-2 sheet 1.

²⁾ AC.

³⁾ Distance covered by the encoder magnet while the sensor outputs a switching signal.

⁴⁾ Supply voltage U_B and constant ambient temperature T_a .

Ambient operating temperature	-40 °C ... +80 °C
Shock and vibration resistance	50 g, 11 ms / 10 ... 55 Hz, 1 mm
EMC	According to EN 60947-5-2
Connection type	Cable, 2-wire, stripped, drag chain use, 2 m
Connection type Detail	
Conductor cross section	0.12 mm²
Cable diameter	Ø 3 mm
Bending radius	With fixed installation > 10 x cable diameter For flexible use > 15 x cable diameter
Cable outlet	Axial
Material	
Housing	Plastic
Cable	PVC
Items supplied	1 x mounting clip plugged in

- 1) Mains fuse F < 0.5 A IEC60127-2 sheet 1.
2) AC.
3) Distance covered by the encoder magnet while the sensor outputs a switching signal.
4) Supply voltage U_B and constant ambient temperature T_a .

Safety-related parameters

MTTF_D	23,876 years
DC_{avg}	0 %
T_M (mission time)	20 years
B_{10D}	790,000 Switching cycles ¹⁾

- 1) Only for devices containing electro-mechanical components. In this case, the MTTF_D value of the entire device must be calculated from the given B_{10D} value, the number of switching cycles and the given MTTF_D value.

Classifications


ECLASS 5.0	27270104
ECLASS 5.1.4	27270104
ECLASS 6.0	27270104
ECLASS 6.2	27270104
ECLASS 7.0	27270104
ECLASS 8.0	27270104
ECLASS 8.1	27270104
ECLASS 9.0	27270104
ECLASS 10.0	27270104
ECLASS 11.0	27270104
ECLASS 12.0	27274301
ETIM 5.0	EC002544
ETIM 6.0	EC002544
ETIM 7.0	EC002544
ETIM 8.0	EC002544

UNSPSC 16.0901	39122230
----------------	----------


Certificates

EU declaration of conformity	✓
UK declaration of conformity	✓
ACMA declaration of conformity	✓
Moroccan declaration of conformity	✓
China RoHS	✓

Installation note



Connection diagram Cd-037




Functional principle Overrun distance



Note: Sensor housing may differ; representation corresponds to “NO contact” output function; overrun distance = switching point width + hysteresis

- ① Position sensor element
- ② Width of the switching point
- ③ Hysteresis
- ④ Direction of movement of the magnet

Dimensional drawing Cable



		L	A	
1117647	RZN-03ZWS-KW0	2 m	31.5 mm	2
1117646	RZN-03ZWS-KWB	5 m	31.5 mm	2
1117648	RZN-03ZWS-KUB	5 m	31.5 mm	2
1117645	RZN-03ZWS-KWD	10 m	31.5 mm	2

Recommended accessories

Other models and accessories → www.sick.com/RZN

	Brief description	Type	part no.
Mounting systems			
	• Description: Mounting clip for round body cylinder, clamping range 9.2 mm to 10 mm, for piston rod diameter of 8 mm • Material: Plastic • Details: Plastic • Items supplied: Mounting hardware included	BEF-S-R1-08	7902337
	• Description: Mounting clip for round body cylinder, clamping range 10.9 mm to 12 mm, for piston rod diameter of 10 mm • Material: Plastic • Details: Plastic • Items supplied: Mounting hardware included	BEF-S-R1-10	7901753
	• Description: Mounting clip for round body cylinder, clamping range 12.9 mm to 41 mm, for piston rod diameter of 12 mm • Material: Plastic • Details: Plastic • Items supplied: Mounting hardware included	BEF-S-R1-12	7901754
	• Description: Mounting clip for round body cylinder, clamping range 16.9 mm to 18 mm, for piston rod diameter of 16 mm • Material: Plastic • Details: Plastic • Items supplied: Mounting hardware included	BEF-S-R1-16	7901755
	• Description: Mounting clip for round body cylinder, clamping range 21 mm to 22 mm, for piston rod diameter of 20 mm • Material: Plastic • Details: Plastic • Items supplied: Mounting hardware included	BEF-S-R1-20	7901756
	• Description: Mounting clip for round body cylinder, clamping range 26.1 mm to 27.2 mm, for piston rod diameter of 25 mm • Material: Plastic • Details: Plastic • Items supplied: Mounting hardware included	BEF-S-R1-25	7901757
	• Description: Mounting clip for round body cylinder, clamping range 33 mm to 35 mm, for piston rod diameter of 32 mm • Material: Plastic • Details: Plastic • Items supplied: Mounting hardware included	BEF-S-R1-32	7901758
	• Description: Mounting clip for round body cylinder, clamping range 41.4 mm to 42.5 mm, for piston rod diameter of 40 mm • Material: Plastic • Details: Plastic • Items supplied: Mounting hardware included	BEF-S-R1-40	7901759

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com