SICK.COM



DATA SHEET

YG2B25-100IB1XLEAX

Industrial Ethernet cables and fieldbus cables
Connectors and cables

SICK Sensor Intelligence



CONNECTORS AND CABLES

YG2B25-100IB1XLEAX

ORDERING INFORMATION

Type	part no.
YG2B25-100IB1XLEAX	2109203

Further device versions and accessories at www.sick.com/Industrial_Ethernet_cables_and_fieldbus_cables

DETAILED TECHNICAL DATA

TECHNICAL SPECIFICATIONS

Connection type head A	Female connector, M12, 5-pin, angled, B-coded
Connection type head B	Flying leads
Locking plug connector	Screw connection
Connector material	TPU
Connector color	Black
Locking nut material	Zinc die-cast, nickel-plated
Tightening torque	0.4 Nm
Cable	10 m, 5-wire, PUR
Jacket material	PUR
Jacket color	Green
Cable diameter	8 mm
Conductor cross section	3 x 2 x 0.22 mm²
Shielding	Shielded
Bending radius	
Flexible use	> 15 x cable diameter
Drag chain operation	> 15 x cable diameter
Bending cycles	5,000,000
Reference voltage	
	≤ 60 V AC/DC
Current loading	4 mA
Traversing speed	1.6 m/s
Travelling distance	10 m
Acceleration	≤ 3 m/s²
Signal type	Fieldbus, Interbus
Application	Drag chain operation
Enclosure rating	IP65/ IP67
Operating temperature	
Flexible use	–30 °C ... +70 °C
Stationary position	–40 °C ... +80 °C

Head	–25 °C ... +90 °C
Contamination rating	3
Insulation resistance	100 MΩ
Overvoltage category	II

CERTIFICATES

EU declaration of conformity	✓
UK declaration of conformity	✓
China RoHS	✓
China Compulsory Product Certification (CCC) exempt	✓

Further information as well as suitable accessories, example applications and downloads such as CAD dimensional models, operating instructions and software can be found at www.sick.com/2109203

SICK AG
WALDKIRCH
GERMANY
SICK.COM

SICK AT A GLANCE

SICK is a leading global technology company for intelligent sensors and integrated solutions in industrial automation. Our technologies set benchmarks, making your industrial processes more efficient, safer and more sustainable – both in logistics and manufacturing operations.

SICK combines sensor intelligence with industry expertise and certified consulting services. We provide the ideal foundation for scalable as well as tailor-made automation solutions and create added value along the entire value chain. Our close partnerships with our customers are more than just a promise: Together, we optimize productivity, improve quality, protect health and safety, and help build a sustainable future. All with empathy and trust.

Since 1946, we have been developing innovative technologies with passion and a pioneering spirit. With a global network in around 40 countries, SICK has a global presence and is always close by. The company's headquarters are located in Waldkirch near Freiburg, Germany. Our customers benefit from our understanding of both local and global requirements, which enables us to deliver tailor-made solutions

SICK

Sensor Intelligence