



DATA SHEET

C25E-120303C11

C2000 Standard in IP69K Housing
Safety light curtains

SICK

Sensor Intelligence



Illustration may differ

SAFETY LIGHT CURTAINS

C25E-120303C11

ORDERING INFORMATION

Type	part no.
C25E-120303C11	1024206

Further device versions and accessories at www.sick.com/C2000_Standard_in_IP69K_Housing

DETAILED TECHNICAL DATA

FEATURES

Resolution	30 mm
Protective field height	1,200 mm
Response time	≤ 19 ms
Synchronization	Optical synchronisation

SAFETY-RELATED PARAMETERS

Type	Type 2 (IEC 61496-1)
Safety integrity level	SIL 1 (IEC 61508)
Category	Category 2 (EN ISO 13849)
Test rate (internal test)	13 /s (EN ISO 13849) ¹⁾
Maximum demand rate	≤ 8 min ⁻¹ (EN ISO 13849) ²⁾
Performance level	PL c (EN ISO 13849)
PFH ₀ (mean probability of a dangerous failure per hour)	2.2 x 10 ⁻⁸ (EN ISO 13849)
T _M (mission time)	20 years (EN ISO 13849)
Safe state in the event of a fault	At least one OSSD is in the OFF state.

¹⁾ Internal test. The test rate may not be exceeded if an external test is performed.
²⁾ Between two requirements on a safety-related response of the device, at least 100 internal or external tests must be carried out.

FUNCTIONS

	Functions	Delivery status
External device monitoring (EDM)	✓	Activated
Beam coding	✓	Uncoded

INTERFACES

System connection	Cable 15 m, PVC
Cable diameter	6 mm
Conductor cross section	0.25 mm ²
Configuration method	Hard wired
Display elements	7-segment display
Status display	LEDs

ELECTRICAL DATA

Protection class	III (EN 50178)
Output signal switching devices (OSSDs)	
Type of output	2 PNP semiconductors, short-circuit protected, cross-circuit monitored ¹⁾
ON state, switching voltage HIGH	24 V DC ($V_s - 2.25 \text{ V DC} \dots V_s$)
OFF state, switching voltage LOW	$\leq 3.5 \text{ V DC}$
Current-carrying capacity per OSSD	$\leq 500 \text{ mA}$

¹⁾ Applies to the voltage range between -30 V and +30 V.


MECHANICAL DATA

Housing diameter	50 mm
Material	
End caps	Stainless steel V4A
Plastic tube	PMMA
Compensating element (membrane)	PA 6
PG connector	PA 6

AMBIENT DATA

Enclosure rating	IP69K, IP67, IP66, IP65 (EN 60529)
Ambient operating temperature	0 °C ... +55 °C
Storage temperature	-25 °C ... +70 °C
Air humidity	15 % ... 95 %, Non-condensing
Vibration resistance	5 g, 10 Hz ... 55 Hz (IEC 68-2-6)
Shock resistance	10 g, 16 ms (EN 60068-2-29)


DIMENSIONAL DRAWING



Dimensions in mm (inch)
illustration sender (receiver mirror image)

Protective field height S	L1	L2
150	357	324
300	476	443
450	626	593
600	777	744
750	927	894
900	1.078	1.045
1.050	1.228	1.195
1.200	1.382	1.349

CONNECTION DIAGRAM C2000 STANDARD TO UE10-30S SAFETY RELAY



Further information as well as suitable accessories, example applications and downloads such as CAD dimensional models, operating instructions and software can be found at www.sick.com/1024206



SICK AG
WALDKIRCH
GERMANY
SICK.COM

SICK AT A GLANCE

SICK is a leading global technology company for intelligent sensors and integrated solutions in industrial automation. Our technologies set benchmarks, making your industrial processes more efficient, safer and more sustainable – both in logistics and manufacturing operations.

SICK combines sensor intelligence with industry expertise and certified consulting services. We provide the ideal foundation for scalable as well as tailor-made automation solutions and create added value along the entire value chain. Our close partnerships with our customers are more than just a promise: Together, we optimize productivity, improve quality, protect health and safety, and help build a sustainable future. All with empathy and trust.

Since 1946, we have been developing innovative technologies with passion and a pioneering spirit. With a global network in around 40 countries, SICK has a global presence and is always close by. The company's headquarters are located in Waldkirch near Freiburg, Germany. Our customers benefit from our understanding of both local and global requirements, which enables us to deliver tailor-made solutions

SICK
Sensor Intelligence