



DATA SHEET

IN40-D0101K

IN4000 Standard
Non-contact safety switches



NON-CONTACT SAFETY SWITCHES

IN40-D0101K

ORDERING INFORMATION

Type	part no.
IN40-D0101K	6027389
Further device versions and accessories at www.sick.com/IN4000_Standard	



DETAILED TECHNICAL DATA

FEATURES

Sensor principle	Inductive
Number of safe outputs	1
Switching delay from state change	T2 + 20 ms ¹⁾
Enable zone	10 mm ... 15 mm ²⁾
Assured switch off distance S _{ar}	30 mm ²⁾
Actuation directions	5
Active sensor surfaces	1
Monitoring time minimum dwell time	≥ 0.2 s

¹⁾ During this time the output is switched off (Logical "0"), see response range.

²⁾ Dependent on material. The indicated values refer to steel ST37.

SAFETY-RELATED PARAMETERS

Safety integrity level	SIL 3 (IEC 61508)
Category	Category 3 (EN ISO 13849)
Performance level	PL e (EN ISO 13849)
PFH _D (mean probability of a dangerous failure per hour)	1.0 x 10 ⁻⁸
T _M (mission time)	10 years (EN ISO 13849) ¹⁾ 20 years (EN ISO 13849) ²⁾
Type	Type 3 (EN ISO 14119)
Actuator coding level	Uncoded (EN ISO 14119)
Classification in compliance with IEC/EN 60947-5-3	PDF-M

¹⁾ At -25 °C ... +70 °C and 5 % ... 95 % relative air humidity.

²⁾ At +10 °C ... +40 °C and 5 % ... 70 % relative air humidity.

FUNCTIONS

Safe series connection	With T-connector (without diagnostics)
------------------------	--

INTERFACES

Connection type	Plug connector, M12, 4-pin
Coupling nut material	Brass
Display elements	LEDs
Power indication	✓
Status display	✓

ELECTRONICS

Protection class	III (EN 50178)
Supply voltage V_s	24 V DC (19.2 V DC ... 30 V DC)
Power consumption	15 mA
Type of output	Semiconductor, pulsed

MECHANICS

Design	Rectangular
Weight	0.22 kg
Material	
Housing	Zinc die cast (housing), PPE (cover)
Installation type	Non-flush

AMBIENT DATA


Enclosure rating	IP67 (IEC 60529)
Ambient operating temperature	-25 °C ... +70 °C
Storage temperature	-25 °C ... +70 °C
Vibration resistance	10 Hz ... 55 Hz, 1 mm (EN 60947-5-3)
Shock resistance	30 g, 11 ms (EN 60947-5-3)

CERTIFICATES

EU declaration of conformity	✓
UK declaration of conformity	✓
ACMA declaration of conformity	✓
Moroccan declaration of conformity	✓
China RoHS	✓
cULus certificate	✓
TÜV approval	✓
TÜV approval annex	✓

Technical drawing of the LED module showing three views: top, side, and front views. Dimensions are provided in millimeters (mm) and inches (in).

- Top View:**
 - Overall width: 40 (1.57)
- Side View:**
 - Overall height: 66 (2.6)
 - Distance from top edge to mounting hole center: 34 (1.34)
 - Mounting hole: M12 x 1
 - Distance from mounting hole center to LED array: 40 (1.57)
 - Distance from LED array to bottom edge: 17 (0.67)
- Front View:**
 - Overall width: 61 (2.4)
 - Overall height: 30 (1.18)
 - Distance from top edge to LED array: 10 (0.39)
 - Distance from top edge to mounting hole center: 20 (0.79)
 - Distance from mounting hole center to LED array: 5.4 (0.21)
 - Distance from mounting hole center to bottom edge: 5.4 (0.21)
 - Distance from LED array to bottom edge: 6 (0.24)
 - Distance from LED array to right edge: 33 (1.3)
 - Distance from LED array to right edge (total): 46 (1.81)
 - Distance from LED array to right edge (total): 61 (2.4)
 - Distance from LED array to right edge (total): 8.5 (0.33)
 - LED array label: LED

RESPONSE RANGE

Further information as well as suitable accessories, example applications and downloads such as CAD dimensional models, operating instructions and software can be found at www.sick.com/6027389



SICK AG
WALDKIRCH
GERMANY
SICK.COM

SICK AT A GLANCE

SICK is a leading global technology company for intelligent sensors and integrated solutions in industrial automation. Our technologies set benchmarks, making your industrial processes more efficient, safer and more sustainable – both in logistics and manufacturing operations.

SICK combines sensor intelligence with industry expertise and certified consulting services. We provide the ideal foundation for scalable as well as tailor-made automation solutions and create added value along the entire value chain. Our close partnerships with our customers are more than just a promise: Together, we optimize productivity, improve quality, protect health and safety, and help build a sustainable future. All with empathy and trust.

Since 1946, we have been developing innovative technologies with passion and a pioneering spirit. With a global network in around 40 countries, SICK has a global presence and is always close by. The company's headquarters are located in Waldkirch near Freiburg, Germany. Our customers benefit from our understanding of both local and global requirements, which enables us to deliver tailor-made solutions

SICK
Sensor Intelligence