




DATA SHEET

TBT-1PAGE1006GZ

TBT
Temperature sensors

SICK

Sensor Intelligence




Illustration may differ

TEMPERATURE SENSORS

TBT-1PAGE1006GZ

ORDERING INFORMATION

Type	part no.
TBT-1PAGE1006GZ	6043022

Further device versions and accessories at www.sick.com/TBT

DETAILED TECHNICAL DATA

FEATURES

Measuring range	-50 °C ... +150 °C
Sensor element	Pt100
Output signal	Pt100, 4-wire

MECHANICS/ELECTRONICS

Communication interface	-
Process connection	Thread G ½ B
Seal	Without seal
Insertion length/diameter of probe	100 mm / 6 mm
Wetted parts	Stainless steel 1.4571
Maximum process pressure	≤ 120 bar ¹⁾
Pressure resistance	Max. 120 bar
Housing material	Aluminum
Connection type	Cable gland M16 x 1.5 ²⁾
Enclosure rating	IP65 ³⁾
Measuring current	0.3 mA ... 1 mA
Electrical safety	Protection class: III, dielectric strength: 500 V AC
Protection class III	✓
CE-conformity	2004/108/EC, EN 61326-2-3
Weight	Ca. 155 g (depending on configuration)
Initialization time	< 1 ms

¹⁾ Pressure resistance at room temperature.

²⁾ The enclosure rating classes specified only apply while the thermometer is connected with female connectors that provide the corresponding enclosure rating.

³⁾ IP enclosure rating as per IEC 60529.

PERFORMANCE

Accuracy of sensor element	Class A according to IEC 60751
Response time	$t_{90} \leq 5.8 \text{ s}^{\text{1)}$ $t_{90} \leq 15.5 \text{ s}^{\text{1)}$

¹⁾ Depending on sensor configuration, according to IEC 60751.


AMBIENT DATA

Ambient temperature	-40 °C ... +125 °C
Storage and transport temperature	-40 °C ... +60 °C
Shock resistance	500 g (IEC 60751)
Vibration resistance according to IEC 60751	3 g

CERTIFICATES


China RoHS	✓
------------	---

DIMENSIONAL DRAWING: ZYLINDRICAL THREADS




Dimensions in mm (inch)


DIMENSIONAL DRAWING: CONICAL THREADS



DIMENSIONAL DRAWING: HOUSING, WITHOUT PROCESS CONNECTION



CONNECTION TYPE CABLE ENTRY M16 X 1.5, CABLE CROSS-SECTION UP TO 0.75 MM2, OUTPUT SIGNAL PT100



Further information as well as suitable accessories, example applications and downloads such as CAD dimensional models, operating instructions and software can be found at www.sick.com/6043022



SICK AG
WALDKIRCH
GERMANY
SICK.COM

SICK AT A GLANCE

SICK is a leading global technology company for intelligent sensors and integrated solutions in industrial automation. Our technologies set benchmarks, making your industrial processes more efficient, safer and more sustainable – both in logistics and manufacturing operations.

SICK combines sensor intelligence with industry expertise and certified consulting services. We provide the ideal foundation for scalable as well as tailor-made automation solutions and create added value along the entire value chain. Our close partnerships with our customers are more than just a promise: Together, we optimize productivity, improve quality, protect health and safety, and help build a sustainable future. All with empathy and trust.

Since 1946, we have been developing innovative technologies with passion and a pioneering spirit. With a global network in around 40 countries, SICK has a global presence and is always close by. The company's headquarters are located in Waldkirch near Freiburg, Germany. Our customers benefit from our understanding of both local and global requirements, which enables us to deliver tailor-made solutions

SICK
Sensor Intelligence