



# V2D611G-MMSBE4

GLS6

IMAGE-BASED CODE READERS

**SICK**  
Sensor Intelligence.



### Ordering information

Type	part no.
V2D611G-MMSBE4	1114539

Other models and accessories → [www.sick.com/GLS6](http://www.sick.com/GLS6)



### Detailed technical data

#### Features

<b>Optical focus</b>	Adjustable focus (manual)
<b>Illumination</b>	Integrated
<b>Illumination color</b>	Amber, LED, Visible, 617 nm, ± 15 nm Blue, LED, Visible, 470 nm, ± 15 nm
<b>LED class</b>	1 (IEC 62471:2006-07, EN 62471:2008-09)
<b>Feedback spot</b>	LED, Visible, green, 525 nm, ± 15 nm LED, Visible, Red, 635 nm, ± 15 nm
<b>Alignment aid</b>	Laser, Visible, 630 nm ... 680 nm
<b>Laser class</b>	1, complies with 21 CFR 1040.10 except for the conformance according to "Laser Notice No. 50" from June 24, 2007 (IEC 60825-1:2014, EN 60825-1:2014+A11:2021)
<b>Reading distance</b>	50 mm ... 300 mm
<b>Overrun speed</b>	≤ 5 m/s
<b>Accuracy (position)</b>	± 0.1 mm <sup>1)</sup>
<b>Repeatability (position)</b>	± 0.05 mm <sup>1)</sup>
<b>Working range</b>	50 mm ... 300 mm

<sup>1)</sup> Reading distance 90 mm.

#### Mechanics/electronics

<b>Connection type</b>	1 x M12, 17-pin male connector 1 x M12, 4-pin Ethernet female connector Circular plug-in connector
<b>Supply voltage</b>	12 V AC ... 24 V DC, ± 15 %
<b>Power consumption</b>	Typ. 3.5 W
<b>Output current</b>	≤ 50 mA
<b>Housing material</b>	Zinc diecast

<b>Housing color</b>	Light blue (RAL 5012)
<b>Enclosure rating</b>	IP54 (EN 60529, EN 60529/A2)
<b>Protection class</b>	III
<b>Electrical safety</b>	EN 62368
<b>Weight</b>	165 g
<b>Dimensions (L x W x H)</b>	50 mm x 40.3 mm x 29.6 mm

## Performance

<b>Readable code structures</b>	2D codes
<b>2D code types</b>	Data Matrix ECC200, QR code
<b>Code qualification</b>	On the basis of ISO/IEC 16022, ISO/IEC 15415, ISO/IEC 15416, ISO/IEC 18004

## Interfaces

<b>Ethernet</b>		✓ , TCP/IP
	Function	Data interface (read result output), FTP (image transmission)
	Data transmission rate	10/100 MBit/s
<b>PROFINET</b>		✓
	Function	PROFINET Single Port
	Data transmission rate	10/100 MBit/s
<b>EtherNet/IP™</b>		✓
	Data transmission rate	10/100 MBit/s
<b>Serial</b>		✓ , RS-232
	Function	Data interface (read result output)
	Data transmission rate	0.3 kBaud ... 115.2 kBaud
<b>CAN</b>		✓
	Function	SICK CAN sensor network CSN (CAN controller/CAN device, multiplexer/server)
	Data transmission rate	20 kbit/s ... 1 Mbit/s
<b>CANopen</b>		✓
	Data transmission rate	20 kbit/s ... 1 Mbit/s
<b>Optical indicators</b>		9 LEDs (6 status displays, 2 LED alignment aids, 1 feedback spot)
<b>Configuration software</b>		SOPAS ET (version 2018.04 or higher)
<b>Data storage and retrieval</b>		Image and data storage via external FTP
<b>EncoderFrequency</b>		Max. 300 Hz
<b>External illumination control</b>		Via digital output (max. 24 V trigger)

## Ambient data

<b>Electromagnetic compatibility (EMC)</b>	EN 61000-6-4:2007+A1:2011 / IEC 61000-6-3:2006+AMD1:2010 / EN 61000-6-2:2005-08
<b>Vibration resistance</b>	EN 60068-2-6:2008-02
<b>Shock resistance</b>	EN 60068-2-27:2009-05
<b>Ambient operating temperature</b>	0 °C ... +40 °C <sup>1)</sup>
<b>Storage temperature</b>	-20 °C ... +70 °C
<b>Permissible relative humidity</b>	90 %, Non-condensing

<sup>1)</sup> To use the product at the maximum ambient operating temperature, mount it with an aluminum mounting bracket (e.g., part number 2113160, 2112790).


### Classifications

<b>ECLASS 5.0</b>	27280103
<b>ECLASS 5.1.4</b>	27280103
<b>ECLASS 6.0</b>	27280103
<b>ECLASS 6.2</b>	27280103
<b>ECLASS 7.0</b>	27280103
<b>ECLASS 8.0</b>	27280103
<b>ECLASS 8.1</b>	27280103
<b>ECLASS 9.0</b>	27280103
<b>ECLASS 10.0</b>	27280103
<b>ECLASS 11.0</b>	27280103
<b>ECLASS 12.0</b>	27280103
<b>ETIM 5.0</b>	EC002550
<b>ETIM 6.0</b>	EC002550
<b>ETIM 7.0</b>	EC002999
<b>ETIM 8.0</b>	EC002999
<b>UNSPSC 16.0901</b>	43211701

### Certificates

<b>EU declaration of conformity</b>	✓
<b>UK declaration of conformity</b>	✓
<b>ACMA declaration of conformity</b>	✓
<b>China RoHS</b>	✓
<b>BIS registration</b>	✓
<b>ESD conformity</b>	✓
<b>Information according to Art. 3 of Data Act (Regulation EU 2023/2854)</b>	✓
<b>4Dpro</b>	✓

## Dimensional drawing



Dimensions in mm (inch)

structure and device dimensions, unit: mm (inch), decimal separator: period

- ① Connecting cable with Ethernet connection (female connector, M12, 4-pin, D-coded), length of cable: 0.25 m
- ② Connecting cable with Power/Serial Data/CAN/I/O connection (male connector, M12, 17-pin, A-coded), length of cable: 0.35 m
- ③ 4 M4 threaded mounting holes: through hole; 6.4 mm deep; max. depth of thread 5 mm
- ④ Viewing window with 8 integrated illumination LEDs, 2 LED alignment aids, 1 feedback LED, 1 time-of-flight sensor
- ⑤ Optics, manual focus adjustment with the help of a focus adjustment tool
- ⑥ 6 status LEDs to display the focus position and working distance and device status (2 display levels)

## Recommended accessories

Other models and accessories → [www.sick.com/GLS6](http://www.sick.com/GLS6)

	Brief description	Type	part no.
Mounting systems			
	<ul style="list-style-type: none"> <li>• <b>Description:</b> Bracket with adapter board</li> </ul>	Mounting bracket	2113160

	Brief description	Type	part no.
connectors and cables			
	<ul style="list-style-type: none"> <li>• <b>Connection type head A:</b> Female connector, M12, 17-pin, straight, A-coded</li> <li>• <b>Connection type head B:</b> Flying leads</li> <li>• <b>Signal type:</b> Power, serial, CAN, digital I/Os</li> <li>• <b>Cable:</b> 2 m, 17-wire, stripped, PE-X</li> <li>• <b>Description:</b> Power, suitable for 2 A, shielded, Serial, Changed color coding of the flying leads, CAN, Digital I/Os</li> <li>• <b>Connection systems:</b> Flying leads</li> <li>• <b>Note:</b> Max. permissible current strength at ambient temperature 50 °C: Contact 1 (blue) and contact 2 (brown): 3 A while the remaining contacts are operated with max. 100 mA; max. permissible current strength at ambient temperature 40 °C: 2 A for two and 1.5 A for 15 contacts.</li> <li>• <b>Application:</b> Drag chain operation</li> </ul>	YF2ASD-020XXXXLECX	2081094
	<ul style="list-style-type: none"> <li>• <b>Connection type head A:</b> Male connector, M12, 4-pin, straight, D-coded</li> <li>• <b>Connection type head B:</b> Male connector, RJ45, 4-pin, straight</li> <li>• <b>Signal type:</b> Ethernet, PROFINET</li> <li>• <b>Cable:</b> 2 m, 4-wire, PUR, halogen-free</li> <li>• <b>Description:</b> Ethernet, shielded, PROFINET</li> <li>• <b>Application:</b> Drag chain operation, Zones with oils and lubricants</li> </ul>	YM2D24-020P-N1MRJA4	2106182
Codes			
	<ul style="list-style-type: none"> <li>• <b>Description:</b> Multi code label with 16 data matrix codes for localizing AGV systems, customized alphanumeric code content, self-adhesive. Recommended for GLS611&amp;621.</li> </ul>	Multi-code label	4105695

## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

## WORLDWIDE PRESENCE:

Contacts and other locations –[www.sick.com](http://www.sick.com)