SICK.COM



DATA SHEET

# IHM06-1B5NSVT0G

IMM
Inductive proximity sensors

SICK Sensor Intelligence



Illustration may differ

# INDUCTIVE PROXIMITY SENSORS

# IHM06-1B5NSVT0G

## ORDERING INFORMATION

| Type | part no. |
|---|---|
| IHM06-1B5NSVT0G | 1101120 |

Further device versions and accessories at www.sick.com/IMM

## DETAILED TECHNICAL DATA

### FEATURES

| | |
|---|---|
| Housing | Cylindrical |
| Housing | Extremely short model |
| Diameter | Ø 6.5 mm |
| Sensing range $S_n$ | 1.5 mm |
| Safe sensing range $S_a$ | 1.215 mm |
| Installation type | Flush |
| Switching frequency | 5,000 Hz |
| Connection type | Connector M8, 3-pin |
| Switching output | NPN |
| Switching output detail | NPN |
| Output function | NO |
| Electrical wiring | DC 3-wire |
| Enclosure rating | IP67 [1] |
| Special features | Visual adjustment indicator |

[1] According to EN 60529.

### MECHANICS/ELECTRONICS

| | |
|---|---|
| Supply voltage | 10 V DC ... 30 V DC |
| Ripple | ≤ 20 % [1] |
| Voltage drop | ≤ 2 V [2] |
| Time delay before availability | ≤ 50 ms |

[1] Of $V_s$.

[2] With Ia = 200 mA.

[3] Supply voltage $U_a$ and constant ambient temperature Ta.

| | |
|---|---|
| Hysteresis | 1 % ... 10 % |
| Reproducibility | ≤ 2 % [3] |
| Temperature drift (of $S_r$) | ≤ 10 % |
| EMC | EN 60947-5-2 |
| Continuous current $I_a$ | ≤ 200 mA |
| Short-circuit protection | ✓ |
| Power-up pulse protection | ✓ |
| Shock and vibration resistance | 30 g, 11 ms / 10 ... 55 Hz, 1 mm |
| Ambient operating temperature | –25 °C ... +70 °C |
| Housing material | Stainless steel V2A, DIN 1.4305 / AISI 303 |
| Sensing face material | Plastic, LCP |
| Housing length | 29 mm |
| UL File No. | NRKH.E348498 |

[1] Of $V_S$.

[2] With Ia = 200 mA.

[3] Supply voltage $U_B$ and constant ambient temperature Ta.

## SAFETY-RELATED PARAMETERS

| | |
|---|---|
| $MTTF_D$ | 1,330 years |
| $DC_{avg}$ | 0 % |

## REDUCTION FACTORS

| | |
|---|---|
| Note | The values are reference values which may vary |
| St37 steel (Fe) | 1 |
| Stainless steel (V2A, 304) | Approx. 0.75 |
| Aluminum (Al) | Approx. 0.5 |
| Copper (Cu) | Approx. 0.43 |
| Brass (Br) | Approx. 0.54 |

## INSTALLATION NOTE


| | |
|---|---|
| Remark | Associated graphic see "Installation note" |
| B | 6 mm |
| C | 6.5 mm |
| D | 4.5 mm |
| F | 12 mm |

## CERTIFICATES

| | |
|---|---|
| EU declaration of conformity | ✓ |
| UK declaration of conformity | ✓ |
| ACMA declaration of conformity | ✓ |
| Moroccan declaration of conformity | ✓ |
| China RoHS | ✓ |
| China Compulsory Product Certification (CCC) exempt | ✓ |
| cULus certificate | ✓ |


| | |
|---|---|
| IO-Link certificate | ✓ |
| Information according to Art. 3 of Data Act (Regulation EU 2023/2854) | ✓ |

## INSTALLATION NOTE MOUNTING USING BEF-KH-M06 BRACKET




| Sensor type | Mounting adapter | Overrun (P) | Max. tightening torque ($M_{max}$) |
|---|---|---|---|
| IHM06-1B5******<br>IHM06-02B******<br>IHM06-03B****** | BEF-KH-M06, part no. 2101067 | ≥ 0 mm | ≤ 0.6 Nm |


## INSTALLATION NOTE FIXING WITH SETSCREW





① Sensing face
② Recommended setscrew: M3, flat point
③ Display LED


| Sensor type | Mounting area (L) | Max. tightening torque ($M_{max}$) |
|---|---|---|
| IHM06-********G | 6 mm ... 11 mm | ≤ 0.4 Nm |
| IHM06-******T0G | 6 mm ... 21 mm | ≤ 0.4 Nm |
| IHM06-********K | 6 mm ... 21 mm | ≤ 0.4 Nm |
| IHM06-******T0K | 6 mm ... 32 mm | ≤ 0.4 Nm |
| IHM06-********S | 6 mm ... 32 mm | ≤ 0.4 Nm |
| IHM06-******T0S | 6 mm ... 42 mm | ≤ 0.4 Nm |

## INSTALLATION NOTE FLUSH INSTALLATION





## CONNECTION DIAGRAM CD-002





## RESPONSE DIAGRAM





All dimensions in mm (inch)

## FUNCTIONAL PRINCIPLE INSTALLATION AID



**DIMENSIONAL DRAWING IHM06, EXTREMELY SHORT VARIANT, FLUSH, MALE CONNECTOR**




Dimensions in mm (inch)
① Connection
② function indicator

Further information as well as suitable accessories, example applications and downloads such as CAD dimensional models, operating instructions and software can be found at www.sick.com/1101120

SICK AG
WALDKIRCH
GERMANY
SICK.COM

# SICK AT A GLANCE

SICK is a leading global technology company for intelligent sensors and integrated solutions in industrial automation. Our technologies set benchmarks, making your industrial processes more efficient, safer and more sustainable – both in logistics and manufacturing operations.

SICK combines sensor intelligence with industry expertise and certified consulting services. We provide the ideal foundation for scalable as well as tailor-made automation solutions and create added value along the entire value chain. Our close partnerships with our customers are more than just a promise: Together, we optimize productivity, improve quality, protect health and safety, and help build a sustainable future. All with empathy and trust.

Since 1946, we have been developing innovative technologies with passion and a pioneering spirit. With a global network in around 40 countries, SICK has a global presence and is always close by. The company's headquarters are located in Waldkirch near Freiburg, Germany. Our customers benefit from our understanding of both local and global requirements, which enables us to deliver tailor-made solutions

SICK

Sensor Intelligence