



# RSB1-0550E055165FP4CZZZP0A

Roller Sensor Bar

PHOTOELECTRIC SENSORS

**SICK**  
Sensor Intelligence.



Illustration may differ



## Ordering information

| Type                       | part no. |
|----------------------------|----------|
| RSB1-0550E055165FP4CZZZP0A | 1129423  |

Included in delivery: BEF-AP-RSBADHA (1)

Other models and accessories → [www.sick.com/Roller\\_Sensor\\_Bar](http://www.sick.com/Roller_Sensor_Bar)

## Detailed technical data

## Features

|                                                                                                 |                                                                                       |
|-------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
| <b>Functional principle</b>                                                                     | Photoelectric proximity sensor                                                        |
| <b>Functional principle detail</b>                                                              | Energetic                                                                             |
| <b>Sensing range</b>                                                                            |                                                                                       |
| Sensing range min.                                                                              | 2 mm                                                                                  |
| Sensing range max.                                                                              | 300 mm                                                                                |
| Reference object                                                                                | Object with 90% remission factor (complies with standard white according to DIN 5033) |
| Recommended sensing range for the best performance                                              | 2 mm ... 45 mm                                                                        |
| <b>Emitted beam</b>                                                                             |                                                                                       |
| Light source                                                                                    | LED                                                                                   |
| Type of light                                                                                   | Infrared light                                                                        |
| Shape of light spot                                                                             | Point-shaped                                                                          |
| Light spot size (distance)                                                                      | 27 mm x 29 mm (45 mm)                                                                 |
| Maximum dispersion of the emitted beam around the standardized transmission axis (squint angle) | < +/- 4° (at T <sub>a</sub> = +23 °C)                                                 |
| <b>Key LED figures</b>                                                                          |                                                                                       |
| LED risk group marking                                                                          | Free group                                                                            |
| Wave length                                                                                     | 850 nm                                                                                |
| Average service life                                                                            | 100,000 h at T <sub>a</sub> = +25 °C                                                  |
| <b>Number of beams</b>                                                                          | 5                                                                                     |
| <b>Beam separation</b>                                                                          | 55 mm                                                                                 |
| <b>Distance from 1st beam to leading edge of housing (including end cap)</b>                    | 165 mm                                                                                |
| <b>Smallest detectable object (MDO) typ.</b>                                                    |                                                                                       |
|                                                                                                 | 165 mm, Dependent on distance between beams                                           |
| <b>Adjustment</b>                                                                               |                                                                                       |
| None                                                                                            | –                                                                                     |
| <b>Display</b>                                                                                  |                                                                                       |

|                             |            |                                                                                                                                   |
|-----------------------------|------------|-----------------------------------------------------------------------------------------------------------------------------------|
|                             | LED green  | Operating indicator<br>Static on: power on                                                                                        |
|                             | LED yellow | Status of received light beam<br>Static on: object present<br>Static off: object not present                                      |
| <b>Special applications</b> |            | Detecting flat objects, Detecting perforated objects, Detecting objects with position tolerances, Detecting uneven, shiny objects |

## Electronics

|                                        |                               |                                                                                |
|----------------------------------------|-------------------------------|--------------------------------------------------------------------------------|
| <b>Supply voltage <math>U_B</math></b> |                               | 10 V DC ... 30 V DC                                                            |
| <b>Ripple</b>                          |                               | $\leq 5 \text{ V}_{pp}$                                                        |
| <b>Usage category</b>                  |                               | DC-12 (According to EN 60947-5-2)<br>DC-13 (According to EN 60947-5-2)         |
| <b>Current consumption</b>             |                               | 23 mA, without load. At $U_B = 24 \text{ V}$                                   |
| <b>Protection class</b>                |                               | III                                                                            |
| <b>Digital output</b>                  |                               |                                                                                |
|                                        | Number                        | 1                                                                              |
|                                        | Type                          | PNP                                                                            |
|                                        | Switching mode                | Light/dark switching                                                           |
|                                        | Signal voltage PNP HIGH/LOW   | Approx. $U_B - 2.5 \text{ V} / 0 \text{ V}$                                    |
|                                        | Output current $I_{max.}$     | $\leq 100 \text{ mA}$                                                          |
|                                        | Circuit protection outputs    | Reverse polarity protected<br>Overcurrent protected<br>Short-circuit protected |
|                                        | Response time                 | $\leq 1 \text{ ms}^{1)}$                                                       |
|                                        | Repeatability (response time) | 1 ms                                                                           |
|                                        | Switching frequency           | 500 Hz <sup>2)</sup>                                                           |
| <b>Pin/Wire assignment</b>             |                               |                                                                                |
|                                        | BN 1                          | + (L+)                                                                         |
|                                        | WH 2                          | $Q_2$                                                                          |
|                                        | BU 3                          | - (M)                                                                          |
|                                        | BK 4                          | $Q_1$                                                                          |
|                                        | Function of pin 4/black (BK)  | Digital output, dark switching, object present → output LOW                    |
|                                        | Function of pin 2/white (WH)  | Digital output, light switching, object present → output HIGH                  |

<sup>1)</sup> Signal transit time with resistive load.<sup>2)</sup> With light/dark ratio 1:1.

## Mechanics

|                               |                      |                                                                 |
|-------------------------------|----------------------|-----------------------------------------------------------------|
| <b>Dimensions (W x H x D)</b> |                      | 550 mm x 20.3 mm x 17 mm <sup>1)</sup>                          |
| <b>Connection</b>             |                      | Cable with connector M12, 4-pin, with knurled nut <sup>2)</sup> |
| <b>Connection detail</b>      |                      |                                                                 |
|                               | Deep-freeze property | Do not bend below 0 °C                                          |
|                               | Conductor size       | 0.13 mm <sup>2</sup>                                            |

<sup>1)</sup> W = length of Roller Sensor Bar (in the installed state).<sup>2)</sup> Due to the manufacturing process, the cable can be a little longer.

|                             |                                                               |
|-----------------------------|---------------------------------------------------------------|
| Cable diameter              | Ø 3.6 mm                                                      |
| Length of cable (L)         | 300 mm <sup>2)</sup>                                          |
| <b>Material</b>             |                                                               |
| Housing                     | Metal, Aluminum (anodised)                                    |
| Front screen                | Plastic, PMMA                                                 |
| Cable                       | Plastic, PVC                                                  |
| Male connector              | Plastic, PVC                                                  |
| <b>Weight</b>               | Approx. 199.7 g                                               |
| <b>Mounting system type</b> | BEF-AP-RSBADHA, 8 mm round adapter bracket with adhesive back |

<sup>1)</sup> W = length of Roller Sensor Bar (in the installed state).

<sup>2)</sup> Due to the manufacturing process, the cable can be a little longer.

### Ambient data

|                                            |                                                                                                   |
|--------------------------------------------|---------------------------------------------------------------------------------------------------|
| <b>Enclosure rating</b>                    | IP67 (EN 60529)                                                                                   |
| <b>Ambient operating temperature</b>       | -40 °C ... +60 °C                                                                                 |
| <b>Ambient temperature, storage</b>        | -40 °C ... +75 °C                                                                                 |
| <b>Shock resistance</b>                    | 30 g, 11 ms (3 positive and 3 negative shocks along X, Y, Z axes, 18 total shocks (EN60068-2-27)) |
| <b>Vibration resistance</b>                | 10 Hz ... 55 Hz (Amplitude 1 mm, 3 x 30 min (EN60068-2-6))                                        |
| <b>Air humidity</b>                        | 15 % ... 95 %, relative humidity (no condensation), as per IEC 60947-5-2                          |
| <b>Electromagnetic compatibility (EMC)</b> | EN 60947-5-2                                                                                      |
| <b>UL File No.</b>                         | NRKH.E189383 & NRKH7.E189383                                                                      |

### Certificates


|                                       |   |
|---------------------------------------|---|
| <b>EU declaration of conformity</b>   | ✓ |
| <b>UK declaration of conformity</b>   | ✓ |
| <b>ACMA declaration of conformity</b> | ✓ |
| <b>China RoHS</b>                     | ✓ |
| <b>cULus certificate</b>              | ✓ |

### Classifications

|                     |          |
|---------------------|----------|
| <b>ECLASS 5.0</b>   | 27270904 |
| <b>ECLASS 5.1.4</b> | 27270904 |
| <b>ECLASS 6.0</b>   | 27270904 |
| <b>ECLASS 6.2</b>   | 27270904 |
| <b>ECLASS 7.0</b>   | 27270904 |
| <b>ECLASS 8.0</b>   | 27270904 |
| <b>ECLASS 8.1</b>   | 27270904 |
| <b>ECLASS 9.0</b>   | 27270904 |
| <b>ECLASS 10.0</b>  | 27270904 |
| <b>ECLASS 11.0</b>  | 27270904 |
| <b>ECLASS 12.0</b>  | 27270903 |
| <b>ETIM 5.0</b>     | EC002719 |
| <b>ETIM 6.0</b>     | EC002719 |




Connection type M12 male connector, 4-pin



### Characteristic curve

Operating reserve



Recommended sensing range for the best performance


- ① Black object, 6% remission factor
- ② Gray object, 18% remission factor
- ③ White object, 90% remission factor

## Light spot size

Dimensions in mm (inch)




Recommended sensing range for the best performance



## Light spot size

mm (inch)



- ① Black object, 6% remission factor
- ② Gray object, 18% remission factor
- ③ White object, 90% remission factor

## Recommended accessories

Other models and accessories → [www.sick.com/Roller\\_Sensor\\_Bar](http://www.sick.com/Roller_Sensor_Bar)

|                                                                                     | Brief description                                                                                                                                                                                                                                                                                                                                                                                                                                                            | Type               | part no. |
|-------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------|----------|
| Mounting systems                                                                    |                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |                    |          |
|    | <ul style="list-style-type: none"> <li><b>Description:</b> 8 mm round adapter bracket with adhesive back</li> </ul>                                                                                                                                                                                                                                                                                                                                                          | BEF-AP-RSBADHA     | 2127765  |
|    | <ul style="list-style-type: none"> <li><b>Description:</b> Adapter bracket with adhesive back</li> </ul>                                                                                                                                                                                                                                                                                                                                                                     | BEF-AP-RSBADHB     | 2127766  |
|    | <ul style="list-style-type: none"> <li><b>Description:</b> Adapter bracket to snap between hex sections</li> </ul>                                                                                                                                                                                                                                                                                                                                                           | BEF-AP-RSBCON      | 2127768  |
|    | <ul style="list-style-type: none"> <li><b>Description:</b> Hex adapter bracket</li> </ul>                                                                                                                                                                                                                                                                                                                                                                                    | BEF-AP-RSBHEX      | 2127767  |
|    | <ul style="list-style-type: none"> <li><b>Description:</b> Adapter kit: BEF-AP-RSBADHA, BEF-AP-RSBADHB, BEF-AP-RSBCON, BEF-AP-RSBHEX</li> <li><b>Items supplied:</b> BEF-AP-RSBADHA, BEF-AP-RSBADHB, BEF-AP-RSBCON, BEF-AP-RSBHEX</li> </ul>                                                                                                                                                                                                                                 | BEF-AP-RSBKIT      | 2127759  |
| connectors and cables                                                               |                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |                    |          |
|   | <ul style="list-style-type: none"> <li><b>Connection type head A:</b> Male connector, M12, 4-pin, straight, A-coded</li> <li><b>Description:</b> Unshielded</li> <li><b>Connection systems:</b> Screw-type terminals</li> <li><b>Permitted cross-section:</b> ≤ 0.75 mm<sup>2</sup></li> </ul>                                                                                                                                                                               | STE-1204-G         | 6009932  |
|  | <ul style="list-style-type: none"> <li><b>Connection type head A:</b> Female connector, M12, 4-pin, straight, A-coded</li> <li><b>Connection type head B:</b> Flying leads</li> <li><b>Signal type:</b> Sensor/actuator cable</li> <li><b>Cable:</b> 5 m, 4-wire, PUR, halogen-free</li> <li><b>Description:</b> Sensor/actuator cable, unshielded</li> <li><b>Application:</b> Drag chain operation, Zones with oils and lubricants, Robot, Drag chain operation</li> </ul> | YF2A14-050UB3XLEAX | 2095608  |
|  | <ul style="list-style-type: none"> <li><b>Connection type head A:</b> Female connector, M12, 4-pin, straight, A-coded</li> <li><b>Connection type head B:</b> Flying leads</li> <li><b>Signal type:</b> Sensor/actuator cable</li> <li><b>Cable:</b> 5 m, 4-wire, PVC</li> <li><b>Description:</b> Sensor/actuator cable, unshielded</li> <li><b>Application:</b> Uncontaminated zones, Zones with chemicals</li> </ul>                                                      | YF2A14-050VB3XLEAX | 2096235  |

## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

**For us, that is “Sensor Intelligence.”**

## WORLDWIDE PRESENCE:

Contacts and other locations –[www.sick.com](http://www.sick.com)