SICK.COM



DATA SHEET

UM30-213111S12

UM30
Ultrasonic distance sensors

SICK
Sensor Intelligence



ULTRASONIC DISTANCE SENSORS

UM30-213111S12

ORDERING INFORMATION

Type	part no.
UM30-213111S12	6057291

Further device versions and accessories at www.sick.com/UM30

DETAILED TECHNICAL DATA

FEATURES

Operating range, limiting range	200 mm ... 1,300 mm, 2,000 mm
Resolution	≥ 0.18 mm
Repeatability	± 0.15 % [1]
Measurement accuracy	± 1 % [2] [3]
Temperature compensation	✓
Response time	92 ms
Switching frequency	8 Hz
Output time	23 ms
Ultrasonic frequency (typical)	200 kHz
Detection area (typical)	See diagrams
Additional function	Adjustable operating modes: Switching point (DtO) / Switching window/Background (ObSB), teach-in of digital output, set levels of digital outputs, invertable digital output, set on delay digital output, synchronization of up to 50 sensors, multiplexing: no cross talk of up to 50 sensors, adjustable measurement filters: Measured value filters/Filter strength/Foreground suppression/Detection area/Sensitivity and sound beam, Display (can be deactivated), reset to factory default
Special characteristic	Platform detection

[1] In relation to the current measured value, minimum value ≥ resolution.

[2] Referring to current measurement value.

[3] Temperature compensation can be switched off, without temperature compensation: 0.17 % / K.

INTERFACES

Digital output	
Number	1 [1]
Type	PNP
Maximum output current I_A	≤ 200 mA
Multifunctional input (MF)	1 x MF

[1] PNP: HIGH = V_S - (< 2 V) / LOW = 0 V.

Hysteresis	20 mm

[1] PNP: HIGH = V_S - (< 2 V) / LOW = 0 V.

ELECTRONICS

Supply voltage U_B	DC 9 V ... 30 V [1]
Power consumption	≤ 2.4 W [2]
Initialization time	< 300 ms
Display	LED display, 2 x LED
Enclosure rating	IP65 / IP67
Protection class	III

[1] Limit values, reverse-polarity protected Operation in short-circuit protected network: max. 8 A, class 2.

[2] Without load.

MECHANICS

Dimensions (W x H x D)	30 mm x 30 mm x 84 mm
Design	Cylindrical
Sending axis	Straight
Housing material	Metal (nickel-plated brass, PBT, ultrasonic transducer: polyurethane foam, glass epoxy resin)
Weight	150 g
Thread size	M30 x 1.5
Connection type	Male connector, M12, 5-pin


AMBIENT DATA

Ambient temperature, operation	–25 °C ... +70 °C
Ambient temperature, storage	–40 °C ... +85 °C

CERTIFICATES


EU declaration of conformity	✓
UK declaration of conformity	✓
ACMA declaration of conformity	✓
China Compulsory Product Certification (CCC) exempt	✓
cULus certificate	✓

DIMENSIONAL DRAWING UM30-211, UM30-212, UM30-213




Dimensions in mm (inch)
① Connection
② Display
③ Mounting nuts, SW 36 mm

CONNECTION TYPE




CONNECTION DIAGRAM UM30-21X111 UM30-21X114 CONNECTOR M12, 5-PIN




① Not assigned
② Synchronization and multiplex mode, Connect+ communication

ADJUSTMENT POSSIBLE



② Display
④ Control elements
⑤ Status indicators

DETECTION AREA



① Detection range dependent on reflection properties, size, and alignment of the object
② Limiting range
③ operating range
④ example object: aligned plate 500 mm x 500 mm
⑤ example object: pipe with 27 mm diameter

Further information as well as suitable accessories, example applications and downloads such as CAD dimensional models, operating instructions and software can be found at www.sick.com/6057291

SICK AG
WALDKIRCH
GERMANY
SICK.COM

SICK AT A GLANCE

SICK is a leading global technology company for intelligent sensors and integrated solutions in industrial automation. Our technologies set benchmarks, making your industrial processes more efficient, safer and more sustainable – both in logistics and manufacturing operations.

SICK combines sensor intelligence with industry expertise and certified consulting services. We provide the ideal foundation for scalable as well as tailor-made automation solutions and create added value along the entire value chain. Our close partnerships with our customers are more than just a promise: Together, we optimize productivity, improve quality, protect health and safety, and help build a sustainable future. All with empathy and trust.

Since 1946, we have been developing innovative technologies with passion and a pioneering spirit. With a global network in around 40 countries, SICK has a global presence and is always close by. The company's headquarters are located in Waldkirch near Freiburg, Germany. Our customers benefit from our understanding of both local and global requirements, which enables us to deliver tailor-made solutions

SICK

Sensor Intelligence