



DATA SHEET

WLD26P-341121A0ZZZ

W26
Photoelectric sensors

SICK

Sensor Intelligence



Illustration may differ

PHOTOELECTRIC SENSORS

WLD26P-341121A0ZZZ

ORDERING INFORMATION

Type	part no.
WLD26P-341121A0ZZZ	1221733

Further device versions and accessories at www.sick.com/W26



DETAILED TECHNICAL DATA

FEATURES

Functional principle	Photoelectric retro-reflective sensor	
Functional principle detail	With minimum distance to reflector (dual lens system)	
Sensing range	Sensing range min.	0.25 m
	Sensing range max.	19 m
	Maximum distance range from reflector to sensor (operating reserve 1)	0.25 m ... 19 m
	Recommended distance range from reflector to sensor (operating reserve 3,75)	0.2 m ... 14 m
	Reference reflector	Reflector PL80A
	Recommended sensing range for the best performance	0.25 m ... 14 m
Polarisation filter	Yes	
Emitted beam	Light source	PinPoint LED
	Type of light	Visible red light
	Shape of light spot	Point-shaped
	Light spot size (distance)	Ø 16 mm (1 m)
	Maximum dispersion of the emitted beam around the standardized transmission axis (squint angle)	< +/- 1.0° (at T ₀ = +23 °C)
Key LED figures	Normative reference	EN 62471:2008-09 IEC 62471:2006, modified
	LED risk group marking	Free group
	Wave length	635 nm
	Average service life	100,000 h at T _a = +25 °C
Adjustment	None	-
Display	LED green	Operating indicator Static on: power on
	LED yellow	Status of received light beam Static on: object not present Static off: object present

Flashing: Below the 1.5 function reserve

SAFETY-RELATED PARAMETERS

MTTF _D	2,009 years
DC _{avg}	0%
T _M (mission time)	20 years

ELECTRONICS

Supply voltage U _B	10 V DC ... 30 V DC ¹⁾																				
Ripple	≤ 5 V _{pp}																				
Usage category	DC-12 (According to EN 60947-5-2) DC-13 (According to EN 60947-5-2)																				
Current consumption	≤ 30 mA, without load. At U _B = 24 V																				
Protection class	III																				
Digital output	<table> <tr> <td>Number</td><td>2 (Complementary)</td></tr> <tr> <td>Type</td><td>Push-pull: PNP/NPN</td></tr> <tr> <td>Switching mode</td><td>Light/dark switching</td></tr> <tr> <td>Signal voltage PNP HIGH/LOW</td><td>Approx. U_B - 2.5 V / 0 V</td></tr> <tr> <td>Signal voltage NPN HIGH/LOW</td><td>Approx. U_B / < 2.5 V</td></tr> <tr> <td>Output current I_{max}</td><td>≤ 100 mA</td></tr> <tr> <td>Circuit protection outputs</td><td>Reverse polarity protected Overcurrent and short-circuit protected</td></tr> <tr> <td>Response time</td><td>≤ 500 μs ²⁾</td></tr> <tr> <td>Repeatability (response time)</td><td>150 μs</td></tr> <tr> <td>Switching frequency</td><td>1,000 Hz ³⁾</td></tr> </table>	Number	2 (Complementary)	Type	Push-pull: PNP/NPN	Switching mode	Light/dark switching	Signal voltage PNP HIGH/LOW	Approx. U _B - 2.5 V / 0 V	Signal voltage NPN HIGH/LOW	Approx. U _B / < 2.5 V	Output current I _{max}	≤ 100 mA	Circuit protection outputs	Reverse polarity protected Overcurrent and short-circuit protected	Response time	≤ 500 μs ²⁾	Repeatability (response time)	150 μs	Switching frequency	1,000 Hz ³⁾
Number	2 (Complementary)																				
Type	Push-pull: PNP/NPN																				
Switching mode	Light/dark switching																				
Signal voltage PNP HIGH/LOW	Approx. U _B - 2.5 V / 0 V																				
Signal voltage NPN HIGH/LOW	Approx. U _B / < 2.5 V																				
Output current I _{max}	≤ 100 mA																				
Circuit protection outputs	Reverse polarity protected Overcurrent and short-circuit protected																				
Response time	≤ 500 μs ²⁾																				
Repeatability (response time)	150 μs																				
Switching frequency	1,000 Hz ³⁾																				
Pin/Wire assignment	<table> <tr> <td>Function of pin 4/black (BK)</td><td>Digital output, light switching, object present → output Q LOW ⁴⁾</td></tr> <tr> <td>Function of pin 2/white (WH)</td><td>Digital output, dark switching, object present → output Q̄ HIGH ⁴⁾</td></tr> </table>	Function of pin 4/black (BK)	Digital output, light switching, object present → output Q LOW ⁴⁾	Function of pin 2/white (WH)	Digital output, dark switching, object present → output Q̄ HIGH ⁴⁾																
Function of pin 4/black (BK)	Digital output, light switching, object present → output Q LOW ⁴⁾																				
Function of pin 2/white (WH)	Digital output, dark switching, object present → output Q̄ HIGH ⁴⁾																				

¹⁾ Limit values.²⁾ Signal transit time with resistive load in switching mode.³⁾ With light/dark ratio 1:1.⁴⁾ This switching output must not be connected to another output.**MECHANICS**

Housing	Rectangular														
Dimensions (W x H x D)	24.6 mm x 82.5 mm x 53.3 mm														
Connection	Cable with plug, M12, 4-pin, 318 mm														
Connection detail	<table> <tr> <td>Deep-freeze property</td><td>Do not bend below 0 °C</td></tr> <tr> <td>Conductor size</td><td>0.14 mm²</td></tr> <tr> <td>Cable diameter</td><td>Ø 4.8 mm</td></tr> <tr> <td>Length of cable (L)</td><td>270 mm</td></tr> <tr> <td>Length of male connector</td><td>48 mm</td></tr> <tr> <td>Bending radius</td><td>For flexible use > 12 x cable diameter</td></tr> <tr> <td>Bending cycles</td><td>1,000,000</td></tr> </table>	Deep-freeze property	Do not bend below 0 °C	Conductor size	0.14 mm ²	Cable diameter	Ø 4.8 mm	Length of cable (L)	270 mm	Length of male connector	48 mm	Bending radius	For flexible use > 12 x cable diameter	Bending cycles	1,000,000
Deep-freeze property	Do not bend below 0 °C														
Conductor size	0.14 mm ²														
Cable diameter	Ø 4.8 mm														
Length of cable (L)	270 mm														
Length of male connector	48 mm														
Bending radius	For flexible use > 12 x cable diameter														
Bending cycles	1,000,000														
Material	<table> <tr> <td>Housing</td><td>Plastic, VISTAL®</td></tr> <tr> <td>Front screen</td><td>Plastic, PMMA</td></tr> <tr> <td>Cable</td><td>Plastic, PVC</td></tr> <tr> <td>Male connector</td><td>Plastic, VISTAL®</td></tr> </table>	Housing	Plastic, VISTAL®	Front screen	Plastic, PMMA	Cable	Plastic, PVC	Male connector	Plastic, VISTAL®						
Housing	Plastic, VISTAL®														
Front screen	Plastic, PMMA														
Cable	Plastic, PVC														
Male connector	Plastic, VISTAL®														
Weight	Approx. 100 g														

Maximum tightening torque of the fixing screws	1.3 Nm
--	--------


AMBIENT DATA

Enclosure rating	IP66 (EN 60529) IP67 (EN 60529) IP69 (EN 60529) ¹⁾
Ambient operating temperature	−40 °C ... +60 °C
Ambient temperature, storage	−40 °C ... +75 °C
Shock resistance	50 g, 11 ms (25 positive and 25 negative shocks per axis, for X, Y, Z axes, 150 shocks in total (EN60068-2-27)) 50 g, 6 ms (5,000 positive and 5,000 negative shocks per axis, for X, Y, Z axes, 30,000 shocks in total (EN60068-2-27))
Vibration resistance	10 Hz ... 2,000 Hz (Amplitude 0.5 mm / 10 g, 20 sweeps per axis, for X, Y, Z axes, 1 octave/min, (EN60068-2-6))
Air humidity	35 % ... 95 %, relative humidity (no condensation)
Electromagnetic compatibility (EMC)	EN 60947-5-2
Resistance to cleaning agent	ECOLAB
UL File No.	NRKH.E181493 & NRKH7.E181493

¹⁾ Replaces IP69K with ISO 20653: 2013-03.


CERTIFICATES

EU declaration of conformity	✓
UK declaration of conformity	✓
ACMA declaration of conformity	✓
Moroccan declaration of conformity	✓
China RoHS	✓
China Compulsory Product Certification (CCC) ex-empt	✓
ECOLAB certificate	✓
cULus certificate	✓
Photobiological safety (DIN EN 62471) certificate	✓

DIMENSIONAL DRAWING, SENSOR

Dimensions in mm (inch)

- ① Center of optical axis, sender
- ② Center of optical axis, receiver
- ③ Mounting hole, Ø 5.2 mm
- ④ Connection
- ⑤ display and adjustment elements


DIMENSIONAL DRAWING, CONNECTION

Dimensions in mm (inch)

For length of cable (L), see technical data


- ① Cable with M12 male connector

DISPLAY AND ADJUSTMENT ELEMENTS




- ① LED indicator green
- ② LED indicator yellow


CONNECTION TYPE M12 MALE CONNECTOR, 4-PIN





CONNECTION DIAGRAM CD-414





CONNECTION DIAGRAM CD-390




TRUTH TABLE PUSH-PULL: PNP/NPN - DARK SWITCHING $\bar{Q}$

	Dark switching $\bar{Q}$ (normally open (upper switch), normally closed (lower switch))	
	Object not present → Output LOW	Object present → Output HIGH
Light receive	✓	✗
Light receive indicator	☀	✗
Load resistance to L+	⚡	✗
Load resistance to M	✗	⚡
		

TRUTH TABLE PUSH-PULL: PNP/NPN - LIGHT SWITCHING Q


	Light switching Q (normally closed (upper switch), normally open (lower switch))	
	Object not present → Output HIGH	Object present → Output LOW
Light receive	✓	✗
Light receive indicator	☀	✗
Load resistance to L+	✗	⚡
Load resistance to M	⚡	✗
		

CHARACTERISTIC CURVE




- Recommended sensing range for the best performance
- ① Reflective tape REF-IRF-56 (50 x 70 mm)

CHARACTERISTIC CURVE



- Recommended sensing range for the best performance
- ① Reflector PL20 CHEM
② Reflector P250 CHEM
③ Reflector P250H
④ Reflector PL40A Antifog


CHARACTERISTIC CURVE



Recommended sensing range for the best performance


- ① Reflector PL22
- ② Reflector P250
- ③ Reflector PL20A
- ④ Reflector PL30A
- ⑤ Reflector PL40A
- ⑥ Reflector C110
- ⑦ Reflector PL80A

LIGHT SPOT SIZE



Recommended sensing range for the best performance


SENSING RANGE DIAGRAM



Recommended sensing range for the best performance

1	Reflective tape REF-IRF-56 (50 x 70 mm)
A	Sensing range min. in m
B	Sensing range max. in m
C	Maximum distance range from reflector to sensor (operating reserve 1)
D	Recommended distance range from reflector to sensor (operating reserve 3,75)


SENSING RANGE DIAGRAM



Recommended sensing range for the best performance

1	Reflector PL20 CHEM
2	Reflector P250 CHEM
3	Reflector P250H
4	Reflector PL40A Antifog
A	Sensing range min. in m
B	Sensing range max. in m
C	Maximum distance range from reflector to sensor (operating reserve 1)
D	Recommended distance range from reflector to sensor (operating reserve 3,75)


SENSING RANGE DIAGRAM



Recommended sensing range for the best performance

1	Reflector PL22
2	Reflector P250
3	Reflector PL20A
4	Reflector PL30A
5	Reflector PL40A
6	Reflector C110
7	Reflector PL80A
A	Sensing range min. in m
B	Sensing range max. in m
C	Maximum distance range from reflector to sensor (operating reserve 1)
D	Recommended distance range from reflector to sensor (operating reserve 3,75)

FUNCTIONS OPERATION NOTE



At a sensing range of „x“ the photoelectric retro-reflective and through-beam photoelectric sensors have different operating reserves (see blue arrow). The higher the operating reserve factor, the better the sensor can compensate the contamination in the air or in the light beam and on the optical surfaces (front screen, reflector), i.e. the sensor has the maximum availability, otherwise the sensor switches due to pollution although there is no object in the path of the light beam.

Further information as well as suitable accessories, example applications and downloads such as CAD dimensional models, operating instructions and software can be found at www.sick.com/1221733



SICK AG
WALDKIRCH
GERMANY
SICK.COM

SICK AT A GLANCE

SICK is a leading global technology company for intelligent sensors and integrated solutions in industrial automation. Our technologies set benchmarks, making your industrial processes more efficient, safer and more sustainable – both in logistics and manufacturing operations.

SICK combines sensor intelligence with industry expertise and certified consulting services. We provide the ideal foundation for scalable as well as tailor-made automation solutions and create added value along the entire value chain. Our close partnerships with our customers are more than just a promise: Together, we optimize productivity, improve quality, protect health and safety, and help build a sustainable future. All with empathy and trust.

Since 1946, we have been developing innovative technologies with passion and a pioneering spirit. With a global network in around 40 countries, SICK has a global presence and is always close by. The company's headquarters are located in Waldkirch near Freiburg, Germany. Our customers benefit from our understanding of both local and global requirements, which enables us to deliver tailor-made solutions

SICK
Sensor Intelligence