



# IME30-38NPSZW2S


IME

INDUCTIVE PROXIMITY SENSORS

**SICK**  
Sensor Intelligence.



Illustration may differ



### Ordering information

| Type            | part no. |
|-----------------|----------|
| IME30-38NPSZW2S | 1071305  |

Included in delivery: BEF-MU-M30 (1)

Other models and accessories → [www.sick.com/IME](http://www.sick.com/IME)

### Detailed technical data

#### Features

|                                            |                                         |
|--------------------------------------------|-----------------------------------------|
| <b>Housing</b>                             | Metric                                  |
| <b>Housing</b>                             | Standard design                         |
| <b>Thread size</b>                         | M30 x 1.5                               |
| <b>Diameter</b>                            | Ø 30 mm                                 |
| <b>Sensing range <math>S_n</math></b>      | 38 mm                                   |
| <b>Safe sensing range <math>S_a</math></b> | 30.78 mm                                |
| <b>Installation type</b>                   | Non-flush                               |
| <b>Switching frequency</b>                 | 100 Hz                                  |
| <b>Connection type</b>                     | Cable, 3-wire, 2 m                      |
| <b>Switching output</b>                    | PNP                                     |
| <b>Switching output detail</b>             | PNP                                     |
| <b>Output function</b>                     | NO                                      |
| <b>Electrical wiring</b>                   | DC 3-wire                               |
| <b>Enclosure rating</b>                    | IP67 <sup>1)</sup>                      |
| <b>Special features</b>                    | Triple sensing range                    |
| <b>Items supplied</b>                      | Mounting nut, brass, nickel-plated (2x) |

<sup>1)</sup> According to EN 60529.

#### Mechanics/electronics

|                       |                     |
|-----------------------|---------------------|
| <b>Supply voltage</b> | 10 V DC ... 30 V DC |
| <b>Ripple</b>         | ≤ 10 %              |

<sup>1)</sup> At  $I_a$  max.

<sup>2)</sup> Supply voltage  $U_B$  and constant ambient temperature  $T_a$ .

<sup>3)</sup> Of  $S_r$ .

|                                                |                                   |
|------------------------------------------------|-----------------------------------|
| <b>Voltage drop</b>                            | $\leq 2 \text{ V}^{1)}$           |
| <b>Time delay before availability</b>          | $\leq 200 \text{ ms}$             |
| <b>Warm-up time</b>                            | 90 s                              |
| <b>Hysteresis</b>                              | 1 % ... 15 %                      |
| <b>Reproducibility</b>                         | $\leq 5 \text{ \%}^{2)}$<br>3)    |
| <b>Temperature drift (of <math>S_r</math>)</b> | $\pm 10 \text{ \%}$               |
| <b>EMC</b>                                     | According to EN 60947-5-2         |
| <b>Continuous current <math>I_a</math></b>     | $\leq 200 \text{ mA}$             |
| <b>No load current</b>                         | $\leq 10 \text{ mA}$              |
| <b>Cable material</b>                          | PVC                               |
| <b>Conductor size</b>                          | 0.25 mm <sup>2</sup>              |
| <b>Cable diameter</b>                          | Ø 3.9 mm                          |
| <b>Short-circuit protection</b>                | ✓                                 |
| <b>Power-up pulse protection</b>               | ✓                                 |
| <b>Shock and vibration resistance</b>          | 30 g, 11 ms/10 Hz ... 55 Hz, 1 mm |
| <b>Ambient operating temperature</b>           | -25 °C ... +75 °C                 |
| <b>Ambient temperature, storage</b>            | -25 °C ... +75 °C                 |
| <b>Housing material</b>                        | Brass, nickel-plated              |
| <b>Sensing face material</b>                   | Plastic, PA 66                    |
| <b>Housing length</b>                          | 70 mm                             |
| <b>Thread length</b>                           | 41 mm                             |
| <b>Tightening torque, max.</b>                 | $\leq 70 \text{ Nm}$              |
| <b>UL File No.</b>                             | NRKH.E181493                      |

1) At  $I_a$  max.

2) Supply voltage  $U_B$  and constant ambient temperature  $T_a$ .

3) Of  $S_r$ .

### Safety-related parameters

|                         |             |
|-------------------------|-------------|
| <b>MTTF<sub>D</sub></b> | 1,735 years |
| <b>DC<sub>avg</sub></b> | 0 %         |

### Reduction factors

|                                   |                                                |
|-----------------------------------|------------------------------------------------|
| <b>Note</b>                       | The values are reference values which may vary |
| <b>St37 steel (Fe)</b>            | 1                                              |
| <b>Stainless steel (V2A, 304)</b> | Approx. 0.77                                   |
| <b>Aluminum (Al)</b>              | Approx. 0.44                                   |
| <b>Copper (Cu)</b>                | Approx. 0.37                                   |
| <b>Brass (Br)</b>                 | Approx. 0.46                                   |

### Installation note

|               |                                       |
|---------------|---------------------------------------|
| <b>Remark</b> | Associated graphic see "Installation" |
| <b>A</b>      | 80 mm                                 |
| <b>B</b>      | 180 mm                                |

|          |        |
|----------|--------|
| <b>C</b> | 30 mm  |
| <b>D</b> | 114 mm |
| <b>E</b> | 35 mm  |
| <b>F</b> | 380 mm |


#### Classifications

|                       |          |
|-----------------------|----------|
| <b>ECLASS 5.0</b>     | 27270101 |
| <b>ECLASS 5.1.4</b>   | 27270101 |
| <b>ECLASS 6.0</b>     | 27270101 |
| <b>ECLASS 6.2</b>     | 27270101 |
| <b>ECLASS 7.0</b>     | 27270101 |
| <b>ECLASS 8.0</b>     | 27270101 |
| <b>ECLASS 8.1</b>     | 27270101 |
| <b>ECLASS 9.0</b>     | 27270101 |
| <b>ECLASS 10.0</b>    | 27270101 |
| <b>ECLASS 11.0</b>    | 27270101 |
| <b>ECLASS 12.0</b>    | 27274001 |
| <b>ETIM 5.0</b>       | EC002714 |
| <b>ETIM 6.0</b>       | EC002714 |
| <b>ETIM 7.0</b>       | EC002714 |
| <b>ETIM 8.0</b>       | EC002714 |
| <b>UNSPSC 16.0901</b> | 39122230 |


#### Certificates

|                                           |   |
|-------------------------------------------|---|
| <b>EU declaration of conformity</b>       | ✓ |
| <b>UK declaration of conformity</b>       | ✓ |
| <b>ACMA declaration of conformity</b>     | ✓ |
| <b>Moroccan declaration of conformity</b> | ✓ |
| <b>China RoHS</b>                         | ✓ |
| <b>cULus certificate</b>                  | ✓ |


#### Installation note Non-flush installation



Connection diagram Cd-001



Dimensional drawing IME30 Standard, cable, non-flush



- Dimensions in mm (inch)
- ① Connection
  - ② Display LED
  - ③ Fastening nuts (2x); width across 36, metal

Recommended accessories

Other models and accessories → [www.sick.com/IME](http://www.sick.com/IME)

|                                                                                     | Brief description                                                                                                                                                                                                                               | Type       | part no. |
|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------|----------|
| Mounting systems                                                                    |                                                                                                                                                                                                                                                 |            |          |
|  | <ul style="list-style-type: none"><li>• <b>Description:</b> Mounting bracket for M30 sensors</li><li>• <b>Material:</b> Steel</li><li>• <b>Details:</b> Steel, zinc coated</li><li>• <b>Items supplied:</b> Without mounting hardware</li></ul> | BEF-WN-M30 | 5308445  |
|  | <ul style="list-style-type: none"><li>• <b>Description:</b> Mounting plate for M30 sensors</li><li>• <b>Material:</b> Steel</li><li>• <b>Details:</b> Steel, zinc coated</li><li>• <b>Items supplied:</b> Without mounting hardware</li></ul>   | BEF-WG-M30 | 5321871  |

## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

## WORLDWIDE PRESENCE:

Contacts and other locations –[www.sick.com](http://www.sick.com)