



DATA SHEET

WTV4FE-1H162120A00

W4
Photoelectric sensors

SICK Sensor Intelligence



Illustration may differ

PHOTOELECTRIC SENSORS

WTV4FE-1H162120A00

ORDERING INFORMATION

Type	part no.
WTV4FE-1H162120A00	1120896

Further device versions and accessories at www.sick.com/W4



DETAILED TECHNICAL DATA

FEATURES

Functional principle		Photoelectric proximity sensor
Functional principle detail		Background suppression, V-optics
Sensing range		
	Sensing range min.	2 mm
	Sensing range max.	50 mm
Adjustable switching threshold for background suppression		15 mm ... 50 mm
	Reference object	Object with 90% remission factor (complies with standard white according to DIN 5033)
Minimum distance between set sensing range and background (black 6% / white 90%)		1 mm, at a distance of 21 mm
Recommended sensing range for the best performance		15 mm ... 30 mm
Emitted beam		
	Light source	PinPoint LED
	Type of light	Visible red light
	Shape of light spot	Rectangular
	Light spot size (distance)	0.5 mm x 1.9 mm (30 mm)
Maximum dispersion of the emitted beam around the standardized transmission axis (squint angle)		< +/- 1.5° (at T _u = +23 °C)
Key LED figures		
	Normative reference	EN 62471:2008-09 IEC 62471:2006, modified
	LED risk group marking	Free group
	Wave length	635 nm
	Average service life	100,000 h at T _a = +25 °C
Smallest detectable object (MDO) typ.		0.1 mm, At 30 mm distance (object with 90% remission (complies with standard white according to DIN 5033))
Adjustment		
	Teach-Turn adjustment	BluePilot For setting the sensing range

	IO-Link	For configuring the sensor parameters and Smart Task functions
Display		
	LED blue	BluePilot: sensing range indicator
	LED green	Operating indicator Static on: power on Flashing: IO-Link mode
	LED yellow	Status of received light beam Static on: object present Static off: object not present
Special applications		Detecting transparent objects

SAFETY-RELATED PARAMETERS

MTTF _D	661 years
DC _{avg}	0 %
T _M (mission time)	20 years

COMMUNICATION INTERFACE

IO-Link	✓, IO-Link V1.1
Data transmission rate	COM2 (38,4 kBaud)
Cycle time	2.3 ms
Process data length	16 Bit
Process data structure	Bit 0 = switching signal Q _{L1} Bit 1 = switching signal Q _{L2} Bit 2 ... 15 = Current receiver level (live)
VendorID	26
DeviceID HEX	0x8002B3
DeviceID DEC	8389299
Compatible master port type	A
SIO mode support	Yes

ELECTRONICS

Supply voltage U _B	10 V DC ... 30 V DC ¹⁾
Ripple	≤ 5 V _{pp}
Usage category	DC-12 (According to EN 60947-5-2) DC-13 (According to EN 60947-5-2)
Current consumption	≤ 25 mA, without load. At U _B = 24 V
Protection class	III
Digital output	
Number	2 (Complementary)
Type	Push-pull: PNP/NPN
Switching mode	Light/dark switching
Signal voltage PNP HIGH/LOW	Approx. U _B - 2.5 V / 0 V
Signal voltage NPN HIGH/LOW	Approx. U _B / < 2.5 V
Output current I _{max}	≤ 100 mA
Circuit protection outputs	Reverse polarity protected Overcurrent protected Short-circuit protected
Response time	≤ 500 μs
Repeatability (response time)	150 μs ²⁾

¹⁾ Limit values.

²⁾ Signal transit time with resistive load in switching mode.

³⁾ With light/dark ratio 1:1.

⁴⁾ This switching output must not be connected to another output.

Switching frequency		1,000 Hz ³⁾
Pin/Wire assignment	Function of pin 4/black (BK)	Digital output, dark switching, object present → output $\bar{Q}_{L1}$ LOW; IO-Link communication C ⁴⁾
	Function of pin 4/black (BK) – detail	The pin 4 function of the sensor can be configured Additional possible settings via IO-Link
	Function of pin 2/white (WH)	Digital output, light switching, object present → output Q_{L1} HIGH ⁴⁾
	Function of pin 2/white (WH) – detail	The pin 2 function of the sensor can be configured Additional possible settings via IO-Link

¹⁾ Limit values.

²⁾ Signal transit time with resistive load in switching mode.

³⁾ With light/dark ratio 1:1.

⁴⁾ This switching output must not be connected to another output.

MECHANICS

Housing		Rectangular
Design detail		Flat
Dimensions (W x H x D)		16 mm x 40.1 mm x 12.1 mm
Connection		Cable, 4-wire, 2 m
Connection detail	Deep-freeze property	Do not bend below 0 °C
	Conductor size	0.14 mm ²
	Cable diameter	Ø 3.4 mm
	Length of cable (L)	2 m
Material	Housing	Plastic, VISTAL®
	Front screen	Plastic, PMMA
	Cable	Plastic, PVC
Weight		Approx. 30 g
Maximum tightening torque of the fixing screws		0.4 Nm

AMBIENT DATA

Enclosure rating		IP66 (EN 60529) IP67 (EN 60529)
Ambient operating temperature		–40 °C ... +60 °C
Ambient temperature, storage		–40 °C ... +75 °C
Typ. Ambient light immunity		Artificial light: ≤ 50,000 lx Sunlight: ≤ 50,000 lx
Shock resistance		30 g, 11 ms (3 positive and 3 negative shocks along X, Y, Z axes, 18 total shocks (EN60068-2-27))
Vibration resistance		10 Hz ... 1,000 Hz (Amplitude 1 mm, 3 x 30 min (EN60068-2-6))
Air humidity		35 % ... 95 %, relative humidity (no condensation)
Electromagnetic compatibility (EMC)		EN 60947-5-2
Resistance to cleaning agent		ECOLAB
UL File No.		NRKH.E181493 & NRKH7.E181493

SMART TASK

Smart Task name	Base logics
Logic function	Direct AND OR
Timer function	Deactivated

¹⁾ Use of Smart Task functions without IO-Link communication (SIO mode).

²⁾ Use of Smart Task functions with IO-Link communication function.

	Switch-on delay Off delay ON and OFF delay Impulse (one shot)
Inverter	Yes
Switching frequency	SIO Logic: 900 Hz ¹⁾ IOL: 800 Hz ²⁾
Response time	SIO Logic: 550 µs ¹⁾ IOL: 600 µs ²⁾
Repeatability	SIO Logic: 200 µs ¹⁾ IOL: 250 µs ²⁾
Switching signal	Switching signal Q_{L1} Switching output Switching signal $\bar{Q}_{L1}$ Switching output

¹⁾ Use of Smart Task functions without IO-Link communication (SIO mode).

²⁾ Use of Smart Task functions with IO-Link communication function.


DIAGNOSIS

Device temperature	Measuring range	Very cold, cold, moderate, warm, hot
Device status		Yes
Detailed device status		Yes
Operating hour counter		Yes
Operating hours counter with reset function		Yes
Quality of teach		Yes

CERTIFICATES

EU declaration of conformity	✓
UK declaration of conformity	✓
ACMA declaration of conformity	✓
Moroccan declaration of conformity	✓
China RoHS	✓
China Compulsory Product Certification (CCC) exempt	✓
ECOLAB certificate	✓
cULus certificate	✓
IO-Link certificate	✓
Photobiological safety (DIN EN 62471) certificate	✓
Information according to Art. 3 of Data Act (Regulation EU 2023/2854)	✓



DISPLAY AND ADJUSTMENT ELEMENTS



- ① LED blue
- ② Teach-Turn adjustment
- ③ LED yellow
- ④ LED green

INSTALLATION NOTE ANGLE OF ACCEPTANCE, ON HIGH-GLOSSY OBJECT, B


High-glossy object, angle of acceptance




Example:
Set sensing range $x = 30$ mm
Angle of acceptance between -7° and $+7^\circ$

INSTALLATION NOTE ANGLE OF ACCEPTANCE, ON HIGH-GLOSSY OBJECT, A

High-glossy object, angle of acceptance




Recommended sensing range for the best performance



Example:
Set sensing range $x = 30$ mm
Angle of acceptance between -12° and $+5^\circ$


INSTALLATION NOTE ANGLE OF ACCEPTANCE, PANE OF GLASS IN FRONT OF BACKGROUND, B

Transparent pane of glass in front of background (18 % remission), angle of acceptance



$d = 10$ mm $d = 120$ mm
 $d = 40$ mm $d \geq 200$ mm
 $d = 80$ mm


Recommended sensing range for the best performance




Example:
Set sensing range $x = 30$ mm
Distance object to background $d \geq 200$ mm
Angle of acceptance between -6° and $+6^\circ$

INSTALLATION NOTE ANGLE OF ACCEPTANCE, PANE OF GLASS IN FRONT OF BACKGROUND, A


Transparent pane of glass in front of background
(18 % remission), angle of acceptance



CONNECTION TYPE CABLE, 4-WIRE



CONNECTION DIAGRAM CD-504



TRUTH TABLE PUSH-PULL: PNP/NPN - LIGHT SWITCHING Q



	Light switching Q (normally open (upper switch), normally closed (lower switch))	
	Object not present → Output LOW	Object present → Output HIGH
Light receive	✗	✓
Light receive indicator	✗	☀
Load resistance to L+	⚡	✗
Load resistance to M	✗	⚡

TRUTH TABLE PUSH-PULL: PNP/NPN - DARK SWITCHING $\bar{Q}$

	Dark switching $\bar{Q}$ (normally closed (upper switch), normally open (lower switch))	
	Object not present → Output HIGH	Object present → Output LOW
Light receive	✗	✓
Light receive indicator	✗	☀
Load resistance to L+	✗	⚡
Load resistance to M	⚡	✗



CHARACTERISTIC CURVE

Minimum distance in mm (y) between the set sensing range and white background (90 % remission)





LIGHT SPOT SIZE VERTICAL

Dimensions in mm (inch)



LIGHT SPOT SIZE HORIZONTAL

Dimensions in mm (inch)

**SENSING RANGE DIAGRAM**

A = Sensing range min. in mm

B = Sensing range max. in mm

C = Viewing range

D = Adjustable switching threshold for background suppression

E = Sensing range indicator

F = Teach-Turn adjustment

Recommended sensing range for the best performance


① ultra-black object, 1% remission factor

② Black object, 6% remission factor

③ Gray object, 18% remission factor

④ White object, 90% remission factor

DIMENSIONAL DRAWING



Dimensions in mm (inch)

- ① Standard direction of the material being detected
- ② Center of optical axis, sender
- ③ Center of optical axis, receiver
- ④ M3 mounting hole
- ⑤ Connection
- ⑥ display and adjustment elements
- ⑦ focus

Further information as well as suitable accessories, example applications and downloads such as CAD dimensional models, operating instructions and software can be found at www.sick.com/1120896



SICK AG
WALDKIRCH
GERMANY
SICK.COM

SICK AT A GLANCE

SICK is a leading global technology company for intelligent sensors and integrated solutions in industrial automation. Our technologies set benchmarks, making your industrial processes more efficient, safer and more sustainable – both in logistics and manufacturing operations.

SICK combines sensor intelligence with industry expertise and certified consulting services. We provide the ideal foundation for scalable as well as tailor-made automation solutions and create added value along the entire value chain. Our close partnerships with our customers are more than just a promise: Together, we optimize productivity, improve quality, protect health and safety, and help build a sustainable future. All with empathy and trust.

Since 1946, we have been developing innovative technologies with passion and a pioneering spirit. With a global network in around 40 countries, SICK has a global presence and is always close by. The company's headquarters are located in Waldkirch near Freiburg, Germany. Our customers benefit from our understanding of both local and global requirements, which enables us to deliver tailor-made solutions

SICK
Sensor Intelligence